

**THREADED BODY**

AISI 303 stainless steel.

**PLUNGER**

Nickel-plated AISI 303 stainless steel.

Suggested tolerance for matching hole = H7.

**LOCKING NUT**

Stainless steel.

**KNOB**

High-resilience polyamide based (PA) technopolymer, black colour, matte finish.

**STANDARD EXECUTIONS**



- **GN 607-A-NI**: with knob, without locking nut.
- **GN 607-AK-NI**: with knob, with locking nut.

**FEATURES AND APPLICATIONS**

GN 607-NI indexing plungers have compact dimensions and are used on thin sheets.




**ACCESSORIES ON REQUEST**

AISI 303 stainless steel distance bushings GN 609.5 (see page 906) for the assembly of the indexing plunger on thin sheets.



GN 607-A-NI

GN 607-AK-NI



Code	Description	d1		d2	d3	e	l1	l2	l3-0.15	l4	sw	Spring preload [N]	Spring max load [N]	Axial holding force [N]	⚖️
		Plunger	Hole H7												
GN.35040	GN 607-6-A-NI	6	M12x1.5	25	19.6	45	6	10	5	17	7	18	400	34	
GN.35050	GN 607-8-A-NI	8	M16x1.5	31	21.9	54	8	12	6	19	14	24	500	60	
GN.35039	GN 607-6-AK-NI	6	M12x1.5	25	19.6	45	6	10	5	17	7	18	400	43	
GN.35049	GN 607-8-AK-NI	8	M16x1.5	31	21.9	54	8	12	6	19	14	24	500	76	

