

MATERIAL

AISI 304 stainless steel, sandblasted matte (GS) or electropolished (EP) finish.

PACKING RING

In black synthetic NBR rubber or blue silicone, suitable for contact with food FDA-compliant (U.S. Food and Drug Administration), attached to the handle body.

SCREWS (ONLY FOR GN 7332-A-2)

AISI 304 stainless steel with countersunk flat head, with polyamide coating in the underhead.

IP PROTECTION

Degree of protection IP 66 in accordance with EN 60529 table (on page A-19).
(only for executions with packing ring).

STANDARD EXECUTIONS

Front mounting by means of pass-through holes for M5 countersunk flat head screws:

- GN 7332-A-1: without gasket and screws.
- GN 7332-A-2: with packing ring NBR, black colour and and 4 M5 AISI 304 stainless steel screws.

Rear mounting by means of 4 M5 screws welded to the handle body:







- GN 7332-C-1: without gasket.
- GN 7332-C-2: with packing ring NBR, black colour.
- GN 7332-C-3: with silicone packing ring, blue.

ASSEMBLY INSTRUCTIONS

Drill the handle housing according to the template dimensions.



Drilling template



GN 7332-A-1



Code	Description	l1	l2	l3	l4	l5	l6 +1	l7 +1	h1	h2	m1	m2	△
GN.29235	GN 7332-155-A-1-GS	155	109	20	3.5	19.2	60	115	80	42	128	53	92
GN.29281	GN 7332-155-A-1-EP	155	109	20	3.5	19.2	60	115	80	42	128	53	92

INOX
STAINLESS
STEEL

GN 7332-A-2

Code	Description	l1	l2	l3	l4	l5	l6 +1	l7 +1	h1	h2	m1	m2	△
GN.29236	GN 7332-155-A-2-GS	155	109	20	3.5	19.2	60	115	80	42	128	53	104
GN.29282	GN 7332-155-A-2-EP	155	109	20	3.5	19.2	60	115	80	42	128	53	104

INOX
STAINLESS
STEEL



GN 7332-C-1

INOX STAINLESS STEEL

Code	Description	l1	l2	l3	l4	l5	l6 +1	l7 +1	h1	h2	m1	m2	⚖
GN.29237	GN 7332-155-C-1-GS	155	109	20	3.5	19.2	60	115	80	42	128	53	97
GN.29283	GN 7332-155-C-1-EP	155	109	20	3.5	19.2	60	115	80	42	128	53	97

GN 7332-C-2

INOX STAINLESS STEEL

Code	Description	l1	l2	l3	l4	l5	l6 +1	l7 +1	h1	h2	m1	m2	⚖
GN.29238	GN 7332-155-C-2-GS	155	109	20	3.5	19.2	60	115	80	42	128	53	107
GN.29284	GN 7332-155-C-2-EP	155	109	20	3.5	19.2	60	115	80	42	128	53	107

GN 7332-C-3

INOX STAINLESS STEEL

Code	Description	l1	l2	l3	l4	l5	l6 +1	l7 +1	h1	h2	m1	m2	⚖
GN.29239	GN 7332-155-C-3-GS	155	109	20	3.5	19.2	60	115	80	42	128	53	109
GN.29285	GN 7332-155-C-3-EP	155	109	20	3.5	19.2	60	115	80	42	128	53	109