

MATERIAL

Knurled aluminium profile, anodised, black colour.

CAP

Acetal resin based (POM) technopolymer, light-grey colour.

HANDLE

Polyamide based (PA) technopolymer, black colour, glossy finish.

STANDARD EXECUTIONS

- **GN 736-B-A**: H8 reamed hole, without handle.

Assembly by means of a supplied stainless steel transversal grub screw UNI 5929 (grub screw with hexagon socket and cup end).

- **GN 736-B-D**: H8 reamed hole, with revolving handle.


Assembly by means of a supplied stainless steel transversal grub screw UNI 5929 (grub screw with hexagon socket and cup end).

- **GN 736-K-A**: H8 reamed hole and keyway in compliance with DIN 6885/1 tolerance P9 (see page A-16), without handle.

- **GN 736-K-D**: H8 reamed hole and keyway in compliance with DIN 6885/1 tolerance P9 (see page A-16), with revolving handle.

SPECIAL EXECUTIONS ON REQUEST

On the surface of the cap words, marks, graphic symbols, etc...can be tampprinted in colours.



GN 736-B

Code	Description	d1	d2 H8	d3	d4	d5	d6	l3	r	△
GN.19501	GN 736-52-B10-A	52	10	22	37	39.5	-	-	-	56
GN.19502	GN 736-52-B10-D	52	10	22	37	39.5	13	19	15.5	69
GN.19511	GN 736-62-B10-A	62	10	25	47	49.5	-	-	-	76
GN.19512	GN 736-62-B10-D	62	10	25	47	49.5	14	21	20.5	90

GN 736-K

Code	Description	d1	d2 H8	d3	d4	d5	d6	l3	r	△
GN.19505	GN 736-52-K10-A	52	10	22	37	39.5	-	-	-	55
GN.19506	GN 736-52-K10-D	52	10	22	37	39.5	13	19	15.5	68
GN.19515	GN 736-62-K10-A	62	10	25	47	49.5	-	-	-	75
GN.19516	GN 736-62-K10-D	62	10	25	47	49.5	14	21	20.5	89