



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

**STANDARD EXECUTIONS**

- **GN 722.3-L**: with lever in left retracted position.
  - **GN 722.3-R**: with lever in right retracted position.
- Index for material and finish:
- **A4**: body and lever made out of cast AISI 316 stainless steel for welding, AISI 316 stainless steel plunger, AISI 316Ti stainless steel spring.
  - **SW**: body made out of cast zinc-plated steel, epoxy resin coating, RAL 9005 black colour, matte finish, cast zinc-plated steel lever, zinc-plated steel plunger, AISI 301 stainless steel spring.
  - **ZB**: body made out of cast zinc-plated steel, cast zinc-plated steel lever, zinc-plated steel plunger, AISI 301 stainless steel spring.

**FEATURES AND APPLICATIONS**

GN 722.3 lever indexing plungers are used when the plunger must be retracted quickly. By rotating the lifting lever by 180°, a notch keeps the plunger in the retracted position. The very small dimensional tolerances guarantee the necessary functional safety even in case of dirt.



GN 722.3-L-A4



Code	Description	d1		d2 +0.2	b+0.3	h1	h2	k1	k2	k3	l1	l2	l3	l4	l5	s	sw	t	m	[N]*	[N]#	△
		Plunger -0.05 -0.25	Hole +0.30 +0.10																			
GN.39451	GN 722.3-8-20-L-A4	8	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	179	
GN.39461	GN 722.3-10-20-L-A4	10	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	180	
GN.39471	GN 722.3-12-20-L-A4	12	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	186	
GN.39481	GN 722.3-14-20-L-A4	14	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	199	
GN.28966	GN 722.3-16-30-L-A4	16	10.1	10.1	15	15	14	34	10	83	20	54	55	80	30	17	10	55	30	110	246	
GN.28972	GN 722.3-20-30-L-A4	20	10.1	10.1	15	15	14	34	10	83	20	54	55	80	30	17	10	55	30	110	263	

GN 722.3-L-SW

Code	Description	d1		d2 +0.2	b+0.3	h1	h2	k1	k2	k3	l1	l2	l3	l4	l5	s	sw	t	m	[N]*	[N]#	△
		Plunger -0.05 -0.25	Hole +0.30 +0.10																			
GN.39371	GN 722.3-8-20-L-SW	8	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	179	
GN.39372	GN 722.3-10-20-L-SW	10	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	180	
GN.39373	GN 722.3-12-20-L-SW	12	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	186	
GN.39374	GN 722.3-14-20-L-SW	14	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	199	
GN.28967	GN 722.3-16-30-L-SW	16	10.1	10.1	15	15	14	34	10	83	20	54	55	80	30	17	10	55	30	110	246	
GN.28973	GN 722.3-20-30-L-SW	20	10.1	10.1	15	15	14	34	10	83	20	54	55	80	30	17	10	55	30	110	263	

GN 722.3-L-ZB

Code	Description	d1		d2 +0.2	b+0.3	h1	h2	k1	k2	k3	l1	l2	l3	l4	l5	s	sw	t	m	[N]*	[N]#	△
		Plunger -0.05 -0.25	Hole +0.30 +0.10																			
GN.39381	GN 722.3-8-20-L-ZB	8	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	179	
GN.39385	GN 722.3-10-20-L-ZB	10	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	180	
GN.39391	GN 722.3-12-20-L-ZB	12	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	186	
GN.39395	GN 722.3-14-20-L-ZB	14	6.1	6.1	7.5	10	7.5	18	12	83	14	35	37	48	20	10	6	34	15	50	199	
GN.28968	GN 722.3-16-30-L-ZB	16	10.1	10.1	15	15	14	34	10	83	20	54	55	80	30	17	10	55	30	110	246	
GN.28974	GN 722.3-20-30-L-ZB	20	10.1	10.1	15	15	14	34	10	83	20	54	55	80	30	17	10	55	30	110	263	

GN 722.3-R-A4



Code	Description	d1		d2 +0.2	b+0.3	h1	h2	k1	k2	k3	l1	l2	l3	l4	l5	s	sw	t	m	[N]*	[N]#	△
		Plunger -0.05 -0.25	Hole +0.30 +0.10																			
GN.39456	GN 722.3-8-20-R-A4	8	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	179	
GN.39466	GN 722.3-10-20-R-A4	10	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	180	
GN.39476	GN 722.3-12-20-R-A4	12	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	186	
GN.39486	GN 722.3-14-20-R-A4	14	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	199	
GN.28969	GN 722.3-16-30-R-A4	16	10.1	10.1	15	15	14	34	10	83	20	54	55	80	30	17	10	55	30	110	246	
GN.28975	GN 722.3-20-30-R-A4	20	10.1	10.1	15	15	14	34	10	83	20	54	55	80	30	17	10	55	30	110	263	

GN 722.3-R-SW

Code	Description	d1		d2 +0.2	b+0.3	h1	h2	k1	k2	k3	l1	l2	l3	l4	l5	s	sw	t	m	[N]*	[N]#	△
		Plunger -0.05 -0.25	Hole +0.30 +0.10																			
GN.39401	GN 722.3-8-20-R-SW	8	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	179	
GN.39402	GN 722.3-10-20-R-SW	10	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	180	
GN.39405	GN 722.3-12-20-R-SW	12	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	186	
GN.39406	GN 722.3-14-20-R-SW	14	6.1	6.1	7.5	10	7.5	18	12	83	14	35	37	48	20	10	6	34	15	50	199	
GN.28970	GN 722.3-16-30-R-SW	16	10.1	10.1	15	15	14	34	10	83	20	54	55	80	30	17	10	55	30	110	246	
GN.28976	GN 722.3-20-30-R-SW	20	10.1	10.1	15	15	14	34	10	83	20	54	55	80	30	17	10	55	30	110	263	

GN 722.3-R-ZB

Code	Description	d1		d2 +0.2	b+0.3	h1	h2	k1	k2	k3	l1	l2	l3	l4	l5	s	sw	t	m	[N]*	[N]#	△
		Plunger -0.05 -0.25	Hole +0.30 +0.10																			
GN.39382	GN 722.3-8-20-R-ZB	8	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	179	
GN.39386	GN 722.3-10-20-R-ZB	10	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	180	
GN.39392	GN 722.3-12-20-R-ZB	12	6.1	6.1	7.5	10	7.5	18	12	54	14	35	37	48	20	10	6	34	15	50	186	
GN.39396	GN 722.3-14-20-R-ZB	14	6.1	6.1	7.5	10	7.5	18	12	83	14	35	37	48	20	10	6	34	15	50	199	
GN.28971	GN 722.3-16-30-R-ZB	16	10.1	10.1	15	15	14	34	10	83	20	54	55	80	30	17	10	55	30	110	246	
GN.28977	GN 722.3-20-30-R-ZB	20	10.1	10.1	15	15	14	34	10	83	20	54	55	80	30	17	10	55	30	110	263	

\* Spring preload

# Spring maximum load