



MATERIAL

AISI 303 stainless steel.

WINDOW

Natural glass for use with maximum continuous working temperature 100°C.

RING

NBR synthetic rubber flat packing ring for use with maximum continuous working temperature 100°C.

STANDARD EXECUTIONS


- **GN 743.4-A:** with reflector made out of technopolymer (PSU polysulfone), maximum continuous working temperature 100°C.
- **GN 743.4-B:** without reflector, with AISI 301 stainless steel seal ring, maximum continuous working temperature 100°C.

FEATURES AND APPLICATIONS

GN 743.4 oil level sight glasses can be used on pressurised oil tanks (oil-proof resistance data available on request).

ACCESSORIES ON REQUEST

Brass nuts with Gas threadings, type GH. (see page 1201) for fitting to reservoirs with wall thickness smaller than 5 mm.



GN 743.4-A

Code	Description	d1	d2	d3	l1	l2	s	⚖
GN.37842	GN 743.4-11-M16X1,5-A	11	M16x1,5	22	8	7,5	20	19
GN.37844	GN 743.4-14-M20X1,5-A	14	M20x1,5	26	8,5	7,5	23	23
GN.37846	GN 743.4-18-M26X1,5-A	18	M26x1,5	32	9	8	30	41
GN.37838	GN 743.4-18-M27X1,5-A	18	M27x1,5	32	9	8	30	45
GN.37848	GN 743.4-24-M33X1,5-A	24	M33x1,5	40	11	8,5	36	64
GN.37850	GN 743.4-32-M42X1,5-A	32	M42x1,5	50	12	9	46	102
GN.37851	GN 743.4-32-M42X2-A	32	M42x2	50	12	9	46	110
GN.37841	GN 743.4-11-G3/8-A	11	G 3/8	22	8	7,5	20	19
GN.37843	GN 743.4-14-G1/2-A	14	G 1/2	26	8,5	7,5	23	23
GN.37845	GN 743.4-18-G3/4-A	18	G 3/4	32	9	8	30	41
GN.37847	GN 743.4-24-G1-A	24	G 1	40	11	8,5	36	64
GN.37849	GN 743.4-32-G1¼-A	32	G 1 1/4	50	12	9	46	102

GN 743.4-B

Code	Description	d1	d2	d3	l1	l2	s	⚖
GN.37548	GN 743.4-11-M16x1,5-B	11	M16x1,5	22	8	7,5	20	19
GN.37550	GN 743.4-14-M20x1,5-B	14	M20x1,5	26	8,5	7,5	23	23
GN.37552	GN 743.4-18-M26x1,5-B	18	M26x1,5	32	9	8	30	41
GN.37839	GN 743.4-18-M27X1,5-B	18	M27x1,5	32	9	8	30	45
GN.37554	GN 743.4-24-M33x1,5-B	24	M33x1,5	40	11	8,5	36	64
GN.37556	GN 743.4-32-M42x1,5-B	32	M42x1,5	50	12	9	46	102
GN.37852	GN 743.4-32-M42X2-B	32	M42x2	50	12	9	46	110
GN.37547	GN 743.4-11-G3/8-B	11	G 3/8	22	8	7,5	20	19
GN.37549	GN 743.4-14-G1/2-B	14	G 1/2	26	8,5	7,5	23	23
GN.37551	GN 743.4-18-G3/4-B	18	G 3/4	32	9	8	30	41
GN.37553	GN 743.4-24-G1-B	24	G 1	40	11	8,5	36	64
GN.37555	GN 743.4-32-G1¼-B	32	G 1 1/4	50	12	9	46	102