

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 

**MAIN SPECIFICATIONS**

- Aluminium
- Epoxy resin coating
- Black, RAL 9005, textured finish **SW**
- Cylindrical-head screw DIN 912
- Stainless Steel AISI 304
- Hexagon nut DIN 985
- Stainless Steel AISI 304
- Self-locking via polyamide ring

**FEATURES AND APPLICATIONS**



The clamping bore of sensor holders GN 277.4 is mechanically machined and designed for construction tubes GN 990 (see page -).  
 At the screw location **z**, the socket cap screw reduces the bore cross-section for clamping.  
 For clamping without tools, the socket cap screw can be replaced by an adjustable lever GN 911 (see page -) listed in the table as accessory.

**ACCESSORY**

Adjustable Hand Levers GN 911 (see page -).

**ON REQUEST**

Stainless steel version.



Code	Description	d1	d2	d3	b	k	l1	l2	m	t	z	z Clamping kit	△
GN.60101	GN 277.4-B12-B12-2-SW	B 12	B 12	27	25	25	64	25	29.5	11	M6-20	GN 911-45 / GN 911-63	59
GN.60102	GN 277.4-B12-B18-2-SW	B 12	B 18	27	25	25	64	25	29.5	11	M6-20	GN 911-45 / GN 911-63	57
GN.60106	GN 277.4-B14-B12-2-SW	B 14	B 12	27	25	25	64	25	29.5	11	M6-20	GN 911-45 / GN 911-63	57
GN.60107	GN 277.4-B14-B18-2-SW	B 14	B 18	27	25	25	64	25	29.5	11	M6-20	GN 911-45 / GN 911-63	55
GN.60111	GN 277.4-B15-B12-2-SW	B 15	B 12	27	25	25	64	25	29.5	11	M6-20	GN 911-45 / GN 911-63	56
GN.60112	GN 277.4-B15-B18-2-SW	B 15	B 18	27	25	25	64	25	29.5	11	M6-20	GN 911-45 / GN 911-63	54
GN.60116	GN 277.4-B16-B12-2-SW	B 16	B 12	27	25	25	64	25	29.5	11	M6-20	GN 911-45 / GN 911-63	55
GN.60117	GN 277.4-B16-B18-2-SW	B 16	B 18	27	25	25	64	25	29.5	11	M6-20	GN 911-45 / GN 911-63	53
GN.60121	GN 277.4-B18-B12-2-SW	B 18	B 12	27	25	25	64	25	29.5	11	M6-20	GN 911-45 / GN 911-63	54
GN.60122	GN 277.4-B18-B18-2-SW	B 18	B 18	27	25	25	64	25	29.5	11	M6-20	GN 911-45 / GN 911-63	52

Tube connectors