

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19

**MATERIAL**

- Cover: steel sheet, with chrome plating superficial treatment.
- Flange: zinc-plated steel sheet.
- Bayonet and flange with bayonet: zinc-plated steel sheet.

**PACKING RINGS**

Three flat packing rings in NBR synthetic rubber.

**OVERPRESSURE VALVE**

Technopolymer with NBR synthetic rubber O-ring and stainless steel spring.  
Set at around 0.350 bar (on request 0.700 bar).

**SUCTION VALVE**

Technopolymer sealing disk with NBR synthetic rubber O-ring and stainless steel spring.  
Set at around 0.030 bar.

**RING-SHAPED AIR FILTER**

Tech-foam 10 µ or 40 µ.

**FILTRATION BASKET**

Electro-galvanized steel or polypropylene-based technopolymer (PP), black colour.

**SAFETY CHAIN**

Brass

**STANDARD EXECUTIONS**

- **SMW-BA-F10-FRB+CM**: filtration fineness 10 µ, steel basket.
- **SMW-BA-F40-FRB+CM**: filtration fineness 40 µ, steel basket.
- **SMW-BA-F10-FRB+C**: filtration fineness 10 µ, technopolymer basket.
- **SMW-BA-F40-FRB+C**: filtration fineness 40 µ, technopolymer basket.

**MOUNTING**

SMW.80: by means of six glossy zinc-plated steel screws with screwdriver slot head M5x12, supplied.

**MAXIMUM CONTINUOUS WORKING TEMPERATURE**

100°C.

**FEATURES AND APPLICATIONS**

Double-valve breather caps SMW.BA with bayonet assembly creates a pressure plenum chamber right above the oil level within given limit conditions in order to avoid any reservoir deformation.

Advantages:

- it reduces reservoir air volume intake keeping clean fluid and filter;
- it improves suction pump action under working conditions reducing cavitation phenomenon;
- \*\*\*translation\_not\_found\*\*
- it reduces foam in fluid.

**TECHNICAL DATA**



Air flow rate for the different executions of breather caps can be obtained from the diagram on the basis of the difference of air pressure inside and outside the reservoir. Tests carried out without filtration basket.



**SPECIAL EXECUTIONS ON REQUEST**

With dipstick for fluid level indication (max 80 mm).



Drilling template





**SMW-BA-F10-FRB+CM**

Code	Description	D	D1	D2	L	L1	d1	Δ
156985	SMW.80-BA-F10-350MB-FRB+CM	81	72	83	55	80	49	445

**SMW-BA-F10-FRB+C**

Code	Description	D	D1	D2	L	L1	d1	Δ
156988	SMW.80-BA-F10-350MB-FRB+C	81	72	83	55	99	49	445

**SMW-BA-F40-FRB+CM**

Code	Description	D	D1	D2	L	L1	d1	Δ
156986	SMW.80-BA-F40-350MB-FRB+CM	81	72	83	55	80	49	445

**SMW-BA-F40-FRB+C**

Code	Description	D	D1	D2	L	L1	d1	Δ
156989	SMW.80-BA-F40-350MB-FRB+C	81	72	83	55	99	49	445