

MATERIAL

- Cover: steel sheet, with chrome plating superficial treatment.
- Flange: zinc-plated steel sheet.
- Threaded connector: zinc-plated steel.

PACKING RING

NBR synthetic rubber flat washer.

RING-SHAPED AIR FILTER

Tech-foam 10 μ or 40 μ .

FILTER SETTING SPRING

Zinc-plated steel.

STANDARD EXECUTIONS



- **SMN-F10**: mesh size 10 μ .
- **SMN-F40**: mesh size 40 μ .

MAXIMUM CONTINUOUS WORKING TEMPERATURE

100°C.

TECHNICAL DATA

Air flow rate for the different executions of breather caps can be obtained from the diagram on the basis of the difference of air pressure inside and outside the reservoir.



SMN-F10

Code	Description	D	d	L	d2	h	h1	⚖
156832	SMN.46-1/4-F10	47	G 1/4	53	7	10	6	69
156882	SMN.80-3/4-F10	81	G 3/4	69	17	16	11	265

SMN-F40

Code	Description	D	d	L	d2	h	h1	⚖
156833	SMN.46-1/4-F40	47	G 1/4	53	7	10	6	69
156883	SMN.80-3/4-F40	81	G 3/4	69	17	16	11	265