

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19

MATERIAL

Polyamide based (PA) technopolymer, black colour, matte finish.
Elastic fork in acetal based technopolymer (POM), black colour.

RETAINING CHAIN

Ball cable and coupling heads in acetal resin based technopolymer (POM), black colour.

NERINOX treated stainless steel ring with two coils.

Head fastening by means of a self-tapping screw Ø4,8 mm UNI EN ISO 7050 or a M5 countersunk-head screw UNI EN ISO 10642.

STANDARD EXECUTIONS

- **BTL-B-LP**: brass boss, threaded blind hole.
- **BTL-p-LP**: zinc-plated steel threaded stud, chamfered flat end according to UNI 947 : ISO 4753 (see Technical data on page A-11).

FEATURES AND APPLICATIONS


Suitable for use when it is necessary to avoid the loss of the knob.
The elastic fork, housed in the groove of the knob can turn freely.
The coiled ring connects the fork to the chain.

SPECIAL EXECUTIONS ON REQUEST

- Chain in different lengths.
- Knob with retaining cable CV-T (see page -) in polyethylene black colour.
- Knob with stainless steel cable GN 111 (see page -), GN 111.2 (see page -), GN 111.4 (see page -) and GN 111.8 (see page -).



ELESA Original design



BTL-B-LP

Code	Description	D	d	L	d1	d2	l2	h	R	Δ
7801	BTL.20 B-M5-LP	20	M5	21	11	11	12	10	20	11
7802	BTL.20 B-M6-LP	20	M6	21	11	11	12	12	20	12
7831	BTL.25 B-M6-LP	26	M6	26	16	15	15	12	21.5	20
7832	BTL.25 B-M8-LP	26	M8	26	16	15	15	13	21.5	19
7862	BTL.32 B-M8-LP	32	M8	30	17	21	17	15	21.5	23

BTL-p-LP

Code	Description	D	d	L	d1	d2	l	l2	R	Δ
7811	BTL.20 p-M6x16-LP	20	M6	21	11	11	16	12	20	14
7841	BTL.25 p-M8x20-LP	26	M8	26	16	15	20	15	21.5	25
7871	BTL.32 p-M8x25-LP	32	M8	30	17	21	25	17	21.5	30

Clamping elements