

**BASE AND CASE**

High-resistance polyamide based (PA) technopolymer.

Black base.

Case in the following colours:

- **C1:** RAL 7021 grey-black, glossy finish.

- **C2:** RAL 2004 orange, glossy finish.

- **C3:** RAL 7035 grey, glossy finish.

- **C55:** RAL 5005 blue colour, glossy finish.

Cover with perfectly sealed gasket and AISI 304 stainless steel UNI 6955 type self-tapping screws with six-lobe socket TORX® T06 (registered trademark by TEXTRON INC.).

The bonding between the base and the containment case using a high-performance sealant, in addition to preventing the penetration of dust and liquids, prevents them from detaching during use.

BOSS

AISI 304 stainless steel with Ø 20 mm H7 reamed hole, fitting to shaft by means of AISI 304 stainless steel grub screw, hexagon socket and cup end UNI 5929-85, included in the supply.

WINDOW

Transparent polyamide based (PA-T) technopolymer, moulded over the case and with a perfect seal. Resistant to solvents, oils, greases and other chemical agents (avoid contact with alcohol during cleaning operations).

DISPLAY

- 6-digit LCD of 12,0 mm height and special characters.

The visualization parameters can be set and modified by the operator by means of appropriate keys:

- values displayed in mm, inches or degrees

- display of mode for use (absolute or incremental mode)

- reading orientation (right or reverse).

KEYBOARD

Polyester membrane. Resistant to solvents, alcohol, acids, alkalis.

INTERNAL GASKET

O-ring front sealing in NBR synthetic rubber, between the case and the boss.

Brass bushing with double O-ring sealing in NBR synthetic rubber inside the rear cavity of the base (DD52R-E-RF-SST-IP67).

REAR GASKET

Foam polyethylene, supplied.


STANDARD EXECUTIONS

- **DD52R-E-RF-SST-IP65:** completely sealed indicator with IP 65 protection class, see EN 60529 table (on page A-19).

- **DD52R-E-RF-SST-IP67:** completely sealed indicator with IP 67 protection class, see EN 60529 table (on page A-19) obtained by means of a brass bushing with double seal ring inside the rear cavity of the base.

ASSEMBLY INSTRUCTIONS

1. Drill a Ø 6 mm by 10 mm hole in the body of the machine with a 30 mm centre distance from the spindle to fit the rear referring pin.
2. Fit the indicator onto the spindle and make sure that the referring pin fit the hole.
3. Clamp the boss to the spindle by tightening the grub screw with hexagon socket and cup end, according to UNI 5929-85.




ELESA Original design

**ACCESSORIES ON REQUEST (TO BE ORDERED SEPARATELY)**

- **MDX-52:** polyamide based (PA) technopolymer knob.


- **RB52-SST:** AISI 304 stainless steel reduction sleeves.

**RB52-SST**

Code	Description	dH7
CE.97941	RB52-12-SST-304	12
CE.97951	RB52-14-SST-304	14
CE.97956	RB52-15-SST-304	15
CE.97961	RB52-16-SST-304	16



- **BSA52-E:** die-cast zinc alloy bases for spindle locking, epoxy resin coating, black colour, matte finish. GN 302 adjustable handle with die-cast zinc alloy lever body and AISI 304 stainless steel clamping element. A Ø 6.1 mm hole to fit the referring pin of the indicator. Handle positioned either on the right or on the left. Fitting to the machine by means of two M4 cylindrical-head screws (not included in the supply).

**BSA52-E**

Code	Description	dH7	Weight
CE.99091	BSA52-E-12	12	234
CE.99093	BSA52-E-14	14	232
CE.99094	BSA52-E-15	15	230
CE.99095	BSA52-E-16	16	228
CE.99099	BSA52-E-20	20	226

FEATURES AND APPLICATIONS

DD52R-E-RF position indicators, with battery power supply, can be used on passing through shafts in any position to provide the reading of the absolute or incremental positioning of a machine component.

- The 6-digit display of 12,0 mm height ensures excellent readability even from a distance and from different viewing angles.
- The window in transparent technopolymer protects the LCD display against accidental shocks.
- In the operating mode, by using the 4 function keys, it is possible to select the incremental or the absolute mode, the unit of measure (mm, inches or degrees), reset the absolute counter or load a preset source value and the preset offset value.
- In the programming mode, through the 4 function keys, it is possible to program the reading after one revolution of the shaft, the direction of rotation, the display orientation, the resolution (number of decimal digits displayed), the source value and the offset value, the max. speed of rotation and set the functions of the keys for the different options available.
- The internal battery has a battery life up to 2.5 years. A specific symbol appears on the display when the battery needs replacing. It is easy to replace the battery by removing the front cover (Fig. 1) without having to remove the indicator from the drive shaft and without losing the configuration parameters.

QUICK POSITIONING SYSTEM

DD52R-E-RF indicators (Elesa Patent) are networked to the control unit UC-RF via radio frequency (RF), constituting a wireless system for rapid positioning of the machine parts (fig.2).

The wireless connection allows:

- reading of the current position
- setting of the target position
- configuration of all operational parameters

The radio frequency system network allows different machines to coexist in the same space without problems of mutual interference.

This system is particularly suitable for applications that require frequent format changes, facilitating the correct adjustment of the target/current position of the machine parts, also representing a safety system. In fact, even if a single DD52R-E-RF indicator is not placed in the target position, PLC doesn't allow the beginning of the machine production cycle, thus avoiding production issues.

The installation of the system is quick and easy as it does not require the use of connecting cables between the control unit and the indicators.

Further technical information available in "Operating instructions".

COMPATIBILITY

The "-W2" electronic indicators are compatible exclusively with the electronic indicators and control unit of the same "-W2" version.

Mechanical and electrical characteristics	
Power supply	Lithium battery CR2477 3.0 V
Battery life	up to 2.5 years
Display	6-digit LCD of 12 mm height and special characters
Reading scale	-199999; 999999
Number of decimal digits	programmable ⁽¹⁾
Unit of measure	millimetres, inches, degrees programmable ⁽¹⁾
Rotation max. speed	300/600/1000 r.p.m ⁽²⁾ programmable ⁽¹⁾
Resolution	10.000 impulses / revolution
Protection class	IP65 or IP67
Working temperature	0 ÷ 50 °C
Storing temperature	-20 ÷ +60 °C
Relative humidity	Max. 95% at 25°C without condensation
Conditions of use	For use in closed and sheltered places only
Altitude	Up to 2000 m
RF frequencies	2400-2416MHz

(1) See the operating instructions.

(2) Default: 600 r.p.m.

Higher rotation speed to 600 r.p.m. can be maintained for short periods of time.

The maximum speed value, the number of drives and the frequency of transmissions affect battery life.

Battery life depends on the conditions of use (setup, temperature, ...). The indicated value is an estimate made in temperature conditions > 20 °C and < 30 °C, and default setup.

Furthermore, this value refers to the condition of the device when it leaves the Elesa factory. Long storage times must always be considered for the estimation of the battery life when the device becomes operational.




Fig.1






Fig.2



C1 C2 C3 C55
RAL7021 RAL2004 RAL7035 RAL5005

INOX STAINLESS STEEL

Code	Description	
CE.99203	DD52R-E-RF-SST-IP65-C1	196
CE.99202	DD52R-E-RF-SST-IP65-C2	196
CE.99201	DD52R-E-RF-SST-IP65-C3	196
CE.99205	DD52R-E-RF-SST-IP65-C55	196
CE.99213	DD52R-E-RF-SST-IP67-C1	208
CE.99212	DD52R-E-RF-SST-IP67-C2	208
CE.99211	DD52R-E-RF-SST-IP67-C3	208
CE.99215	DD52R-E-RF-SST-IP67-C55	208