

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8**
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

SPECIFICATION


Body
Stainless steel AISI 305

Ball
Stainless Steel AISI 420C **NI**
Hardened

Clip
Stainless steel AISI 631

FEATURES AND APPLICATIONS

Press-fit stainless steel spring plungers GN 614.7 are used as detents as well as for push-on and push-off applications and ejectors. The tolerance d1 H7 is recommended for the locating bore.



Code	Description	d1 +0.1	d2	d3	d4 ±0.05	l1	l2	l3	l4	w	Spring preload [N]	Spring max load [N]	
GN.32651	GN 614.7-4-NI	4	3	4.6	4	10.7	0.9	1.8	5.6	0.9	12.9	19	1
GN.32653	GN 614.7-5-NI	5	4	5.6	5	12	0.9	2.1	6	1.3	19.3	29.2	2
GN.32655	GN 614.7-6-NI	6	5	6.5	6	15	1	2.3	8.2	1.7	28	47.5	3
GN.32657	GN 614.7-8-NI	8	6.5	8.5	8	18	1.1	2.9	9.5	2.3	40	67.3	5
GN.32659	GN 614.7-10-NI	10	8.5	11	10	26	1.5	4.2	14.3	3.1	66	105	9