


- MATERIAL**
 Polyamide based (PA) technopolymer, black or red colour, glossy finish (HGFT/SL only black colour).
- WINDOW**
 Transparent polyamide based (PA-T/AR) technopolymer.
- PACKING RING**
 NBR synthetic rubber.
- STANDARD EXECUTIONS**
 - **HGFT.**: with matte anodised aluminium star-shaped contrast screen with red central level point.
 - **HGFT/SL**: without contrast screen.
- MAXIMUM CONTINUOUS WORKING TEMPERATURE**
 100°C at 3 bar pressure.
- NOTE**
 For use with other fluids with special additives, please contact ELESa Sales Department.
- ACCESSORIES ON REQUEST**
 Brass nut type GH. (see page 1201) for fitting to reservoirs with wall thickness smaller than 5 mm.



ELESa Original design



HGFT.

Code	Description	Code	Description	d1	A	B	D	d	s	Tightening torque [Nm]	⚖
14441	HGFT.10-3/8 C9	14444	HGFT.10-3/8 C6	G 3/8	8	7	24	11	22	4+8	4
14461	HGFT.13-1/2 C9	14464	HGFT.13-1/2 C6	G 1/2	10	8.5	28	14.5	24	6+8	6
14481	HGFT.16-3/4 C9	14484	HGFT.16-3/4 C6	G 3/4	9.5	8.5	35	18	32	8+10	10
14521	HGFT.21-1 C9	14524	HGFT.21-1 C6	G 1	11	9.5	42.5	23	38	10+12	15
14541	HGFT.25-1¼ C9	14544	HGFT.25-1¼ C6	G1 1/4	11	9	50	30	46	12+15	30
14561	HGFT.40-2 C9	14564	HGFT.40-2 C6	G 2	12	11	66	40	60	12+15	60

HGFT/SL

Code	Description	d1	A	B	D	d	s	Tightening torque [Nm]	⚖
14446	HGFT.10/SL-3/8	G 3/8	8	7	24	11	22	4+8	3
14466	HGFT.13/SL-1/2	G 1/2	10	8.5	28	14.5	24	6+8	5
14486	HGFT.16/SL-3/4	G 3/4	9.5	8.5	35	18	32	8+10	9
14526	HGFT.21/SL-1	G 1	11	9.5	42.5	23	38	10+12	14
14546	HGFT.25/SL-1¼	G1 1/4	11	9	50	30	46	12+15	29
14566	HGFT.40/SL-2	G 2	12	11	66	40	60	12+15	59