

MATERIAL

AlSi 304 stainless steel.

RIVETS

AlSi 304 stainless steel.

BASE

AlSi 304 stainless steel.

PUSH LEVER

AlSi 303 stainless steel.

HANDLE




Polyurethane, red colour.

CLAMPING BOLT

To be ordered separately.

FEATURES AND APPLICATIONS

All articulated joints are lubricated with special grease.
MFC-SST clamps are suitable for use requiring high resistant torque given their solid base body. Both push and pull clamping can be performed effectively.



Code	Description	a	b1	b2	d1	d2	d3	h1	l1	l2	l3	m1	m2	m3	s	t	w	FH*	Δ
GG.AS395	MFC.70-ASX	12	64	36	8.5	M6	4.3	41	86	79	22	26	13	26	6	12	20	1200	165
GG.AS397	MFC.160-ASX	15	85	46	11	M6	5.5	56	116	107	31	33.5	11.5	36.5	7	12	30	2800	360
GG.AS399	MFC.360-ASX	25	90	45.5	12	M8	5.5	70	122	114	32	33.5	30	36.5	7	15	32	5600	485

* Holding force.