

MATERIAL

Polyamide based (PA) technopolymer, black colour, matte finish.

STANDARD EXECUTIONS

- **BT-HP-p**: zinc-plated steel threaded stud, chamfered flat end UNI EN ISO 4753 : 2012 (see Technical data on page A-11).
- **BT-HP-SST-p**: AISI 304 stainless steel threaded stud, chamfered flat end UNI EN ISO 4753 : 2012 (see Technical data on page A-11).

FEATURES AND APPLICATIONS


The retained knobs are used to secure blanking plates, covers, or other items without the risk of loss.

This is made possible by the non-threaded part of the stem, which allows the knob to remain anchored (retained) to the machinery.




ELESA Original design

Types of assembly



Conversion Table
1 mm = 0.039 inch

D	
mm	inch
25	0.98
32	1.26



BT-HP-p

Code	Description	D	L	d1	d2	d3 ±0.1	d4	l1	l2	l3	h	a1	a2	a3	△
5351	BT-HP.25-p-M6x22	25	19	M6	16	4.7	6.5	22	8	3	8	5 + 8	10 + 16	15 + 24	13
5356	BT-HP.25-p-M6x32	25	19	M6	16	4.7	6.5	32	8	3	8	5 + 8	10 + 16	15 + 24	15
5361	BT-HP.25-p-M8x30	25	19	M8	16	6.5	8.5	30	10	4	8	7 + 10	14 + 20	21 + 30	18
5366	BT-HP.25-p-M8x40	25	19	M8	16	6.5	8.5	40	10	4	8	7 + 10	14 + 20	21 + 30	23
5369	BT-HP.32-p-M6x18	32	23	M6	17	4.7	6.5	18	8	3	9	5 + 8	10 + 16	15 + 24	15
5371	BT-HP.32-p-M6x22	32	23	M6	17	4.7	6.5	22	8	3	9	5 + 8	10 + 16	15 + 24	16
5376	BT-HP.32-p-M6x32	32	23	M6	17	4.7	6.5	32	8	3	9	5 + 8	10 + 16	15 + 24	18
5381	BT-HP.32-p-M8x30	32	23	M8	17	6.5	8.5	30	10	4	9	7 + 10	14 + 20	21 + 30	22
5386	BT-HP.32-p-M8x40	32	23	M8	17	6.5	8.5	40	10	4	9	7 + 10	14 + 20	21 + 30	27

BT-HP-SST-p

Code	Description	D	L	d1	d2	d3 ±0.1	d4	l1	l2	l3	h	a1	a2	a3	△
105351	BT-HP.25-SST-p-M6x22	25	19	M6	16	4.7	6.5	22	8	3	8	5 + 8	10 + 16	15 + 24	13
105356	BT-HP.25-SST-p-M6x32	25	19	M6	16	4.7	6.5	32	8	3	8	5 + 8	10 + 16	15 + 24	15
105361	BT-HP.25-SST-p-M8x30	25	19	M8	16	6.5	8.5	30	10	4	8	7 + 10	14 + 20	21 + 30	18
105366	BT-HP.25-SST-p-M8x40	25	19	M8	16	6.5	8.5	40	10	4	8	7 + 10	14 + 20	21 + 30	23
105371	BT-HP.32-SST-p-M6x22	32	23	M6	17	4.7	6.5	22	8	3	9	5 + 8	10 + 16	15 + 24	16
105376	BT-HP.32-SST-p-M6x32	32	23	M6	17	4.7	6.5	32	8	3	9	5 + 8	10 + 16	15 + 24	18
105381	BT-HP.32-SST-p-M8x30	32	23	M8	17	6.5	8.5	30	10	4	9	7 + 10	14 + 20	21 + 30	22
105386	BT-HP.32-SST-p-M8x40	32	23	M8	17	6.5	8.5	40	10	4	9	7 + 10	14 + 20	21 + 30	27