


DIN 39 | Impugnature sagomate

Acciaio o acciaio INOX AISI 316L



MATERIALE


Acciaio tornito, lucidato a specchio.

ESECUZIONE STANDARD


- **DIN 39-ST**: acciaio tornito, lucidato a specchio.
- **DIN 39-A4**: acciaio INOX AISI 316L.

ESECUZIONI SPECIALI A RICHIESTA


Perno liscio in tolleranza h8 (DIN 39-D).



DIN 39-ST



DIN 39-A4



DIN 39-ST

Codice	Descrizione	d1	d3	d4 h13	l1	l2	l3	⚖
GN.10935	DIN 39-ST-16-E	16	M6	10	50	11	7	45
GN.10955	DIN 39-ST-20-E	20	M8	13	64	13	8	91
GN.10975	DIN 39-ST-25-E	25	M10	16	80	14	10	177
GN.10995	DIN 39-ST-32-E	32	M12	20	100	21	13	360
GN.10998	DIN 39-ST-36-E	36	M16	22	112	26	14	526

DIN 39-A4

Codice	Descrizione	d1	d3	d4 h13	l1	l2	l3	⚖
GN.10911	DIN 39-A4-16-E	16	M6	10	50	11	7	40
GN.10914	DIN 39-A4-20-E	20	M8	13	64	13	8	100
GN.10917	DIN 39-A4-25-E	25	M10	16	80	14	10	177

