





GN 918-KV




Codice	Descrizione	d3	d1 -0.5	d2	d6	l1	l2	h1	h2	h4	h7	⚖
GN.31795	GN 918-40-KV-L	25	40	M8	20	8	100	10	31	55	0.2	178
GN.31796	GN 918-40-KV-R	25	40	M8	20	8	100	10	31	55	0.2	177
GN.31800	GN 918-50-KV-L	30	50	M10	24	11	116	12	35	62	0.2	297
GN.31801	GN 918-50-KV-R	30	50	M10	24	11	116	12	35	62	0.2	297

GN 918-GV

Codice	Descrizione	d3	d1 -0.5	d2	d6	l1	l2	h1	h2	h5	h7	⚖
GN.84501	GN 918-40-GV-L	25	40	M8	20	8	100	10	31	31	0.2	176
GN.84521	GN 918-40-GV-R	25	40	M8	20	8	100	10	31	31	0.2	176
GN.84701	GN 918-50-GV-L	30	50	M10	24	11	116	12	35	36	0.2	297
GN.84721	GN 918-50-GV-R	30	50	M10	24	11	116	12	35	36	0.2	297


GN 918-SK

Codice	Descrizione	d1 -0.5	d2	d6	l1	h1	h3	h7	sw	⚖
GN.84631	GN 918-40-SK-L	40	M8	20	8	10	21.5	0.2	15	87
GN.84651	GN 918-40-SK-R	40	M8	20	8	10	21.5	0.2	15	88
GN.84831	GN 918-50-SK-L	50	M10	24	11	12	24.5	0.2	19	160
GN.84851	GN 918-50-SK-R	50	M10	24	11	12	24.5	0.2	19	160





GN 918-KVS

Codice	Descrizione	d3	d1 -0.5	d2	d4 h9	d6	l1	l2	h1	h2	h4	h6 -0.1	h7	Δ
GN.84601	GN 918-40-KVS-L-10	25	40	M6	9	20	10	100	10	36	55	2.5	0.2	179
GN.84602	GN 918-40-KVS-L-15	25	40	M6	9	20	15	100	10	36	55	2.5	0.2	180
GN.84603	GN 918-40-KVS-L-20	25	40	M6	9	20	20	100	10	36	55	2.5	0.2	181
GN.84604	GN 918-40-KVS-L-25	25	40	M6	9	20	25	100	10	36	55	2.5	0.2	182
GN.84605	GN 918-40-KVS-L-30	25	40	M6	9	20	30	100	10	36	55	2.5	0.2	183
GN.84606	GN 918-40-KVS-L-40	25	40	M6	9	20	40	100	10	36	55	2.5	0.2	185
GN.84607	GN 918-40-KVS-L-45	25	40	M6	9	20	45	100	10	36	55	2.5	0.2	185
GN.84608	GN 918-40-KVS-L-50	25	40	M6	9	20	50	100	10	36	55	2.5	0.2	186
GN.84609	GN 918-40-KVS-L-60	25	40	M6	9	20	60	100	10	36	55	2.5	0.2	188
GN.84610	GN 918-40-KVS-L-65	25	40	M6	9	20	65	100	10	36	55	2.5	0.2	190
GN.84611	GN 918-40-KVS-L-70	25	40	M6	9	20	70	100	10	36	55	2.5	0.2	192
GN.84612	GN 918-40-KVS-L-80	25	40	M6	9	20	80	100	10	36	55	2.5	0.2	193
GN.84613	GN 918-40-KVS-L-90	25	40	M6	9	20	90	100	10	36	55	2.5	0.2	196
GN.84616	GN 918-40-KVS-R-10	25	40	M6	9	20	10	100	10	36	55	2.5	0.2	179
GN.84617	GN 918-40-KVS-R-15	25	40	M6	9	20	15	100	10	36	55	2.5	0.2	180
GN.84618	GN 918-40-KVS-R-20	25	40	M6	9	20	20	100	10	36	55	2.5	0.2	181
GN.84619	GN 918-40-KVS-R-25	25	40	M6	9	20	25	100	10	36	55	2.5	0.2	182
GN.84620	GN 918-40-KVS-R-30	25	40	M6	9	20	30	100	10	36	55	2.5	0.2	183
GN.84621	GN 918-40-KVS-R-40	25	40	M6	9	20	40	100	10	36	55	2.5	0.2	185
GN.84622	GN 918-40-KVS-R-45	25	40	M6	9	20	45	100	10	36	55	2.5	0.2	185
GN.84623	GN 918-40-KVS-R-50	25	40	M6	9	20	50	100	10	36	55	2.5	0.2	186
GN.84624	GN 918-40-KVS-R-60	25	40	M6	9	20	60	100	10	36	55	2.5	0.2	188
GN.84625	GN 918-40-KVS-R-65	25	40	M6	9	20	65	100	10	36	55	2.5	0.2	190
GN.84626	GN 918-40-KVS-R-70	25	40	M6	9	20	70	100	10	36	55	2.5	0.2	192
GN.84627	GN 918-40-KVS-R-80	25	40	M6	9	20	80	100	10	36	55	2.5	0.2	193
GN.84628	GN 918-40-KVS-R-90	25	40	M6	9	20	90	100	10	36	55	2.5	0.2	196
GN.84801	GN 918-50-KVS-L-12	30	50	M8	11	24	12	116	12	41	62	2.5	0.2	297
GN.84802	GN 918-50-KVS-L-22	30	50	M8	11	24	22	116	12	41	62	2.5	0.2	301
GN.84803	GN 918-50-KVS-L-32	30	50	M8	11	24	32	116	12	41	62	2.5	0.2	305
GN.84804	GN 918-50-KVS-L-42	30	50	M8	11	24	42	116	12	41	62	2.5	0.2	308
GN.84805	GN 918-50-KVS-L-52	30	50	M8	11	24	52	116	12	41	62	2.5	0.2	313
GN.84806	GN 918-50-KVS-L-62	30	50	M8	11	24	62	116	12	41	62	2.5	0.2	316
GN.84807	GN 918-50-KVS-L-72	30	50	M8	11	24	72	116	12	41	62	2.5	0.2	320
GN.84808	GN 918-50-KVS-L-82	30	50	M8	11	24	82	116	12	41	62	2.5	0.2	324
GN.84809	GN 918-50-KVS-L-92	30	50	M8	11	24	92	116	12	41	62	2.5	0.2	326
GN.84810	GN 918-50-KVS-L-102	30	50	M8	11	24	102	116	12	41	62	2.5	0.2	324
GN.84811	GN 918-50-KVS-L-112	30	50	M8	11	24	112	116	12	41	62	2.5	0.2	333
GN.84815	GN 918-50-KVS-R-12	30	50	M8	11	24	12	116	12	41	62	2.5	0.2	297
GN.84816	GN 918-50-KVS-R-22	30	50	M8	11	24	22	116	12	41	62	2.5	0.2	301
GN.84817	GN 918-50-KVS-R-32	30	50	M8	11	24	32	116	12	41	62	2.5	0.2	305
GN.84818	GN 918-50-KVS-R-42	30	50	M8	11	24	42	116	12	41	62	2.5	0.2	308
GN.84819	GN 918-50-KVS-R-52	30	50	M8	11	24	52	116	12	41	62	2.5	0.2	313
GN.84820	GN 918-50-KVS-R-62	30	50	M8	11	24	62	116	12	41	62	2.5	0.2	316
GN.84821	GN 918-50-KVS-R-72	30	50	M8	11	24	72	116	12	41	62	2.5	0.2	320
GN.84822	GN 918-50-KVS-R-82	30	50	M8	11	24	82	116	12	41	62	2.5	0.2	324
GN.84823	GN 918-50-KVS-R-92	30	50	M8	11	24	92	116	12	41	62	2.5	0.2	326
GN.84824	GN 918-50-KVS-R-102	30	50	M8	11	24	102	116	12	41	62	2.5	0.2	324
GN.84825	GN 918-50-KVS-R-112	30	50	M8	11	24	112	116	12	41	62	2.5	0.2	333




GN 918-GVS

Codice	Descrizione	d3	d1 -0.5	d2	d4 h9	d6	l1	l2	h1	h2	h5	h6 -0.1	h7	△
GN.84541	GN 918-40-GVS-L-10	25	40	M6	9	20	10	100	10	36	31	2.5	0.2	178
GN.84542	GN 918-40-GVS-L-15	25	40	M6	9	20	15	100	10	36	31	2.5	0.2	178
GN.84543	GN 918-40-GVS-L-20	25	40	M6	9	20	20	100	10	36	31	2.5	0.2	180
GN.84544	GN 918-40-GVS-L-25	25	40	M6	9	20	25	100	10	36	31	2.5	0.2	180
GN.84545	GN 918-40-GVS-L-30	25	40	M6	9	20	30	100	10	36	31	2.5	0.2	182
GN.84546	GN 918-40-GVS-L-40	25	40	M6	9	20	40	100	10	36	31	2.5	0.2	183
GN.84547	GN 918-40-GVS-L-45	25	40	M6	9	20	45	100	10	36	31	2.5	0.2	184
GN.84548	GN 918-40-GVS-L-50	25	40	M6	9	20	50	100	10	36	31	2.5	0.2	184
GN.84549	GN 918-40-GVS-L-60	25	40	M6	9	20	60	100	10	36	31	2.5	0.2	186
GN.84550	GN 918-40-GVS-L-65	25	40	M6	9	20	65	100	10	36	31	2.5	0.2	188
GN.84551	GN 918-40-GVS-L-70	25	40	M6	9	20	70	100	10	36	31	2.5	0.2	190
GN.84552	GN 918-40-GVS-L-80	25	40	M6	9	20	80	100	10	36	31	2.5	0.2	192
GN.84553	GN 918-40-GVS-L-90	25	40	M6	9	20	90	100	10	36	31	2.5	0.2	194
GN.84556	GN 918-40-GVS-R-10	25	40	M6	9	20	10	100	10	36	31	2.5	0.2	178
GN.84557	GN 918-40-GVS-R-15	25	40	M6	9	20	15	100	10	36	31	2.5	0.2	178
GN.84558	GN 918-40-GVS-R-20	25	40	M6	9	20	20	100	10	36	31	2.5	0.2	180
GN.84559	GN 918-40-GVS-R-25	25	40	M6	9	20	25	100	10	36	31	2.5	0.2	180
GN.84560	GN 918-40-GVS-R-30	25	40	M6	9	20	30	100	10	36	31	2.5	0.2	182
GN.84561	GN 918-40-GVS-R-40	25	40	M6	9	20	40	100	10	36	31	2.5	0.2	183
GN.84562	GN 918-40-GVS-R-45	25	40	M6	9	20	45	100	10	36	31	2.5	0.2	184
GN.84563	GN 918-40-GVS-R-50	25	40	M6	9	20	50	100	10	36	31	2.5	0.2	184
GN.84564	GN 918-40-GVS-R-60	25	40	M6	9	20	60	100	10	36	31	2.5	0.2	186
GN.84565	GN 918-40-GVS-R-65	25	40	M6	9	20	65	100	10	36	31	2.5	0.2	188
GN.84566	GN 918-40-GVS-R-70	25	40	M6	9	20	70	100	10	36	31	2.5	0.2	190
GN.84567	GN 918-40-GVS-R-80	25	40	M6	9	20	80	100	10	36	31	2.5	0.2	192
GN.84568	GN 918-40-GVS-R-90	25	40	M6	9	20	90	100	10	36	31	2.5	0.2	194
GN.84741	GN 918-50-GVS-L-12	30	50	M8	11	24	12	116	12	41	36	2.5	0.2	297
GN.84742	GN 918-50-GVS-L-22	30	50	M8	11	24	22	116	12	41	36	2.5	0.2	301
GN.84743	GN 918-50-GVS-L-32	30	50	M8	11	24	32	116	12	41	36	2.5	0.2	305
GN.84744	GN 918-50-GVS-L-42	30	50	M8	11	24	42	116	12	41	36	2.5	0.2	308
GN.84745	GN 918-50-GVS-L-52	30	50	M8	11	24	52	116	12	41	36	2.5	0.2	313
GN.84746	GN 918-50-GVS-L-62	30	50	M8	11	24	62	116	12	41	36	2.5	0.2	316
GN.84747	GN 918-50-GVS-L-72	30	50	M8	11	24	72	116	12	41	36	2.5	0.2	320
GN.84748	GN 918-50-GVS-L-82	30	50	M8	11	24	82	116	12	41	36	2.5	0.2	324
GN.84749	GN 918-50-GVS-L-92	30	50	M8	11	24	92	116	12	41	36	2.5	0.2	326
GN.84750	GN 918-50-GVS-L-102	30	50	M8	11	24	102	116	12	41	36	2.5	0.2	324
GN.84751	GN 918-50-GVS-L-112	30	50	M8	11	24	112	116	12	41	36	2.5	0.2	333
GN.84755	GN 918-50-GVS-R-12	30	50	M8	11	24	12	116	12	41	36	2.5	0.2	297
GN.84756	GN 918-50-GVS-R-22	30	50	M8	11	24	22	116	12	41	36	2.5	0.2	301
GN.84757	GN 918-50-GVS-R-32	30	50	M8	11	24	32	116	12	41	36	2.5	0.2	305
GN.84758	GN 918-50-GVS-R-42	30	50	M8	11	24	42	116	12	41	36	2.5	0.2	308
GN.84759	GN 918-50-GVS-R-52	30	50	M8	11	24	52	116	12	41	36	2.5	0.2	313
GN.84760	GN 918-50-GVS-R-62	30	50	M8	11	24	62	116	12	41	36	2.5	0.2	316
GN.84761	GN 918-50-GVS-R-72	30	50	M8	11	24	72	116	12	41	36	2.5	0.2	320
GN.84762	GN 918-50-GVS-R-82	30	50	M8	11	24	82	116	12	41	36	2.5	0.2	324
GN.84763	GN 918-50-GVS-R-92	30	50	M8	11	24	92	116	12	41	36	2.5	0.2	326
GN.84764	GN 918-50-GVS-R-102	30	50	M8	11	24	102	116	12	41	36	2.5	0.2	324
GN.84765	GN 918-50-GVS-R-112	30	50	M8	11	24	112	116	12	41	36	2.5	0.2	333




GN 918-SKS

Codice	Descrizione	d1 -0.5	d2	d4 h9	d6	l1	h1	h3	h6 -0.1	h7	sw	⚖
GN.84671	GN 918-40-SKS-L-15	40	M6	9	20	15	10	26	2.5	0.2	15	92
GN.84672	GN 918-40-SKS-L-20	40	M6	9	20	20	10	26	2.5	0.2	15	92
GN.84673	GN 918-40-SKS-L-25	40	M6	9	20	25	10	26	2.5	0.2	15	94
GN.84674	GN 918-40-SKS-L-30	40	M6	9	20	30	10	26	2.5	0.2	15	94
GN.84675	GN 918-40-SKS-L-35	40	M6	9	20	35	10	26	2.5	0.2	15	96
GN.84676	GN 918-40-SKS-L-40	40	M6	9	20	40	10	26	2.5	0.2	15	97
GN.84677	GN 918-40-SKS-L-50	40	M6	9	20	50	10	26	2.5	0.2	15	98
GN.84678	GN 918-40-SKS-L-55	40	M6	9	20	55	10	26	2.5	0.2	15	98
GN.84679	GN 918-40-SKS-L-60	40	M6	9	20	60	10	26	2.5	0.2	15	100
GN.84680	GN 918-40-SKS-L-70	40	M6	9	20	70	10	26	2.5	0.2	15	102
GN.84681	GN 918-40-SKS-L-75	40	M6	9	20	75	10	26	2.5	0.2	15	104
GN.84682	GN 918-40-SKS-L-80	40	M6	9	20	80	10	26	2.5	0.2	15	106
GN.84683	GN 918-40-SKS-L-90	40	M6	9	20	90	10	26	2.5	0.2	15	108
GN.84686	GN 918-40-SKS-R-15	40	M6	9	20	15	10	26	2.5	0.2	15	92
GN.84687	GN 918-40-SKS-R-20	40	M6	9	20	20	10	26	2.5	0.2	15	92
GN.84688	GN 918-40-SKS-R-25	40	M6	9	20	25	10	26	2.5	0.2	15	94
GN.84689	GN 918-40-SKS-R-30	40	M6	9	20	30	10	26	2.5	0.2	15	94
GN.84690	GN 918-40-SKS-R-35	40	M6	9	20	35	10	26	2.5	0.2	15	96
GN.84691	GN 918-40-SKS-R-40	40	M6	9	20	40	10	26	2.5	0.2	15	97
GN.84692	GN 918-40-SKS-R-50	40	M6	9	20	50	10	26	2.5	0.2	15	98
GN.84693	GN 918-40-SKS-R-55	40	M6	9	20	55	10	26	2.5	0.2	15	98
GN.84694	GN 918-40-SKS-R-60	40	M6	9	20	60	10	26	2.5	0.2	15	100
GN.84695	GN 918-40-SKS-R-70	40	M6	9	20	70	10	26	2.5	0.2	15	102
GN.84696	GN 918-40-SKS-R-75	40	M6	9	20	75	10	26	2.5	0.2	15	104
GN.84697	GN 918-40-SKS-R-80	40	M6	9	20	80	10	26	2.5	0.2	15	106
GN.84698	GN 918-40-SKS-R-90	40	M6	9	20	90	10	26	2.5	0.2	15	108
GN.84871	GN 918-50-SKS-L-12	50	M8	11	24	12	12	31	2.5	0.2	19	165
GN.84872	GN 918-50-SKS-L-22	50	M8	11	24	22	12	31	2.5	0.2	19	169
GN.84873	GN 918-50-SKS-L-32	50	M8	11	24	32	12	31	2.5	0.2	19	173
GN.84874	GN 918-50-SKS-L-42	50	M8	11	24	42	12	31	2.5	0.2	19	176
GN.84875	GN 918-50-SKS-L-52	50	M8	11	24	52	12	31	2.5	0.2	19	181
GN.84876	GN 918-50-SKS-L-62	50	M8	11	24	62	12	31	2.5	0.2	19	184
GN.84877	GN 918-50-SKS-L-72	50	M8	11	24	72	12	31	2.5	0.2	19	188
GN.84878	GN 918-50-SKS-L-82	50	M8	11	24	82	12	31	2.5	0.2	19	192
GN.84879	GN 918-50-SKS-L-92	50	M8	11	24	92	12	31	2.5	0.2	19	194
GN.84880	GN 918-50-SKS-L-102	50	M8	11	24	102	12	31	2.5	0.2	19	192
GN.84881	GN 918-50-SKS-L-112	50	M8	11	24	112	12	31	2.5	0.2	19	201
GN.84886	GN 918-50-SKS-R-12	50	M8	11	24	12	12	31	2.5	0.2	19	165
GN.84887	GN 918-50-SKS-R-22	50	M8	11	24	22	12	31	2.5	0.2	19	169
GN.84888	GN 918-50-SKS-R-32	50	M8	11	24	32	12	31	2.5	0.2	19	173
GN.84889	GN 918-50-SKS-R-42	50	M8	11	24	42	12	31	2.5	0.2	19	176
GN.84890	GN 918-50-SKS-R-52	50	M8	11	24	52	12	31	2.5	0.2	19	181
GN.84891	GN 918-50-SKS-R-62	50	M8	11	24	62	12	31	2.5	0.2	19	184
GN.84892	GN 918-50-SKS-R-72	50	M8	11	24	72	12	31	2.5	0.2	19	188
GN.84893	GN 918-50-SKS-R-82	50	M8	11	24	82	12	31	2.5	0.2	19	192
GN.84894	GN 918-50-SKS-R-92	50	M8	11	24	92	12	31	2.5	0.2	19	194
GN.84895	GN 918-50-SKS-R-102	50	M8	11	24	102	12	31	2.5	0.2	19	192
GN.84896	GN 918-50-SKS-R-112	50	M8	11	24	112	12	31	2.5	0.2	19	201




GN 918-KVB

Codice	Descrizione	d3	d1 -0.5	d2	d4 h9	d5	d6	l1 max	l2	l3	h1	h2	h4	h6 -0.1	h7	wmax	
GN.84571	GN 918-40-KVB-L-12	25	40	M6	9	12	20	12	100	8.5	10	30.5	55	2.5	0.2	5	180
GN.84572	GN 918-40-KVB-L-22	25	40	M6	9	12	20	22	100	8.5	10	30.5	55	2.5	0.2	5	182
GN.84573	GN 918-40-KVB-L-27	25	40	M6	9	12	20	27	100	8.5	10	30.5	55	2.5	0.2	5	183
GN.84574	GN 918-40-KVB-L-32	25	40	M6	9	12	20	32	100	8.5	10	30.5	55	2.5	0.2	5	184
GN.84575	GN 918-40-KVB-L-37	25	40	M6	9	12	20	37	100	8.5	10	30.5	55	2.5	0.2	5	185
GN.84576	GN 918-40-KVB-L-42	25	40	M6	9	12	20	42	100	8.5	10	30.5	55	2.5	0.2	5	186
GN.84577	GN 918-40-KVB-L-47	25	40	M6	9	12	20	47	100	8.5	10	30.5	55	2.5	0.2	5	187
GN.84578	GN 918-40-KVB-L-57	25	40	M6	9	12	20	57	100	8.5	10	30.5	55	2.5	0.2	5	189
GN.84579	GN 918-40-KVB-L-62	25	40	M6	9	12	20	62	100	8.5	10	30.5	55	2.5	0.2	5	189
GN.84580	GN 918-40-KVB-L-67	25	40	M6	9	12	20	67	100	8.5	10	30.5	55	2.5	0.2	5	190
GN.84581	GN 918-40-KVB-L-77	25	40	M6	9	12	20	77	100	8.5	10	30.5	55	2.5	0.2	5	192
GN.84582	GN 918-40-KVB-L-82	25	40	M6	9	12	20	82	100	8.5	10	30.5	55	2.5	0.2	5	194
GN.84586	GN 918-40-KVB-R-12	25	40	M6	9	12	20	12	100	8.5	10	30.5	55	2.5	0.2	5	180
GN.84587	GN 918-40-KVB-R-22	25	40	M6	9	12	20	22	100	8.5	10	30.5	55	2.5	0.2	5	182
GN.84588	GN 918-40-KVB-R-27	25	40	M6	9	12	20	27	100	8.5	10	30.5	55	2.5	0.2	5	183
GN.84589	GN 918-40-KVB-R-32	25	40	M6	9	12	20	32	100	8.5	10	30.5	55	2.5	0.2	5	184
GN.84590	GN 918-40-KVB-R-37	25	40	M6	9	12	20	37	100	8.5	10	30.5	55	2.5	0.2	5	185
GN.84591	GN 918-40-KVB-R-42	25	40	M6	9	12	20	42	100	8.5	10	30.5	55	2.5	0.2	5	186
GN.84592	GN 918-40-KVB-R-47	25	40	M6	9	12	20	47	100	8.5	10	30.5	55	2.5	0.2	5	187
GN.84593	GN 918-40-KVB-R-57	25	40	M6	9	12	20	57	100	8.5	10	30.5	55	2.5	0.2	5	189
GN.84594	GN 918-40-KVB-R-62	25	40	M6	9	12	20	62	100	8.5	10	30.5	55	2.5	0.2	5	189
GN.84595	GN 918-40-KVB-R-67	25	40	M6	9	12	20	67	100	8.5	10	30.5	55	2.5	0.2	5	190
GN.84596	GN 918-40-KVB-R-77	25	40	M6	9	12	20	77	100	8.5	10	30.5	55	2.5	0.2	5	192
GN.84597	GN 918-40-KVB-R-82	25	40	M6	9	12	20	82	100	8.5	10	30.5	55	2.5	0.2	5	194
GN.84771	GN 918-50-KVB-L-10	30	50	M8	11	16	24	10	116	10.5	12	34.5	62	2.5	0.2	5	301
GN.84772	GN 918-50-KVB-L-20	30	50	M8	11	16	24	20	116	10.5	12	34.5	62	2.5	0.2	5	303
GN.84773	GN 918-50-KVB-L-30	30	50	M8	11	16	24	30	116	10.5	12	34.5	62	2.5	0.2	5	307
GN.84774	GN 918-50-KVB-L-40	30	50	M8	11	16	24	40	116	10.5	12	34.5	62	2.5	0.2	5	311
GN.84775	GN 918-50-KVB-L-50	30	50	M8	11	16	24	50	116	10.5	12	34.5	62	2.5	0.2	5	315
GN.84776	GN 918-50-KVB-L-60	30	50	M8	11	16	24	60	116	10.5	12	34.5	62	2.5	0.2	5	318
GN.84777	GN 918-50-KVB-L-70	30	50	M8	11	16	24	70	116	10.5	12	34.5	62	2.5	0.2	5	323
GN.84778	GN 918-50-KVB-L-80	30	50	M8	11	16	24	80	116	10.5	12	34.5	62	2.5	0.2	5	326
GN.84779	GN 918-50-KVB-L-90	30	50	M8	11	16	24	90	116	10.5	12	34.5	62	2.5	0.2	5	330
GN.84780	GN 918-50-KVB-L-100	30	50	M8	11	16	24	100	116	10.5	12	34.5	62	2.5	0.2	5	334
GN.84785	GN 918-50-KVB-R-10	30	50	M8	11	16	24	10	116	10.5	12	34.5	62	2.5	0.2	5	301
GN.84786	GN 918-50-KVB-R-20	30	50	M8	11	16	24	20	116	10.5	12	34.5	62	2.5	0.2	5	303
GN.84787	GN 918-50-KVB-R-30	30	50	M8	11	16	24	30	116	10.5	12	34.5	62	2.5	0.2	5	307
GN.84788	GN 918-50-KVB-R-40	30	50	M8	11	16	24	40	116	10.5	12	34.5	62	2.5	0.2	5	311
GN.84789	GN 918-50-KVB-R-50	30	50	M8	11	16	24	50	116	10.5	12	34.5	62	2.5	0.2	5	315
GN.84790	GN 918-50-KVB-R-60	30	50	M8	11	16	24	60	116	10.5	12	34.5	62	2.5	0.2	5	318
GN.84791	GN 918-50-KVB-R-70	30	50	M8	11	16	24	70	116	10.5	12	34.5	62	2.5	0.2	5	323
GN.84792	GN 918-50-KVB-R-80	30	50	M8	11	16	24	80	116	10.5	12	34.5	62	2.5	0.2	5	326
GN.84793	GN 918-50-KVB-R-90	30	50	M8	11	16	24	90	116	10.5	12	34.5	62	2.5	0.2	5	330
GN.84794	GN 918-50-KVB-R-100	30	50	M8	11	16	24	100	116	10.5	12	34.5	62	2.5	0.2	5	334



GN 918-GVB

Codice	Descrizione	d3	d1 -0.5	d2	d4 h9	d5	d6	l1 max	l2	l3	h1	h2	h5	h6-0.1	h7	wmax	△
GN.84506	GN 918-40-GVB-L-12	25	40	M6	9	12	20	12	100	8.5	10	30.5	31	2.5	0.2	5	178
GN.84507	GN 918-40-GVB-L-22	25	40	M6	9	12	20	22	100	8.5	10	30.5	31	2.5	0.2	5	180
GN.84508	GN 918-40-GVB-L-27	25	40	M6	9	12	20	27	100	8.5	10	30.5	31	2.5	0.2	5	182
GN.84509	GN 918-40-GVB-L-32	25	40	M6	9	12	20	32	100	8.5	10	30.5	31	2.5	0.2	5	182
GN.84510	GN 918-40-GVB-L-37	25	40	M6	9	12	20	37	100	8.5	10	30.5	31	2.5	0.2	5	184
GN.84511	GN 918-40-GVB-L-42	25	40	M6	9	12	20	42	100	8.5	10	30.5	31	2.5	0.2	5	184
GN.84512	GN 918-40-GVB-L-47	25	40	M6	9	12	20	47	100	8.5	10	30.5	31	2.5	0.2	5	186
GN.84513	GN 918-40-GVB-L-57	25	40	M6	9	12	20	57	100	8.5	10	30.5	31	2.5	0.2	5	187
GN.84514	GN 918-40-GVB-L-62	25	40	M6	9	12	20	62	100	8.5	10	30.5	31	2.5	0.2	5	188
GN.84515	GN 918-40-GVB-L-67	25	40	M6	9	12	20	67	100	8.5	10	30.5	31	2.5	0.2	5	188
GN.84516	GN 918-40-GVB-L-77	25	40	M6	9	12	20	77	100	8.5	10	30.5	31	2.5	0.2	5	190
GN.84517	GN 918-40-GVB-L-82	25	40	M6	9	12	20	82	100	8.5	10	30.5	31	2.5	0.2	5	192
GN.84526	GN 918-40-GVB-R-12	25	40	M6	9	12	20	12	100	8.5	10	30.5	31	2.5	0.2	5	178
GN.84527	GN 918-40-GVB-R-22	25	40	M6	9	12	20	22	100	8.5	10	30.5	31	2.5	0.2	5	180
GN.84528	GN 918-40-GVB-R-27	25	40	M6	9	12	20	27	100	8.5	10	30.5	31	2.5	0.2	5	182
GN.84529	GN 918-40-GVB-R-32	25	40	M6	9	12	20	32	100	8.5	10	30.5	31	2.5	0.2	5	182
GN.84530	GN 918-40-GVB-R-37	25	40	M6	9	12	20	37	100	8.5	10	30.5	31	2.5	0.2	5	184
GN.84531	GN 918-40-GVB-R-42	25	40	M6	9	12	20	42	100	8.5	10	30.5	31	2.5	0.2	5	184
GN.84532	GN 918-40-GVB-R-47	25	40	M6	9	12	20	47	100	8.5	10	30.5	31	2.5	0.2	5	186
GN.84533	GN 918-40-GVB-R-57	25	40	M6	9	12	20	57	100	8.5	10	30.5	31	2.5	0.2	5	187
GN.84534	GN 918-40-GVB-R-62	25	40	M6	9	12	20	62	100	8.5	10	30.5	31	2.5	0.2	5	188
GN.84535	GN 918-40-GVB-R-67	25	40	M6	9	12	20	67	100	8.5	10	30.5	31	2.5	0.2	5	188
GN.84536	GN 918-40-GVB-R-77	25	40	M6	9	12	20	77	100	8.5	10	30.5	31	2.5	0.2	5	190
GN.84537	GN 918-40-GVB-R-82	25	40	M6	9	12	20	82	100	8.5	10	30.5	31	2.5	0.2	5	192
GN.84706	GN 918-50-GVB-L-10	30	50	M8	11	16	24	10	116	10.5	12	34.5	36	2.5	0.2	5	301
GN.84707	GN 918-50-GVB-L-20	30	50	M8	11	16	24	20	116	10.5	12	34.5	36	2.5	0.2	5	303
GN.84708	GN 918-50-GVB-L-30	30	50	M8	11	16	24	30	116	10.5	12	34.5	36	2.5	0.2	5	307
GN.84709	GN 918-50-GVB-L-40	30	50	M8	11	16	24	40	116	10.5	12	34.5	36	2.5	0.2	5	311
GN.84710	GN 918-50-GVB-L-50	30	50	M8	11	16	24	50	116	10.5	12	34.5	36	2.5	0.2	5	315
GN.84711	GN 918-50-GVB-L-60	30	50	M8	11	16	24	60	116	10.5	12	34.5	36	2.5	0.2	5	318
GN.84712	GN 918-50-GVB-L-70	30	50	M8	11	16	24	70	116	10.5	12	34.5	36	2.5	0.2	5	323
GN.84713	GN 918-50-GVB-L-80	30	50	M8	11	16	24	80	116	10.5	12	34.5	36	2.5	0.2	5	326
GN.84714	GN 918-50-GVB-L-90	30	50	M8	11	16	24	90	116	10.5	12	34.5	36	2.5	0.2	5	330
GN.84716	GN 918-50-GVB-L-100	30	50	M8	11	16	24	100	116	10.5	12	34.5	36	2.5	0.2	5	334
GN.84725	GN 918-50-GVB-R-10	30	50	M8	11	16	24	10	116	10.5	12	34.5	36	2.5	0.2	5	301
GN.84726	GN 918-50-GVB-R-20	30	50	M8	11	16	24	20	116	10.5	12	34.5	36	2.5	0.2	5	303
GN.84727	GN 918-50-GVB-R-30	30	50	M8	11	16	24	30	116	10.5	12	34.5	36	2.5	0.2	5	307
GN.84728	GN 918-50-GVB-R-40	30	50	M8	11	16	24	40	116	10.5	12	34.5	36	2.5	0.2	5	311
GN.84729	GN 918-50-GVB-R-50	30	50	M8	11	16	24	50	116	10.5	12	34.5	36	2.5	0.2	5	315
GN.84730	GN 918-50-GVB-R-60	30	50	M8	11	16	24	60	116	10.5	12	34.5	36	2.5	0.2	5	318
GN.84731	GN 918-50-GVB-R-70	30	50	M8	11	16	24	70	116	10.5	12	34.5	36	2.5	0.2	5	323
GN.84732	GN 918-50-GVB-R-80	30	50	M8	11	16	24	80	116	10.5	12	34.5	36	2.5	0.2	5	326
GN.84733	GN 918-50-GVB-R-90	30	50	M8	11	16	24	90	116	10.5	12	34.5	36	2.5	0.2	5	330
GN.84734	GN 918-50-GVB-R-100	30	50	M8	11	16	24	100	116	10.5	12	34.5	36	2.5	0.2	5	334



GN 918-SKB

Codice	Descrizione	d1 -0.5	d2	d4 h9	d5	d6	l1 max	l3	h1	h3	h6 -0.1	h7	wmax	sw	△
GN.84636	GN 918-40-SKB-L-12	40	M6	9	12	20	12	8.5	10	21	2.5	0.2	5	15	92
GN.84637	GN 918-40-SKB-L-22	40	M6	9	12	20	22	8.5	10	21	2.5	0.2	5	15	94
GN.84638	GN 918-40-SKB-L-27	40	M6	9	12	20	27	8.5	10	21	2.5	0.2	5	15	96
GN.84639	GN 918-40-SKB-L-32	40	M6	9	12	20	32	8.5	10	21	2.5	0.2	5	15	96
GN.84640	GN 918-40-SKB-L-37	40	M6	9	12	20	37	8.5	10	21	2.5	0.2	5	15	98
GN.84641	GN 918-40-SKB-L-42	40	M6	9	12	20	42	8.5	10	21	2.5	0.2	5	15	98
GN.84642	GN 918-40-SKB-L-47	40	M6	9	12	20	47	8.5	10	21	2.5	0.2	5	15	100
GN.84643	GN 918-40-SKB-L-57	40	M6	9	12	20	57	8.5	10	21	2.5	0.2	5	15	101
GN.84644	GN 918-40-SKB-L-62	40	M6	9	12	20	62	8.5	10	21	2.5	0.2	5	15	102
GN.84645	GN 918-40-SKB-L-67	40	M6	9	12	20	67	8.5	10	21	2.5	0.2	5	15	102
GN.84646	GN 918-40-SKB-L-77	40	M6	9	12	20	77	8.5	10	21	2.5	0.2	5	15	104
GN.84647	GN 918-40-SKB-L-82	40	M6	9	12	20	82	8.5	10	21	2.5	0.2	5	15	106
GN.84656	GN 918-40-SKB-R-12	40	M6	9	12	20	12	8.5	10	21	2.5	0.2	5	15	92
GN.84657	GN 918-40-SKB-R-22	40	M6	9	12	20	22	8.5	10	21	2.5	0.2	5	15	94
GN.84658	GN 918-40-SKB-R-27	40	M6	9	12	20	27	8.5	10	21	2.5	0.2	5	15	96
GN.84659	GN 918-40-SKB-R-32	40	M6	9	12	20	32	8.5	10	21	2.5	0.2	5	15	96
GN.84660	GN 918-40-SKB-R-37	40	M6	9	12	20	37	8.5	10	21	2.5	0.2	5	15	98
GN.84661	GN 918-40-SKB-R-42	40	M6	9	12	20	42	8.5	10	21	2.5	0.2	5	15	98
GN.84662	GN 918-40-SKB-R-47	40	M6	9	12	20	47	8.5	10	21	2.5	0.2	5	15	100
GN.84663	GN 918-40-SKB-R-57	40	M6	9	12	20	57	8.5	10	21	2.5	0.2	5	15	101
GN.84664	GN 918-40-SKB-R-62	40	M6	9	12	20	62	8.5	10	21	2.5	0.2	5	15	102
GN.84665	GN 918-40-SKB-R-67	40	M6	9	12	20	67	8.5	10	21	2.5	0.2	5	15	102
GN.84666	GN 918-40-SKB-R-77	40	M6	9	12	20	77	8.5	10	21	2.5	0.2	5	15	104
GN.84667	GN 918-40-SKB-R-82	40	M6	9	12	20	82	8.5	10	21	2.5	0.2	5	15	106
GN.84835	GN 918-50-SKB-L-10	50	M8	11	16	24	10	10.5	12	24	2.5	0.2	5	19	165
GN.84836	GN 918-50-SKB-L-20	50	M8	11	16	24	20	10.5	12	24	2.5	0.2	5	19	167
GN.84837	GN 918-50-SKB-L-30	50	M8	11	16	24	30	10.5	12	24	2.5	0.2	5	19	171
GN.84838	GN 918-50-SKB-L-40	50	M8	11	16	24	40	10.5	12	24	2.5	0.2	5	19	175
GN.84839	GN 918-50-SKB-L-50	50	M8	11	16	24	50	10.5	12	24	2.5	0.2	5	19	179
GN.84840	GN 918-50-SKB-L-60	50	M8	11	16	24	60	10.5	12	24	2.5	0.2	5	19	182
GN.84841	GN 918-50-SKB-L-70	50	M8	11	16	24	70	10.5	12	24	2.5	0.2	5	19	187
GN.84842	GN 918-50-SKB-L-80	50	M8	11	16	24	80	10.5	12	24	2.5	0.2	5	19	190
GN.84843	GN 918-50-SKB-L-90	50	M8	11	16	24	90	10.5	12	24	2.5	0.2	5	19	194
GN.84844	GN 918-50-SKB-L-100	50	M8	11	16	24	100	10.5	12	24	2.5	0.2	5	19	198
GN.84855	GN 918-50-SKB-R-10	50	M8	11	16	24	10	10.5	12	24	2.5	0.2	5	19	165
GN.84856	GN 918-50-SKB-R-20	50	M8	11	16	24	20	10.5	12	24	2.5	0.2	5	19	167
GN.84857	GN 918-50-SKB-R-30	50	M8	11	16	24	30	10.5	12	24	2.5	0.2	5	19	171
GN.84858	GN 918-50-SKB-R-40	50	M8	11	16	24	40	10.5	12	24	2.5	0.2	5	19	175
GN.84859	GN 918-50-SKB-R-50	50	M8	11	16	24	50	10.5	12	24	2.5	0.2	5	19	179
GN.84860	GN 918-50-SKB-R-60	50	M8	11	16	24	60	10.5	12	24	2.5	0.2	5	19	182
GN.84861	GN 918-50-SKB-R-70	50	M8	11	16	24	70	10.5	12	24	2.5	0.2	5	19	187
GN.84862	GN 918-50-SKB-R-80	50	M8	11	16	24	80	10.5	12	24	2.5	0.2	5	19	190
GN.84863	GN 918-50-SKB-R-90	50	M8	11	16	24	90	10.5	12	24	2.5	0.2	5	19	194
GN.84864	GN 918-50-SKB-R-100	50	M8	11	16	24	100	10.5	12	24	2.5	0.2	5	19	198