

MATERIAL

Glass-fibre reinforced polyamide based (PA) SUPER-technopolymer, black colour, matte finish.

ROTATING PIN


Self-lubricating glass-fibre reinforced polyamide based (PA) technopolymer, black colour.

STANDARD EXECUTIONS

- Pass-through holes for countersunk head screws.
- **CFMY-D**: rotation pin fitted on the right hinge body.
 - **CFMY-S**: rotation pin fitted on the left hinge body.

ROTATION ANGLE (APPROXIMATE VALUE)


Max 270° (-90° and +180° being 0° the condition where the two interconnected surfaces are on the same plane).
Do not exceed the rotation angle limit so as not to prejudice the hinge mechanical performance.
To choose the convenient type and the right number of hinges for your application, see the Guidelines (see page 952).



Resistance tests			
		Axial Stress	Radial Stress
		90° Angled Stress	
Description	Max limit static load Sa [N]	Max limit static load Sr [N]	Max limit static load S90 [N]
CFMY.40	800	500	400
CFMY.50	1200	1100	700
CFMY.60	2050	1600	1250

The max static load is the value above which the material may break thus prejudicing the hinge functionality. Obviously, a suitable factor, according to the importance and the safety level of the specific application must be applied to this value.

Conversion Table	
1 mm = 0.039 inch	
mm	inch
40	1.57
50	1.97
60	2.36



METRIC

CFMY-D

Code	Description	L	f±0.25	H	h1	h2	b1	d	d3	d4	C# [Nm]	⚖
425981	CFMY.40 SH-4-D	40	25	9	5.5	5	14	4	4.5	8.5	3	14
425971	CFMY.50 SH-6-D	50	30	11.5	6.5	6	18	6	6.5	12.5	5	27
425965	CFMY.60 SH-6-D	60	36	15	8.5	8	26	6	6.5	12.5	5	44
425961	CFMY.60-SH-8-D	60	36	15	8.5	8	26	8	8.5	16.5	5	41

CFMY-S

Code	Description	L	f±0.25	H	h1	h2	b1	d	d3	d4	C# [Nm]	⚖
425982	CFMY.40 SH-4-S	40	25	9	5.5	5	14	4	4.5	8.5	3	14
425972	CFMY.50 SH-6-S	50	30	11.5	6.5	6	18	6	6.5	12.5	5	28
425966	CFMY.60 SH-6-S	60	36	15	8.5	8	26	6	6.5	12.5	5	44
425962	CFMY.60-SH-8-S	60	36	15	8.5	8	26	8	8.5	16.5	5	41

Suggested tightening torque for assembly screws.