

DIN 98 | Vridbara handtag

Stål



MATERIAL



Blankförzinkat stål.

STANDARDUTFÖRANDE

Gängad tapp i förzinkat stål, invändig sexkant i den gängade änden.

SPECIALUTFÖRANDE PÅ FÖRFRÅGAN

Slät tapp h8 (DIN 98-D).



Kod	Benämning	d1	d3	d4 h13	l1	l2	l3	⚖️
GN.11105	DIN 98-ST-16-E	16	M6	10	49	11	5.5	55
GN.11125	DIN 98-ST-20-E	20	M8	13	61	13	6	104
GN.11145	DIN 98-ST-25-E	25	M10	16	75	14	8	187
GN.11165	DIN 98-ST-32-E	32	M12	20	95	21	10.5	387
GN.11175	DIN 98-ST-36-E	36	M16	22	106	26	11	541