

MATERIAL

Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.

STANDARD EXECUTIONS


- **CT.476-B:** brass boss, threaded blind hole.
- **CT.476-p:** zinc-plated steel threaded stud with chamfered flat end as in ISO 4753 (see Technical Data on page A-10).

FEATURES AND APPLICATIONS

These wing knobs allow high tightening torque values.



ELESA Original design



CT.476-B

INCH

Code	Description	D	d2B	L	b	h	C# [ft lb]	⚖
908302	CT.476/25 B-10-32	1.02	10-32	0.51	0.43	0.24	6	0.01
908351	CT.476/30 B-1/4-20	1.26	1/4-20	0.59	0.51	0.31	11	0.02
908452	CT.476/40 B-5/16-18	1.57	5/16-18	0.67	0.61	0.31	18	0.02
908502	CT.476/48 B-5/16-18	1.89	5/16-18	0.75	0.75	0.39	22	0.03
908552	CT.476/56 B-3/8-16	2.2	3/8-16	0.91	0.83	0.51	24	0.04

CT.476-p

INCH

Code	Description	D	d2A	L	l	b	C# [ft lb]	⚖
908313	CT.476/25 p-10-32x1/2	1.02	10-32	0.51	0.500	0.43	6	0.02
908315	CT.476/25 p-10-32x3/4	1.02	10-32	0.51	0.750	0.43	6	0.02
908373	CT.476/30 p-10-32x1/2	1.26	10-32	0.59	0.500	0.51	9	0.02
908375	CT.476/30 p-10-32x3/4	1.26	10-32	0.59	0.750	0.51	9	0.02
908363	CT.476/30 p-1/4-20x1/2	1.26	1/4-20	0.59	0.500	0.51	10	0.02
908365	CT.476/30 p-1/4-20x3/4	1.26	1/4-20	0.59	0.750	0.51	10	0.03
908367	CT.476/30 p-1/4-20x1	1.26	1/4-20	0.59	1.000	0.51	10	0.03
908465	CT.476/40 p-5/16-18x3/4	1.57	5/16-18	0.67	0.750	0.61	13	0.04
908467	CT.476/40 p-5/16-18x1	1.57	5/16-18	0.67	1.000	0.61	13	0.04
908469	CT.476/40 p-5/16-18x1¼	1.57	5/16-18	0.67	1.250	0.61	13	0.04

"Max limit Tightening torque" means the max torque value at which the metal insert, in normal conditions of use, is perfectly and strongly anchored to the plastic material.