

MATERIAL


- **DIN 467:** turned black-oxide steel.
- **DIN 467-NI:** AISI 303 stainless steel, sandblasted matte finish.

STANDARD EXECUTION

Threaded pass-through hole.



Conversion Table	
1 mm = 0.039 inch	
d2	
mm	inch
12	0.47
16	0.63
20	0.79
24	0.94
30	1.18
36	1.41
40	1.57



DIN 467

METRIC

Code	Description	d2	d1	d3	h	k	⚖️
GN.29601	DIN 467-M3	12	M3	6	3	2.5	2
GN.29611	DIN 467-M4	16	M4	8	4	3.5	5
GN.29621	DIN 467-M5	20	M5	10	5	4	10
GN.29631	DIN 467-M6	24	M6	12	6	5	18
GN.29641	DIN 467-M8	30	M8	16	8	6	33
GN.29651	DIN 467-M10	36	M10	20	10	8	63
GN.29661	DIN 467-M12	40	M12	22	12	10	93

DIN 467-NI

INOX
STAINLESS
STEEL

METRIC

Code	Description	d2	d1	d3	h	k	⚖️
GN.29679	DIN 467-M3-NI	12	M3	6	3	2.5	2
GN.29681	DIN 467-M4-NI	16	M4	8	4	3.5	5
GN.29683	DIN 467-M5-NI	20	M5	10	5	4	10
GN.29685	DIN 467-M6-NI	24	M6	12	6	5	19
GN.29687	DIN 467-M8-NI	30	M8	16	8	6	35
GN.29689	DIN 467-M10-NI	36	M10	20	10	8	69

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

Clamping knobs