

MATERIAL

Steel

Hardened steel (62 ±2 HRC).

Ground coupling dimension d1 / d2.

Stainless steel AISI 440B **NI**


Hardened stainless steel (55 +4 HRC).

Ground coupling dimension d1 / d2.

FEATURES AND APPLICATIONS

d2 external diameter n6 tolerance assures a perfect clamping in the mounting holes in H7 tolerance.

Conversion Table 1 mm = 0.039 inch			
d3			
mm	inch	mm	inch
6	0.23	15	0.59
7	0.27	18	0.70
8	0.31	22	0.86
9	0.35	26	1.01
10	0.39	30	1.17
11	0.43		
13	0.51		



METRIC

DIN 172

Code	Description	d1 F7	d2 n6	d3	l1	l2	△
GN.17601	DIN 172-B0,6-6-A	B 0.6	3	6	6	2	1
GN.17602	DIN 172-B0,7-6-A	B 0.7	3	6	6	2	1
GN.17603	DIN 172-B0,8-6-A	B 0.8	3	6	6	2	1
GN.17604	DIN 172-B0,9-6-A	B 0.9	3	6	6	2	1
GN.17605	DIN 172-B0,9-9-A	B 0.9	3	6	9	2	1
GN.17611	DIN 172-B1,6-6-A	B 1	3	6	6	2	1
GN.17628	DIN 172-B1,9-9-A	B 1	3	6	9	2	1
GN.17612	DIN 172-B1,1-6-A	B 1.1	4	7	6	2	1
GN.17613	DIN 172-B1,1-9-A	B 1.1	4	7	9	2	1
GN.17614	DIN 172-B1,2-6-A	B 1.2	4	7	6	2	1
GN.17615	DIN 172-B1,2-9-A	B 1.2	4	7	9	2	1
GN.17616	DIN 172-B1,3-6-A	B 1.3	4	7	6	2	1
GN.17617	DIN 172-B1,3-9-A	B 1.3	4	7	9	2	2
GN.17618	DIN 172-B1,4-6-A	B 1.4	4	7	6	2	1
GN.17619	DIN 172-B1,4-9-A	B 1.4	4	7	9	2	1
GN.17620	DIN 172-B1,5-6-A	B 1.5	4	7	6	2	1
GN.17621	DIN 172-B1,5-9-A	B 1.5	4	7	9	2	2
GN.17622	DIN 172-B1,6-6-A	B 1.6	4	7	6	2	1
GN.17623	DIN 172-B1,6-9-A	B 1.6	4	7	9	2	2
GN.17624	DIN 172-B1,7-6-A	B 1.7	4	7	6	2	1
GN.17625	DIN 172-B1,7-9-A	B 1.7	4	7	9	2	1
GN.17626	DIN 172-B1,8-6-A	B 1.8	4	7	6	2	1
GN.17627	DIN 172-B1,8-9-A	B 1.8	4	7	9	2	1
GN.17629	DIN 172-B1,9-6-A	B 1.9	5	8	6	2	1
GN.17630	DIN 172-B1,9-9-A	B 1.9	5	8	9	2	2
GN.12750	DIN 172-B2,6-A	B 2	5	8	6	2	1
GN.12751	DIN 172-B2,9-A	B 2	5	8	9	2	2
GN.12752	DIN 172-B2,1-6-A	B 2.1	5	8	6	2	1
GN.12753	DIN 172-B2,1-9-A	B 2.1	5	8	9	2	2
GN.17640	DIN 172-B2,2-6-A	B 2.2	5	8	6	2	1
GN.17641	DIN 172-B2,2-9-A	B 2.2	5	8	9	2	2
GN.17642	DIN 172-B2,3-6-A	B 2.3	5	8	6	2	1
GN.17643	DIN 172-B2,3-9-A	B 2.3	5	8	9	2	2
GN.17644	DIN 172-B2,4-6-A	B 2.4	5	8	6	2	1
GN.17645	DIN 172-B2,4-9-A	B 2.4	5	8	9	2	1
GN.12754	DIN 172-B2,5-6-A	B 2.5	5	8	6	2	1

Code	Description	d1 F7	d2 n6	d3	l1	l2	△
GN.12755	DIN 172-B2,5-9-A	B 2.5	5	8	9	2	1
GN.17646	DIN 172-B2,6-6-A	B 2.6	5	8	6	2	1
GN.17647	DIN 172-B2,6-9-A	B 2.6	5	8	9	2	1
GN.17648	DIN 172-B2,7-8-A	B 2.7	6	9	8	2.5	2
GN.17649	DIN 172-B2,7-12-A	B 2.7	6	9	12	2.5	3
GN.17650	DIN 172-B2,7-16-A	B 2.7	6	9	16	2.5	3
GN.17651	DIN 172-B2,8-8-A	B 2.8	6	9	8	2.5	2
GN.17652	DIN 172-B2,8-12-A	B 2.8	6	9	12	2.5	3
GN.17653	DIN 172-B2,8-16-A	B 2.8	6	9	16	2.5	3
GN.17654	DIN 172-B2,9-8-A	B 2.9	6	9	8	2.5	2
GN.17655	DIN 172-B2,9-12-A	B 2.9	6	9	12	2.5	2
GN.17656	DIN 172-B2,9-16-A	B 2.9	6	9	16	2.5	3
GN.12756	DIN 172-B3,8-A	B 3	6	9	8	2.5	2
GN.12757	DIN 172-B3,12-A	B 3	6	9	12	2.5	3
GN.12711	DIN 172-B3,16-A	B 3	6	9	16	2.5	5
GN.12758	DIN 172-B3,1-8-A	B 3.1	6	9	8	2.5	2
GN.12759	DIN 172-B3,1-12-A	B 3.1	6	9	12	2.5	3
GN.12712	DIN 172-B3,1-16-A	B 3.1	6	9	16	2.5	2
GN.17661	DIN 172-B3,2-8-A	B 3.2	6	9	8	2.5	2
GN.17662	DIN 172-B3,2-12-A	B 3.2	6	9	12	2.5	2
GN.17663	DIN 172-B3,2-16-A	B 3.2	6	9	16	2.5	4
GN.12760	DIN 172-B3,3-8-A	B 3.3	6	9	8	2.5	2
GN.12761	DIN 172-B3,3-12-A	B 3.3	6	9	12	2.5	2
GN.12713	DIN 172-B3,3-16-A	B 3.3	6	9	16	2.5	4
GN.17664	DIN 172-B3,4-8-A	B 3.4	7	10	8	2.5	2
GN.17665	DIN 172-B3,4-12-A	B 3.4	7	10	12	2.5	3
GN.17666	DIN 172-B3,4-16-A	B 3.4	7	10	16	2.5	4
GN.12762	DIN 172-B3,5-8-A	B 3.5	7	10	8	2.5	2
GN.12763	DIN 172-B3,5-12-A	B 3.5	7	10	12	2.5	3
GN.12714	DIN 172-B3,5-16-A	B 3.5	7	10	16	2.5	4
GN.17667	DIN 172-B3,6-8-A	B 3.6	7	10	8	2.5	2
GN.17668	DIN 172-B3,6-12-A	B 3.6	7	10	12	2.5	3
GN.17669	DIN 172-B3,6-16-A	B 3.6	7	10	16	2.5	4
GN.17670	DIN 172-B3,7-8-A	B 3.7	7	10	8	2.5	2
GN.17671	DIN 172-B3,7-12-A	B 3.7	7	10	12	2.5	3
GN.17672	DIN 172-B3,7-16-A	B 3.7	7	10	16	2.5	4
GN.12764	DIN 172-B3,8-8-A	B 3.8	7	10	8	2.5	3
GN.12765	DIN 172-B3,8-12-A	B 3.8	7	10	12	2.5	3
GN.12715	DIN 172-B3,8-16-A	B 3.8	7	10	16	2.5	5
GN.17673	DIN 172-B3,9-8-A	B 3.9	7	10	8	2.5	2
GN.17674	DIN 172-B3,9-12-A	B 3.9	7	10	12	2.5	3
GN.17675	DIN 172-B3,9-16-A	B 3.9	7	10	16	2.5	4

DIN 172

Code	Description	d1 F7	d2 n6	d3	l1	l2	
GN.12766	DIN 172-B4-8-A	B 4	7	10	8	2.5	2
GN.12767	DIN 172-B4-12-A	B 4	7	10	12	2.5	4
GN.12716	DIN 172-B4-16-A	B 4	7	10	16	2.5	4
GN.12768	DIN 172-B4,1-8-A	B 4.1	8	11	8	2.5	3
GN.12769	DIN 172-B4,1-12-A	B 4.1	8	11	12	2.5	4
GN.12717	DIN 172-B4,1-16-A	B 4.1	8	11	16	2.5	6
GN.12770	DIN 172-B4,2-8-A	B 4.2	8	11	8	2.5	3
GN.12771	DIN 172-B4,2-12-A	B 4.2	8	11	12	2.5	4
GN.12718	DIN 172-B4,2-16-A	B 4.2	8	11	16	2.5	2
GN.17681	DIN 172-B4,3-8-A	B 4.3	8	11	8	2.5	3
GN.17682	DIN 172-B4,3-12-A	B 4.3	8	11	12	2.5	4
GN.17683	DIN 172-B4,3-16-A	B 4.3	8	11	16	2.5	5
GN.17684	DIN 172-B4,4-8-A	B 4.4	8	11	8	2.5	3
GN.17685	DIN 172-B4,4-12-A	B 4.4	8	11	12	2.5	4
GN.17686	DIN 172-B4,4-16-A	B 4.4	8	11	16	2.5	5
GN.12772	DIN 172-B4,5-8-A	B 4.5	8	11	8	2.5	3
GN.12773	DIN 172-B4,5-12-A	B 4.5	8	11	12	2.5	4
GN.12719	DIN 172-B4,5-16-A	B 4.5	8	11	16	2.5	2
GN.17687	DIN 172-B4,6-8-A	B 4.6	8	11	8	2.5	3
GN.17688	DIN 172-B4,6-12-A	B 4.6	8	11	12	2.5	4
GN.17689	DIN 172-B4,6-16-A	B 4.6	8	11	16	2.5	5
GN.17690	DIN 172-B4,7-8-A	B 4.7	8	11	8	2.5	3
GN.17691	DIN 172-B4,7-12-A	B 4.7	8	11	12	2.5	4
GN.17692	DIN 172-B4,7-16-A	B 4.7	8	11	16	2.5	5
GN.12774	DIN 172-B4,8-8-A	B 4.8	8	11	8	2.5	3
GN.12775	DIN 172-B4,8-12-A	B 4.8	8	11	12	2.5	4
GN.12720	DIN 172-B4,8-16-A	B 4.8	8	11	16	2.5	5
GN.17693	DIN 172-B4,9-8-A	B 4.9	8	11	8	2.5	3
GN.17694	DIN 172-B4,9-12-A	B 4.9	8	11	12	2.5	4
GN.17695	DIN 172-B4,9-16-A	B 4.9	8	11	16	2.5	5
GN.12776	DIN 172-B5-8-A	B 5	8	11	8	2.5	3
GN.12777	DIN 172-B5-12-A	B 5	8	11	12	2.5	4
GN.12721	DIN 172-B5-16-A	B 5	8	11	16	2.5	2
GN.12778	DIN 172-B5,1-10-A	B 5.1	10	13	10	3	6
GN.12779	DIN 172-B5,1-16-A	B 5.1	10	13	16	3	8
GN.12722	DIN 172-B5,1-20-A	B 5.1	10	13	20	3	10
GN.17701	DIN 172-B5,2-10-A	B 5.2	10	13	10	3	6
GN.17702	DIN 172-B5,2-16-A	B 5.2	10	13	16	3	8
GN.17703	DIN 172-B5,2-20-A	B 5.2	10	13	20	3	10
GN.17704	DIN 172-B5,3-10-A	B 5.3	10	13	10	3	6
GN.17705	DIN 172-B5,3-16-A	B 5.3	10	13	16	3	8
GN.17706	DIN 172-B5,3-20-A	B 5.3	10	13	20	3	10
GN.17707	DIN 172-B5,4-10-A	B 5.4	10	13	10	3	5
GN.17708	DIN 172-B5,4-16-A	B 5.4	10	13	16	3	8
GN.17709	DIN 172-B5,4-20-A	B 5.4	10	13	20	3	10
GN.12780	DIN 172-B5,5-10-A	B 5.5	10	13	10	3	5
GN.12781	DIN 172-B5,5-16-A	B 5.5	10	13	16	3	8
GN.12723	DIN 172-B5,5-20-A	B 5.5	10	13	20	3	2
GN.17710	DIN 172-B5,6-10-A	B 5.6	10	13	10	3	5
GN.17711	DIN 172-B5,6-16-A	B 5.6	10	13	16	3	8
GN.17712	DIN 172-B5,6-20-A	B 5.6	10	13	20	3	10
GN.17713	DIN 172-B5,7-10-A	B 5.7	10	13	10	3	5
GN.17714	DIN 172-B5,7-16-A	B 5.7	10	13	16	3	8
GN.17715	DIN 172-B5,7-20-A	B 5.7	10	13	20	3	9
GN.12782	DIN 172-B5,8-10-A	B 5.8	10	13	10	3	5
GN.12783	DIN 172-B5,8-16-A	B 5.8	10	13	16	3	8
GN.12724	DIN 172-B5,8-20-A	B 5.8	10	13	20	3	2
GN.17716	DIN 172-B5,9-10-A	B 5.9	10	13	10	3	5
GN.17717	DIN 172-B5,9-16-A	B 5.9	10	13	16	3	7
GN.17718	DIN 172-B5,9-20-A	B 5.9	10	13	20	3	9

METRIC

Code	Description	d1 F7	d2 n6	d3	l1	l2	
GN.12784	DIN 172-B6-10-A	B 6	10	13	10	3	5
GN.12785	DIN 172-B6-16-A	B 6	10	13	16	3	7
GN.12725	DIN 172-B6-20-A	B 6	10	13	20	3	9
GN.12786	DIN 172-B6,1-10-A	B 6.1	12	15	10	3	8
GN.12787	DIN 172-B6,1-16-A	B 6.1	12	15	16	3	12
GN.12726	DIN 172-B6,1-20-A	B 6.1	12	15	20	3	15
GN.17721	DIN 172-B6,2-10-A	B 6.2	12	15	10	3	8
GN.17722	DIN 172-B6,2-16-A	B 6.2	12	15	16	3	11
GN.17723	DIN 172-B6,2-20-A	B 6.2	12	15	20	3	14
GN.17724	DIN 172-B6,3-10-A	B 6.3	12	15	10	3	8
GN.17725	DIN 172-B6,3-16-A	B 6.3	12	15	16	3	11
GN.17726	DIN 172-B6,3-20-A	B 6.3	12	15	20	3	14
GN.17727	DIN 172-B6,4-10-A	B 6.4	12	15	10	3	8
GN.17728	DIN 172-B6,4-16-A	B 6.4	12	15	16	3	11
GN.17729	DIN 172-B6,4-20-A	B 6.4	12	15	20	3	14
GN.12788	DIN 172-B6,5-10-A	B 6.5	12	15	10	3	7
GN.12789	DIN 172-B6,5-16-A	B 6.5	12	15	16	3	11
GN.12727	DIN 172-B6,5-20-A	B 6.5	12	15	20	3	14
GN.17730	DIN 172-B6,6-10-A	B 6.6	12	15	10	3	8
GN.17731	DIN 172-B6,6-16-A	B 6.6	12	15	16	3	11
GN.17732	DIN 172-B6,6-20-A	B 6.6	12	15	20	3	13
GN.17733	DIN 172-B6,7-10-A	B 6.7	12	15	10	3	7
GN.17734	DIN 172-B6,7-16-A	B 6.7	12	15	16	3	11
GN.17735	DIN 172-B6,7-20-A	B 6.7	12	15	20	3	13
GN.12790	DIN 172-B6,8-10-A	B 6.8	12	15	10	3	7
GN.12791	DIN 172-B6,8-16-A	B 6.8	12	15	16	3	11
GN.12728	DIN 172-B6,8-20-A	B 6.8	12	15	20	3	13
GN.17736	DIN 172-B6,9-10-A	B 6.9	12	15	10	3	7
GN.17737	DIN 172-B6,9-16-A	B 6.9	12	15	16	3	10
GN.17738	DIN 172-B6,9-20-A	B 6.9	12	15	20	3	13
GN.12792	DIN 172-B7-10-A	B 7	12	15	10	3	7
GN.12793	DIN 172-B7-16-A	B 7	12	15	16	3	10
GN.12729	DIN 172-B7-20-A	B 7	12	15	20	3	12
GN.17751	DIN 172-B7,1-10-A	B 7.1	12	15	10	3	8
GN.17752	DIN 172-B7,1-16-A	B 7.1	12	15	16	3	10
GN.17753	DIN 172-B7,1-20-A	B 7.1	12	15	20	3	13
GN.17754	DIN 172-B7,2-10-A	B 7.2	12	15	10	3	7
GN.17755	DIN 172-B7,2-16-A	B 7.2	12	15	16	3	10
GN.17756	DIN 172-B7,2-20-A	B 7.2	12	15	20	3	12
GN.17757	DIN 172-B7,3-10-A	B 7.3	12	15	10	3	7
GN.17758	DIN 172-B7,3-16-A	B 7.3	12	15	16	3	10
GN.17759	DIN 172-B7,3-20-A	B 7.3	12	15	20	3	12
GN.17760	DIN 172-B7,4-10-A	B 7.4	12	15	10	3	6
GN.17761	DIN 172-B7,4-16-A	B 7.4	12	15	16	3	10
GN.17762	DIN 172-B7,4-20-A	B 7.4	12	15	20	3	12
GN.12794	DIN 172-B7,5-10-A	B 7.5	12	15	10	3	7
GN.12795	DIN 172-B7,5-16-A	B 7.5	12	15	16	3	11
GN.12730	DIN 172-B7,5-20-A	B 7.5	12	15	20	3	13
GN.17763	DIN 172-B7,6-10-A	B 7.6	12	15	10	3	6
GN.17764	DIN 172-B7,6-16-A	B 7.6	12	15	16	3	10
GN.17765	DIN 172-B7,6-20-A	B 7.6	12	15	20	3	12
GN.17766	DIN 172-B7,7-10-A	B 7.7	12	15	10	3	6
GN.17767	DIN 172-B7,7-16-A	B 7.7	12	15	16	3	9
GN.17768	DIN 172-B7,7-20-A	B 7.7	12	15	20	3	14
GN.12796	DIN 172-B7,8-10-A	B 7.8	12	15	10	3	6
GN.12797	DIN 172-B7,8-16-A	B 7.8	12	15	16	3	9
GN.12731	DIN 172-B7,8-20-A	B 7.8	12	15	20	3	12
GN.17769	DIN 172-B7,9-10-A	B 7.9	12	15	10	3	6
GN.17770	DIN 172-B7,9-16-A	B 7.9	12	15	16	3	9
GN.17771	DIN 172-B7,9-20-A	B 7.9	12	15	20	3	11

METRIC

DIN 172

Code	Description	d1	F7	d2	n6	d3	l1	l2	⚖
GN.12798	DIN 172-B8-10-A	B 8	12	15	10	3	6		
GN.12799	DIN 172-B8-16-A	B 8	12	15	16	3	9		
GN.12732	DIN 172-B8-20-A	B 8	12	15	20	3	11		
GN.12800	DIN 172-B8,1-12-A	B 8.1	15	18	12	3	13		
GN.12801	DIN 172-B8,1-20-A	B 8.1	15	18	20	3	21		
GN.12733	DIN 172-B8,1-25-A	B 8.1	15	18	25	3	26		
GN.17776	DIN 172-B8,2-12-A	B 8.2	15	18	12	3	13		
GN.17777	DIN 172-B8,2-20-A	B 8.2	15	18	20	3	20		
GN.17778	DIN 172-B8,2-25-A	B 8.2	15	18	25	3	25		
GN.17779	DIN 172-B8,3-12-A	B 8.3	15	18	12	3	13		
GN.17780	DIN 172-B8,3-20-A	B 8.3	15	18	20	3	20		
GN.17781	DIN 172-B8,3-25-A	B 8.3	15	18	25	3	25		
GN.17782	DIN 172-B8,4-12-A	B 8.4	15	18	12	3	13		
GN.17783	DIN 172-B8,4-20-A	B 8.4	15	18	20	3	20		
GN.17784	DIN 172-B8,4-25-A	B 8.4	15	18	25	3	25		
GN.12802	DIN 172-B8,5-12-A	B 8.5	15	18	12	3	12		
GN.12803	DIN 172-B8,5-20-A	B 8.5	15	18	20	3	20		
GN.12734	DIN 172-B8,5-25-A	B 8.5	15	18	25	3	24		
GN.17785	DIN 172-B8,6-12-A	B 8.6	15	18	12	3	12		
GN.17786	DIN 172-B8,6-20-A	B 8.6	15	18	20	3	20		
GN.17787	DIN 172-B8,6-25-A	B 8.6	15	18	25	3	24		
GN.17788	DIN 172-B8,7-12-A	B 8.7	15	18	12	3	12		
GN.17789	DIN 172-B8,7-20-A	B 8.7	15	18	20	3	20		
GN.17790	DIN 172-B8,7-25-A	B 8.7	15	18	25	3	24		
GN.17791	DIN 172-B8,8-12-A	B 8.8	15	18	12	3	12		
GN.17792	DIN 172-B8,8-20-A	B 8.8	15	18	20	3	20		
GN.17793	DIN 172-B8,8-25-A	B 8.8	15	18	25	3	24		
GN.17794	DIN 172-B8,9-12-A	B 8.9	15	18	12	3	12		
GN.17795	DIN 172-B8,9-20-A	B 8.9	15	18	20	3	19		
GN.17796	DIN 172-B8,9-25-A	B 8.9	15	18	25	3	24		
GN.12804	DIN 172-B9-12-A	B 9	15	18	12	3	12		
GN.12805	DIN 172-B9-20-A	B 9	15	18	20	3	19		
GN.12737	DIN 172-B9-25-A	B 9	15	18	25	3	24		
GN.17801	DIN 172-B9,1-12-A	B 9.1	15	18	12	3	12		
GN.17802	DIN 172-B9,1-20-A	B 9.1	15	18	20	3	19		
GN.17803	DIN 172-B9,1-25-A	B 9.1	15	18	25	3	23		
GN.17804	DIN 172-B9,2-12-A	B 9.2	15	18	12	3	12		
GN.17805	DIN 172-B9,2-20-A	B 9.2	15	18	20	3	18		
GN.17806	DIN 172-B9,2-25-A	B 9.2	15	18	25	3	23		
GN.17807	DIN 172-B9,3-12-A	B 9.3	15	18	12	3	11		
GN.17808	DIN 172-B9,3-20-A	B 9.3	15	18	20	3	18		
GN.17809	DIN 172-B9,3-25-A	B 9.3	15	18	25	3	22		
GN.17810	DIN 172-B9,4-12-A	B 9.4	15	18	12	3	11		
GN.17811	DIN 172-B9,4-20-A	B 9.4	15	18	20	3	18		
GN.17812	DIN 172-B9,4-25-A	B 9.4	15	18	25	3	22		
GN.12806	DIN 172-B9,5-12-A	B 9.5	15	18	12	3	11		
GN.12807	DIN 172-B9,5-20-A	B 9.5	15	18	20	3	18		
GN.12735	DIN 172-B9,5-25-A	B 9.5	15	18	25	3	23		
GN.17813	DIN 172-B9,6-12-A	B 9.6	15	18	12	3	11		
GN.17814	DIN 172-B9,6-20-A	B 9.6	15	18	20	3	18		
GN.17815	DIN 172-B9,6-25-A	B 9.6	15	18	25	3	22		
GN.17816	DIN 172-B9,7-12-A	B 9.7	15	18	12	3	11		
GN.17817	DIN 172-B9,7-20-A	B 9.7	15	18	20	3	17		
GN.17818	DIN 172-B9,7-25-A	B 9.7	15	18	25	3	21		
GN.12808	DIN 172-B9,8-12-A	B 9.8	15	18	12	3	11		
GN.12809	DIN 172-B9,8-20-A	B 9.8	15	18	20	3	17		
GN.12736	DIN 172-B9,8-25-A	B 9.8	15	18	25	3	22		
GN.17819	DIN 172-B9,9-12-A	B 9.9	15	18	12	3	11		
GN.17820	DIN 172-B9,9-20-A	B 9.9	15	18	20	3	17		
GN.17821	DIN 172-B9,9-25-A	B 9.9	15	18	25	3	20		

Code	Description	d1	F7	d2	n6	d3	l1	l2	⚖
GN.12810	DIN 172-B10-12-A	B 10	15	18	12	3	10		
GN.12811	DIN 172-B10-20-A	B 10	15	18	20	3	17		
GN.12738	DIN 172-B10-25-A	B 10	15	18	25	3	21		
GN.12812	DIN 172-B10,1-12-A	B 10.1	18	22	12	4	20		
GN.12813	DIN 172-B10,1-20-A	B 10.1	18	22	20	4	30		
GN.12739	DIN 172-B10,1-25-A	B 10.1	18	22	25	4	35		
GN.12814	DIN 172-B10,2-12-A	B 10.2	18	22	12	4	20		
GN.12815	DIN 172-B10,2-20-A	B 10.2	18	22	20	4	30		
GN.12740	DIN 172-B10,2-25-A	B 10.2	18	22	25	4	37		
GN.17826	DIN 172-B10,3-12-A	B 10.3	18	22	12	4	19		
GN.17827	DIN 172-B10,3-20-A	B 10.3	18	22	20	4	30		
GN.17828	DIN 172-B10,3-25-A	B 10.3	18	22	25	4	36		
GN.17829	DIN 172-B10,4-12-A	B 10.4	18	22	12	4	19		
GN.17830	DIN 172-B10,4-20-A	B 10.4	18	22	20	4	30		
GN.17831	DIN 172-B10,4-25-A	B 10.4	18	22	25	4	38		
GN.12816	DIN 172-B10,5-12-A	B 10.5	18	22	12	4	19		
GN.12817	DIN 172-B10,5-20-A	B 10.5	18	22	20	4	29		
GN.12741	DIN 172-B10,5-25-A	B 10.5	18	22	25	4	36		
GN.17832	DIN 172-B10,6-12-A	B 10.6	18	22	12	4	19		
GN.17833	DIN 172-B10,6-20-A	B 10.6	18	22	20	4	29		
GN.17834	DIN 172-B10,6-25-A	B 10.6	18	22	25	4	36		
GN.17835	DIN 172-B10,7-12-A	B 10.7	18	22	12	4	19		
GN.17836	DIN 172-B10,7-20-A	B 10.7	18	22	20	4	30		
GN.17837	DIN 172-B10,7-25-A	B 10.7	18	22	25	4	36		
GN.17838	DIN 172-B10,8-12-A	B 10.8	18	22	12	4	18		
GN.17839	DIN 172-B10,8-20-A	B 10.8	18	22	20	4	28		
GN.17840	DIN 172-B10,8-25-A	B 10.8	18	22	25	4	34		
GN.17841	DIN 172-B10,9-12-A	B 10.9	18	22	12	4	18		
GN.17842	DIN 172-B10,9-20-A	B 10.9	18	22	20	4	32		
GN.17843	DIN 172-B10,9-25-A	B 10.9	18	22	25	4	36		
GN.12818	DIN 172-B11-12-A	B 11	18	22	12	4	18		
GN.12819	DIN 172-B11-20-A	B 11	18	22	20	4	28		
GN.12742	DIN 172-B11-25-A	B 11	18	22	25	4	35		
GN.17851	DIN 172-B11,1-12-A	B 11.1	18	22	12	4	18		
GN.17852	DIN 172-B11,1-20-A	B 11.1	18	22	20	4	28		
GN.17853	DIN 172-B11,1-25-A	B 11.1	18	22	25	4	34		
GN.17854	DIN 172-B11,2-12-A	B 11.2	18	22	12	4	18		
GN.17855	DIN 172-B11,2-20-A	B 11.2	18	22	20	4	28		
GN.17856	DIN 172-B11,2-25-A	B 11.2	18	22	25	4	34		
GN.17857	DIN 172-B11,3-12-A	B 11.3	18	22	12	4	18		
GN.17858	DIN 172-B11,3-20-A	B 11.3	18	22	20	4	28		
GN.17859	DIN 172-B11,3-25-A	B 11.3	18	22	25	4	33		
GN.17860	DIN 172-B11,4-12-A	B 11.4	18	22	12	4	17		
GN.17861	DIN 172-B11,4-20-A	B 11.4	18	22	20	4	27		
GN.17862	DIN 172-B11,4-25-A	B 11.4	18	22	25	4	33		
GN.12820	DIN 172-B11,5-12-A	B 11.5	18	22	12	4	17		
GN.12821	DIN 172-B11,5-20-A	B 11.5	18	22	20	4	28		
GN.12743	DIN 172-B11,5-25-A	B 11.5	18	22	25	4	33		
GN.17863	DIN 172-B11,6-12-A	B 11.6	18	22	12	4	17		
GN.17864	DIN 172-B11,6-20-A	B 11.6	18	22	20	4	26		
GN.17865	DIN 172-B11,6-25-A	B 11.6	18	22	25	4	32		
GN.17866	DIN 172-B11,7-12-A	B 11.7	18	22	12	4	17		
GN.17867	DIN 172-B11,7-20-A	B 11.7	18	22	20	4	26		
GN.17868	DIN 172-B11,7-25-A	B 11.7	18	22	25	4	32		
GN.12822	DIN 172-B11,8-12-A	B 11.8	18	22	12	4	17		
GN.12823	DIN 172-B11,8-20-A	B 11.8	18	22	20	4	26		
GN.12744	DIN 172-B11,8-25-A	B 11.8	18	22	25	4	32		
GN.17869	DIN 172-B11,9-12-A	B 11.9	18	22	12	4	17		
GN.17870	DIN 172-B11,9-20-A	B 11.9	18	22	20	4	25		
GN.17871	DIN 172-B11,9-25-A	B 11.9	18	22	25	4	31		


Standard machine parts

DIN 172

Code	Description	d1 F7	d2 n6	d3	l1	l2	
GN.12824	DIN 172-B12-12-A	B 12	18	22	12	4	16
GN.12825	DIN 172-B12-20-A	B 12	18	22	20	4	26
GN.12745	DIN 172-B12-25-A	B 12	18	22	25	4	31
GN.12826	DIN 172-B12,1-16-A	B 12.1	22	26	16	4	37
GN.12827	DIN 172-B12,1-28-A	B 12.1	22	26	28	4	62
GN.12746	DIN 172-B12,1-36-A	B 12.1	22	26	36	4	80
GN.17876	DIN 172-B12,2-16-A	B 12.2	22	26	16	4	37
GN.17877	DIN 172-B12,2-28-A	B 12.2	22	26	28	4	61
GN.17878	DIN 172-B12,2-36-A	B 12.2	22	26	36	4	78
GN.17879	DIN 172-B12,3-16-A	B 12.3	22	26	16	4	36
GN.17880	DIN 172-B12,3-28-A	B 12.3	22	26	28	4	61
GN.17881	DIN 172-B12,3-36-A	B 12.3	22	26	36	4	78
GN.17882	DIN 172-B12,4-16-A	B 12.4	22	26	16	4	36
GN.17883	DIN 172-B12,4-28-A	B 12.4	22	26	28	4	60
GN.17884	DIN 172-B12,4-36-A	B 12.4	22	26	36	4	78
GN.12828	DIN 172-B12,5-16-A	B 12.5	22	26	16	4	36
GN.12829	DIN 172-B12,5-28-A	B 12.5	22	26	28	4	60
GN.12747	DIN 172-B12,5-36-A	B 12.5	22	26	36	4	78
GN.17885	DIN 172-B12,6-16-A	B 12.6	22	26	16	4	36
GN.17886	DIN 172-B12,6-28-A	B 12.6	22	26	28	4	62
GN.17887	DIN 172-B12,6-36-A	B 12.6	22	26	36	4	78
GN.17888	DIN 172-B12,7-16-A	B 12.7	22	26	16	4	36
GN.17889	DIN 172-B12,7-28-A	B 12.7	22	26	28	4	60
GN.17890	DIN 172-B12,7-36-A	B 12.7	22	26	36	4	78
GN.17891	DIN 172-B12,8-16-A	B 12.8	22	26	16	4	35
GN.17892	DIN 172-B12,8-28-A	B 12.8	22	26	28	4	60
GN.17893	DIN 172-B12,8-36-A	B 12.8	22	26	36	4	78
GN.17894	DIN 172-B12,9-16-A	B 12.9	22	26	16	4	36
GN.17895	DIN 172-B12,9-28-A	B 12.9	22	26	28	4	60
GN.17896	DIN 172-B12,9-36-A	B 12.9	22	26	36	4	74
GN.12830	DIN 172-B13-16-A	B 13	22	26	16	4	35
GN.12831	DIN 172-B13-28-A	B 13	22	26	28	4	58
GN.12748	DIN 172-B13-36-A	B 13	22	26	36	4	74
GN.17901	DIN 172-B13,1-16-A	B 13.1	22	26	16	4	34
GN.17902	DIN 172-B13,1-28-A	B 13.1	22	26	28	4	57
GN.17903	DIN 172-B13,1-36-A	B 13.1	22	26	36	4	74
GN.17904	DIN 172-B13,2-16-A	B 13.2	22	26	16	4	36
GN.17905	DIN 172-B13,2-28-A	B 13.2	22	26	28	4	57
GN.17906	DIN 172-B13,2-36-A	B 13.2	22	26	36	4	74
GN.17907	DIN 172-B13,3-16-A	B 13.3	22	26	16	4	36
GN.17908	DIN 172-B13,3-28-A	B 13.3	22	26	28	4	58
GN.17909	DIN 172-B13,3-36-A	B 13.3	22	26	36	4	72
GN.17910	DIN 172-B13,4-16-A	B 13.4	22	26	16	4	36
GN.17911	DIN 172-B13,4-28-A	B 13.4	22	26	28	4	58
GN.17912	DIN 172-B13,4-36-A	B 13.4	22	26	36	4	72
GN.12832	DIN 172-B13,5-16-A	B 13.5	22	26	16	4	33
GN.12833	DIN 172-B13,5-28-A	B 13.5	22	26	28	4	55
GN.12749	DIN 172-B13,5-36-A	B 13.5	22	26	36	4	71
GN.17913	DIN 172-B13,6-16-A	B 13.6	22	26	16	4	32
GN.17914	DIN 172-B13,6-28-A	B 13.6	22	26	28	4	56
GN.17915	DIN 172-B13,6-36-A	B 13.6	22	26	36	4	72
GN.17916	DIN 172-B13,7-16-A	B 13.7	22	26	16	4	36
GN.17917	DIN 172-B13,7-28-A	B 13.7	22	26	28	4	56
GN.17918	DIN 172-B13,7-36-A	B 13.7	22	26	36	4	72
GN.17919	DIN 172-B13,8-16-A	B 13.8	22	26	16	4	32
GN.17920	DIN 172-B13,8-28-A	B 13.8	22	26	28	4	54
GN.17921	DIN 172-B13,8-36-A	B 13.8	22	26	36	4	70
GN.17922	DIN 172-B13,9-16-A	B 13.9	22	26	16	4	36
GN.17923	DIN 172-B13,9-28-A	B 13.9	22	26	28	4	54
GN.17924	DIN 172-B13,9-36-A	B 13.9	22	26	36	4	70


METRIC

Code	Description	d1 F7	d2 n6	d3	l1	l2	
GN.12834	DIN 172-B14-16-A	B 14	22	26	16	4	32
GN.12835	DIN 172-B14-28-A	B 14	22	26	28	4	53
GN.12870	DIN 172-B14-36-A	B 14	22	26	36	4	68
GN.12836	DIN 172-B14,1-16-A	B 14.1	22	26	16	4	32
GN.12837	DIN 172-B14,1-28-A	B 14.1	22	26	28	4	53
GN.12871	DIN 172-B14,1-36-A	B 14.1	22	26	36	4	68
GN.17931	DIN 172-B14,2-16-A	B 14.2	22	26	16	4	32
GN.17932	DIN 172-B14,2-28-A	B 14.2	22	26	28	4	52
GN.17933	DIN 172-B14,2-36-A	B 14.2	22	26	36	4	76
GN.17934	DIN 172-B14,3-16-A	B 14.3	22	26	16	4	31
GN.17935	DIN 172-B14,3-28-A	B 14.3	22	26	28	4	62
GN.17936	DIN 172-B14,3-36-A	B 14.3	22	26	36	4	74
GN.17937	DIN 172-B14,4-16-A	B 14.4	22	26	16	4	31
GN.17938	DIN 172-B14,4-28-A	B 14.4	22	26	28	4	62
GN.17939	DIN 172-B14,4-36-A	B 14.4	22	26	36	4	74
GN.12838	DIN 172-B14,5-16-A	B 14.5	22	26	16	4	31
GN.12839	DIN 172-B14,5-28-A	B 14.5	22	26	28	4	51
GN.12872	DIN 172-B14,5-36-A	B 14.5	22	26	36	4	65
GN.17940	DIN 172-B14,6-16-A	B 14.6	22	26	16	4	40
GN.17941	DIN 172-B14,6-28-A	B 14.6	22	26	28	4	60
GN.17942	DIN 172-B14,6-36-A	B 14.6	22	26	36	4	63
GN.17943	DIN 172-B14,7-16-A	B 14.7	22	26	16	4	40
GN.17944	DIN 172-B14,7-28-A	B 14.7	22	26	28	4	58
GN.17945	DIN 172-B14,7-36-A	B 14.7	22	26	36	4	74
GN.17946	DIN 172-B14,8-16-A	B 14.8	22	26	16	4	40
GN.17947	DIN 172-B14,8-28-A	B 14.8	22	26	28	4	58
GN.17948	DIN 172-B14,8-36-A	B 14.8	22	26	36	4	70
GN.17949	DIN 172-B14,9-16-A	B 14.9	22	26	16	4	40
GN.17950	DIN 172-B14,9-28-A	B 14.9	22	26	28	4	60
GN.17951	DIN 172-B14,9-36-A	B 14.9	22	26	36	4	74
GN.12840	DIN 172-B15-16-A	B 15	22	26	16	4	29
GN.12841	DIN 172-B15-28-A	B 15	22	26	28	4	48
GN.12873	DIN 172-B15-36-A	B 15	22	26	36	4	61
GN.17956	DIN 172-B15,1-16-A	B 15.1	26	30	16	4	48
GN.17957	DIN 172-B15,1-28-A	B 15.1	26	30	28	4	80
GN.17958	DIN 172-B15,1-36-A	B 15.1	26	30	36	4	60
GN.12842	DIN 172-B15,5-16-A	B 15.5	26	30	16	4	47
GN.12843	DIN 172-B15,5-28-A	B 15.5	26	30	28	4	79
GN.12874	DIN 172-B15,5-36-A	B 15.5	26	30	36	4	60
GN.12844	DIN 172-B16-16-A	B 16	26	30	16	4	46
GN.12845	DIN 172-B16-28-A	B 16	26	30	28	4	76
GN.12875	DIN 172-B16-36-A	B 16	26	30	36	4	98
GN.12848	DIN 172-B16,1-16-A	B 16.1	26	30	16	4	45
GN.12849	DIN 172-B16,1-28-A	B 16.1	26	30	28	4	75
GN.12876	DIN 172-B16,1-36-A	B 16.1	26	30	36	4	97
GN.12846	DIN 172-B16,5-16-A	B 16.5	26	30	16	4	44
GN.12847	DIN 172-B16,5-28-A	B 16.5	26	30	28	4	74
GN.12877	DIN 172-B16,5-36-A	B 16.5	26	30	36	4	95



Standard machine parts

Conversion Table	
1 mm = 0,039 inch	
d3	
mm	inch
30	1.17
34	1.33
39	1.52
46	1.79
52	2.03
59	2.30




DIN 172

Code	Description	d1 F7	d2 n6	d3	l1	l2	ΔL
GN.12850	DIN 172-B17-16-A	B 17	26	30	16	4	42
GN.12851	DIN 172-B17-28-A	B 17	26	30	28	4	71
GN.12878	DIN 172-B17-36-A	B 17	26	30	36	4	91
GN.17959	DIN 172-B17,5-16-A	B 17.5	26	30	16	4	50
GN.17960	DIN 172-B17,5-28-A	B 17.5	26	30	28	4	68
GN.17961	DIN 172-B17,5-36-A	B 17.5	26	30	36	4	86
GN.12852	DIN 172-B18-16-A	B 18	26	30	16	4	39
GN.12853	DIN 172-B18-28-A	B 18	26	30	28	4	45
GN.12879	DIN 172-B18-36-A	B 18	26	30	36	4	83
GN.17962	DIN 172-B18,5-20-A	B 18.5	30	34	20	5	74
GN.17963	DIN 172-B18,5-36-A	B 18.5	30	34	36	5	128
GN.17964	DIN 172-B18,5-45-A	B 18.5	30	34	45	5	159
GN.12854	DIN 172-B19-20-A	B 19	30	34	20	5	72
GN.12855	DIN 172-B19-36-A	B 19	30	34	36	5	124
GN.12880	DIN 172-B19-45-A	B 19	30	34	45	5	155
GN.17965	DIN 172-B19,5-20-A	B 19.5	30	34	20	5	72
GN.17966	DIN 172-B19,5-36-A	B 19.5	30	34	36	5	120
GN.17967	DIN 172-B19,5-45-A	B 19.5	30	34	45	5	152
GN.12856	DIN 172-B20-20-A	B 20	30	34	20	5	66
GN.12857	DIN 172-B20-36-A	B 20	30	34	36	5	116
GN.12881	DIN 172-B20-45-A	B 20	30	34	45	5	145
GN.17968	DIN 172-B20,5-20-A	B 20.5	30	34	20	5	64
GN.17969	DIN 172-B20,5-36-A	B 20.5	30	34	36	5	111
GN.17970	DIN 172-B20,5-45-A	B 20.5	30	34	45	5	138
GN.17971	DIN 172-B21-20-A	B 21	30	34	20	5	61
GN.17972	DIN 172-B21-36-A	B 21	30	34	36	5	107
GN.17973	DIN 172-B21-45-A	B 21	30	34	45	5	132
GN.17974	DIN 172-B21,5-20-A	B 21.5	30	34	20	5	58
GN.17975	DIN 172-B21,5-36-A	B 21.5	30	34	36	5	102
GN.17976	DIN 172-B21,5-45-A	B 21.5	30	34	45	5	125
GN.12858	DIN 172-B22-20-A	B 22	30	34	20	5	45
GN.12859	DIN 172-B22-36-A	B 22	30	34	36	5	97
GN.12882	DIN 172-B22-45-A	B 22	30	34	45	5	121
GN.17977	DIN 172-B22,5-20-A	B 22.5	35	39	20	5	94
GN.17978	DIN 172-B22,5-36-A	B 22.5	35	39	36	5	166
GN.17979	DIN 172-B22,5-45-A	B 22.5	35	39	45	5	205

METRIC

Code	Description	d1 F7	d2 n6	d3	l1	l2	ΔL
GN.17980	DIN 172-B23-20-A	B 23	35	39	20	5	92
GN.17981	DIN 172-B23-36-A	B 23	35	39	36	5	160
GN.17982	DIN 172-B23-45-A	B 23	35	39	45	5	181
GN.17983	DIN 172-B23,5-20-A	B 23.5	35	39	20	5	72
GN.17984	DIN 172-B23,5-36-A	B 23.5	35	39	36	5	155
GN.17985	DIN 172-B23,5-45-A	B 23.5	35	39	45	5	192
GN.12860	DIN 172-B24-20-A	B 24	35	39	20	5	86
GN.12861	DIN 172-B24-36-A	B 24	35	39	36	5	150
GN.12883	DIN 172-B24-45-A	B 24	35	39	45	5	186
GN.17986	DIN 172-B24,5-20-A	B 24.5	35	39	20	5	83
GN.17987	DIN 172-B24,5-36-A	B 24.5	35	39	36	5	143
GN.17988	DIN 172-B24,5-45-A	B 24.5	35	39	45	5	178
GN.12862	DIN 172-B25-20-A	B 25	35	39	20	5	60
GN.12863	DIN 172-B25-36-A	B 25	35	39	36	5	138
GN.12884	DIN 172-B25-45-A	B 25	35	39	45	5	173
GN.17989	DIN 172-B25,5-20-A	B 25.5	35	39	20	5	77
GN.17990	DIN 172-B25,5-36-A	B 25.5	35	39	36	5	134
GN.17991	DIN 172-B25,5-45-A	B 25.5	35	39	45	5	165
GN.12864	DIN 172-B26-20-A	B 26	35	39	20	5	73
GN.12865	DIN 172-B26-36-A	B 26	35	39	36	5	127
GN.12885	DIN 172-B26-45-A	B 26	35	39	45	5	159
GN.17992	DIN 172-B26,5-25-A	B 26.5	42	46	25	5	170
GN.17993	DIN 172-B26,5-45-A	B 26.5	42	46	45	5	300
GN.17994	DIN 172-B26,5-56-A	B 26.5	42	46	56	5	367
GN.17995	DIN 172-B27-25-A	B 27	42	46	25	5	167
GN.17996	DIN 172-B27-45-A	B 27	42	46	45	5	292
GN.17997	DIN 172-B27-56-A	B 27	42	46	56	5	362
GN.17998	DIN 172-B27,5-25-A	B 27.5	42	46	25	5	162
GN.17999	DIN 172-B27,5-45-A	B 27.5	42	46	45	5	287
GN.18000	DIN 172-B27,5-56-A	B 27.5	42	46	56	5	349
GN.12866	DIN 172-B28-25-A	B 28	42	46	25	5	157
GN.12867	DIN 172-B28-45-A	B 28	42	46	45	5	277
GN.12886	DIN 172-B28-56-A	B 28	42	46	56	5	343
GN.18001	DIN 172-B28,5-25-A	B 28.5	42	46	25	5	153
GN.18002	DIN 172-B28,5-45-A	B 28.5	42	46	45	5	271
GN.18003	DIN 172-B28,5-56-A	B 28.5	42	46	56	5	330

Conversion Table	
1 mm = 0.039 inch	
d3	
mm	inch
30	1.17
34	1.33
39	1.52
46	1.79
52	2.03
59	2.30




DIN 172

Code	Description	d1 F7	d2 n6	d3	l1	l2	⚖
GN.18004	DIN 172-B29-25-A	B 29	42	46	25	5	149
GN.18005	DIN 172-B29-45-A	B 29	42	46	45	5	261
GN.18006	DIN 172-B29-56-A	B 29	42	46	56	5	320
GN.18007	DIN 172-B29,5-25-A	B 29.5	42	46	25	5	143
GN.18008	DIN 172-B29,5-45-A	B 29.5	42	46	45	5	253
GN.18009	DIN 172-B29,5-56-A	B 29.5	42	46	56	5	310
GN.12868	DIN 172-B30-25-A	B 30	42	46	25	5	135
GN.12869	DIN 172-B30-45-A	B 30	42	46	45	5	245
GN.12887	DIN 172-B30-56-A	B 30	42	46	56	5	303
GN.18010	DIN 172-B30,5-25-A	B 30.5	48	52	25	5	220
GN.18011	DIN 172-B30,5-45-A	B 30.5	48	52	45	5	385
GN.18012	DIN 172-B30,5-56-A	B 30.5	48	52	56	5	482
GN.18013	DIN 172-B31-25-A	B 31	48	52	25	5	214
GN.18014	DIN 172-B31-45-A	B 31	48	52	45	5	378
GN.18015	DIN 172-B31-56-A	B 31	48	52	56	5	470
GN.18016	DIN 172-B31,5-25-A	B 31.5	48	52	25	5	209
GN.18017	DIN 172-B31,5-45-A	B 31.5	48	52	45	5	365
GN.18018	DIN 172-B31,5-56-A	B 31.5	48	52	56	5	452
GN.18019	DIN 172-B32-25-A	B 32	48	52	25	5	200
GN.18020	DIN 172-B32-45-A	B 32	48	52	45	5	360
GN.18021	DIN 172-B32-56-A	B 32	48	52	56	5	447
GN.18022	DIN 172-B32,5-25-A	B 32.5	48	52	25	5	189
GN.18023	DIN 172-B32,5-45-A	B 32.5	48	52	45	5	347
GN.18024	DIN 172-B32,5-56-A	B 32.5	48	52	56	5	430
GN.18025	DIN 172-B33-25-A	B 33	48	52	25	5	194
GN.18026	DIN 172-B33-45-A	B 33	48	52	45	5	343
GN.18027	DIN 172-B33-56-A	B 33	48	52	56	5	416
GN.18028	DIN 172-B33,5-25-A	B 33.5	48	52	25	5	189
GN.18029	DIN 172-B33,5-45-A	B 33.5	48	52	45	5	329
GN.18030	DIN 172-B33,5-56-A	B 33.5	48	52	56	5	408


METRIC

Code	Description	d1 F7	d2 n6	d3	l1	l2	⚖
GN.18031	DIN 172-B34-25-A	B 34	48	52	25	5	184
GN.18032	DIN 172-B34-45-A	B 34	48	52	45	5	324
GN.18033	DIN 172-B34-56-A	B 34	48	52	56	5	400
GN.18034	DIN 172-B34,5-25-A	B 34.5	48	52	25	5	176
GN.18035	DIN 172-B34,5-45-A	B 34.5	48	52	45	5	314
GN.18036	DIN 172-B34,5-56-A	B 34.5	48	52	56	5	385
GN.18037	DIN 172-B35-25-A	B 35	48	52	25	5	173
GN.18038	DIN 172-B35-45-A	B 35	48	52	45	5	304
GN.18039	DIN 172-B35-56-A	B 35	48	52	56	5	378
GN.18040	DIN 172-B36-30-A	B 36	55	59	30	5	326
GN.18041	DIN 172-B36-56-A	B 36	55	59	56	5	601
GN.18042	DIN 172-B36-67-A	B 36	55	59	67	5	230
GN.18043	DIN 172-B37-30-A	B 37	55	59	30	5	313
GN.18044	DIN 172-B37-56-A	B 37	55	59	56	5	568
GN.18045	DIN 172-B37-67-A	B 37	55	59	67	5	678
GN.18046	DIN 172-B38-30-A	B 38	55	59	30	5	299
GN.18047	DIN 172-B38-56-A	B 38	55	59	56	5	550
GN.18048	DIN 172-B38-67-A	B 38	55	59	67	5	658
GN.18049	DIN 172-B39-30-A	B 39	55	59	30	5	280
GN.18050	DIN 172-B39-56-A	B 39	55	59	56	5	517
GN.18051	DIN 172-B39-67-A	B 39	55	59	67	5	617
GN.18052	DIN 172-B40-30-A	B 40	55	59	30	5	270
GN.18053	DIN 172-B40-56-A	B 40	55	59	56	5	496
GN.18054	DIN 172-B40-67-A	B 40	55	59	67	5	593
GN.18055	DIN 172-B41-30-A	B 41	55	59	30	5	255
GN.18056	DIN 172-B41-56-A	B 41	55	59	56	5	462
GN.18057	DIN 172-B41-67-A	B 41	55	59	67	5	552
GN.18058	DIN 172-B42-30-A	B 42	55	59	30	5	240
GN.18059	DIN 172-B42-56-A	B 42	55	59	56	5	496
GN.18060	DIN 172-B42-67-A	B 42	55	59	67	5	524



Standard machine parts

Conversion Table		
1 mm = 0,039 inch		
d3		
mm	inch	
10	0.39	
11	0.43	
13	0.51	
15	0.59	
18	0.70	
22	0.86	
26	1.01	
30	1.17	



INOX STAINLESS STEEL METRIC

DIN 172-NI

Code	Description	d1	F7	d2	n6	d3	l1	l2	⚖
GN.18061	DIN 172-B4-8-A-NI	B 4	7	10	8	2.5	2		
GN.18062	DIN 172-B4-12-A-NI	B 4	7	10	12	2.5	4		
GN.18063	DIN 172-B4,1-8-A-NI	B 4.1	8	11	8	2.5	3		
GN.18064	DIN 172-B4,1-12-A-NI	B 4.1	8	11	12	2.5	4		
GN.18065	DIN 172-B5-8-A-NI	B 5	8	11	8	2.5	4		
GN.18066	DIN 172-B5-12-A-NI	B 5	8	11	12	2.5	3		
GN.18067	DIN 172-B5,1-10-A-NI	B 5.1	10	13	10	3	6		
GN.18068	DIN 172-B5,1-16-A-NI	B 5.1	10	13	16	3	8		
GN.18069	DIN 172-B6-10-A-NI	B 6	10	13	10	3	5		
GN.18070	DIN 172-B6-16-A-NI	B 6	10	13	16	3	7		
GN.18071	DIN 172-B6,1-10-A-NI	B 6.1	12	15	10	3	8		
GN.18072	DIN 172-B6,1-16-A-NI	B 6.1	12	15	16	3	12		
GN.18073	DIN 172-B8-10-A-NI	B 8	12	15	10	3	6		
GN.18074	DIN 172-B8-16-A-NI	B 8	12	15	16	3	9		
GN.18075	DIN 172-B8,1-12-A-NI	B 8.1	15	18	12	3	13		
GN.18076	DIN 172-B8,1-20-A-NI	B 8.1	15	18	20	3	21		
GN.18077	DIN 172-B10-12-A-NI	B 10	15	18	12	3	10		
GN.18078	DIN 172-B10-20-A-NI	B 10	15	18	20	3	17		
GN.18079	DIN 172-B10,1-12-A-NI	B 10.1	18	22	12	4	20		
GN.18080	DIN 172-B10,1-20-A-NI	B 10.1	18	22	20	4	30		
GN.18081	DIN 172-B12-12-A-NI	B 12	18	22	12	4	16		
GN.18082	DIN 172-B12-20-A-NI	B 12	18	22	20	4	26		
GN.18083	DIN 172-B12,1-16-A-NI	B 12.1	22	26	16	4	37		
GN.18084	DIN 172-B12,1-28-A-NI	B 12.1	22	26	28	4	62		
GN.18085	DIN 172-B14-16-A-NI	B 14	22	26	16	4	32		
GN.18086	DIN 172-B14-28-A-NI	B 14	22	26	28	4	53		
GN.18087	DIN 172-B14,1-16-A-NI	B 14.1	22	26	16	4	32		
GN.18088	DIN 172-B14,1-28-A-NI	B 14.1	22	26	28	4	53		
GN.18089	DIN 172-B15-16-A-NI	B 15	22	26	16	4	29		
GN.18090	DIN 172-B15-28-A-NI	B 15	22	26	28	4	48		
GN.18091	DIN 172-B15,1-16-A-NI	B 15.1	26	30	16	4	48		
GN.18092	DIN 172-B15,1-28-A-NI	B 15.1	26	30	28	4	80		
GN.18093	DIN 172-B16-16-A-NI	B 16	26	30	16	4	46		
GN.18094	DIN 172-B16-28-A-NI	B 16	26	30	28	4	76		
GN.18095	DIN 172-B16,1-16-A-NI	B 16.1	26	30	16	4	45		
GN.18096	DIN 172-B16,1-28-A-NI	B 16.1	26	30	28	4	75		