


- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

STANDARD EXECUTIONS

Stainless steel precision casting AISI CF-8, matte shot-blasted.

- DIN 6336-NI-A: without hole.
- DIN 6336-NI-D: with pass-through threaded hole.
- DIN 6336-NI-E: with threaded blind hole.



DIN 6336-NI-A

Code	Description	d1	d4	h3	h4 min	Δ
GN.1079450	DIN 6336-NI-32-A	1.26	0.47	0.83	0.39	0.12
GN.1079590	DIN 6336-NI-40-A	1.57	0.55	1.02	0.51	0.19
GN.1079741	DIN 6336-NI-50-A	1.97	0.71	1.34	0.67	0.39
GN.1079851	DIN 6336-NI-63-A	2.48	0.79	1.65	0.83	0.71

DIN 6336-NI-D

Code	Description	d1	d2	d4	h1	h2 min	t2	Δ
GN.9108510	DIN 6336-NI-32-1/4-20-D	1.26	1/4-20	0.47	0.79	0.35	0.39	0.11
GN.9108512	DIN 6336-NI-40-5/16-18-D	1.57	5/16-18	0.55	0.98	0.47	0.51	0.17
GN.9108514	DIN 6336-NI-50-3/8-16-D	1.97	3/8-16	0.71	1.26	0.59	0.63	0.35
GN.9108516	DIN 6336-NI-50-5/16-18-D	1.97	5/16-18	0.71	1.26	0.59	0.63	0.37
GN.9108518	DIN 6336-NI-63-1/2-13-D	2.48	1/2-13	0.79	1.57	0.75	0.79	0.62
GN.9108520	DIN 6336-NI-63-3/8-16-D	2.48	3/8-16	0.79	1.57	0.75	0.79	0.64

DIN 6336-NI-E

Code	Description	d1	d2	d4	h1	h2 min	t1 min	Δ
GN.9108511	DIN 6336-NI-32-1/4-20-E	1.26	1/4-20	0.47	0.79	0.35	0.47	0.12
GN.9108513	DIN 6336-NI-40-5/16-18-E	1.57	5/16-18	0.55	0.98	0.47	0.59	0.19
GN.9108515	DIN 6336-NI-50-3/8-16-E	1.97	3/8-16	0.71	1.26	0.59	0.71	0.38
GN.9108517	DIN 6336-NI-50-5/16-18-E	1.97	5/16-18	0.71	1.26	0.59	0.71	0.38
GN.9108519	DIN 6336-NI-63-1/2-13-E	2.48	1/2-13	0.79	1.57	0.75	0.87	0.65
GN.9108521	DIN 6336-NI-63-3/8-16-E	2.48	3/8-16	0.79	1.57	0.75	0.87	0.67