



STANDARD EXECUTIONS

- **DVA.4**: threaded stud and base plate in polished zinc-plated steel, vibration-damper body in natural rubber NR, black colour, hardness 40, 55, 70 Shore A ± 5 .
- **DVA.4-SST**: threaded stud and base plate in INOX AISI 304 stainless steel, vibration-damper body in natural rubber NR, black colour, hardness 55 Shore A ± 5 .

FEATURES AND APPLICATIONS


The rubber buffers have been designed to damp vibrations, shocks and noises produced by moving bodies or non-balanced vibrating masses of equipment and machines which can cause:

- malfunctioning and reduction of the machine lifespan and/or of the adjacent ones;
- damage to health;
- noise.

Load diagrams for each single code are available on request.
See Technical data and guidelines for the choice (on page 728).

SPECIAL EXECUTIONS ON REQUEST

Natural rubber NR, hardness 40, 70 tolerance ± 5 Shore A for executions with AISI 304 stainless steel base.



DVA.4

										DVA.4-SST	
Code	Description	D	L	d	l	Max. load [lbf]	Max. deflection [inch]	Stiffness [lbf/inch]		Code	Description
9412756	DVA.4-25-13-1/4-55	0.98	0.51	1/4-20	0.5	179	0.15	1217	0.03	9410331	DVA.4-25-13-SST-1/4-55
9412766	DVA.4-25-19-1/4-55	0.98	0.75	1/4-20	0.5	130	0.2	663	0.04	9410335	DVA.4-25-19-SST-1/4-55
9412771	DVA.4-25-25-5/16-55	0.98	0.98	5/16-18	0.63	230	0.25	937	0.06	9410336	DVA.4-25-25-SST-5/16-55
9412773	DVA.4-38-19-5/16-55	1.5	0.75	5/16-18	0.63	560	0.2	2857	0.09	9410351	DVA.4-38-19-SST-5/16-55
9412831	DVA.4-40-25-5/16-55	1.57	0.98	5/16-18	0.63	372	0.25	1520	0.12	9410354	DVA.4-40-25-SST-5/16-55
9412841	DVA.4-40-25-3/8-55	1.57	0.98	3/8-16	0.63	372	0.25	1520	0.14	9410353	DVA.4-40-25-SST-3/8-55
9412881	DVA.4-51-19-3/8-55	2.01	0.75	3/8-16	1.13	775	0.2	3954	0.18	9410361	DVA.4-51-19-SST-3/8-55
9412921	DVA.4-51-41-3/8-55	2.01	1.61	3/8-16	0.63	618	0.39	1577	0.29	9410365	DVA.4-51-41-SST-3/8-55