



STANDARD EXECUTIONS

- **DVA.5**: bushing with threaded blind hole and base plate in polished zinc-plated steel, vibration-damper body in natural rubber NR, black colour, hardness 40, 55, 70 Shore A ± 5 .
- **DVA.5-SST**: bushing with threaded blind hole and base plate in AISI 304 stainless steel, vibration-damper body in natural rubber NR, black colour, hardness 55 Shore A ± 5 .

FEATURES AND APPLICATIONS


The rubber buffers have been designed to damp vibrations, shocks and noises produced by moving bodies or non-balanced vibrating masses of equipment and machines which can cause:

- malfunctioning and reduction of the machine lifespan and/or of the adjacent ones;
- damage to health;
- noise.

Load diagrams for each single code are available on request.
See Technical data and guidelines for the choice (on page 728).

SPECIAL EXECUTIONS ON REQUEST

Natural rubber NR, hardness 40, 70 tolerance ± 5 Shore A for executions with AISI 304 stainless steel base.



DVA.5

INCH										DVA.5-SST	
Code	Description	D	L	d	h	Max. load [lbf]	Max. deflection [inch]	Stiffness [lbf/inch]		Code	Description
9413091	DVA.5-25-13-1/4-55	0.98	0.51	1/4-20	0.24	179	0.15	1217	0.03	9410421	DVA.5-25-13-SST-1/4-55
9413101	DVA.5-25-19-1/4-55	0.98	0.75	1/4-20	0.24	130	0.2	663	0.03	9410425	DVA.5-25-19-SST-1/4-55
9413106	DVA.5-25-25-5/16-55	0.98	0.98	5/16-18	0.24	227	0.2	1160	0.05	9410426	DVA.5-25-25-SST-5/16-55
9413107	DVA.5-38-19-5/16-55	1.5	0.75	5/16-18	0.31	560	0.2	2857	0.09	9410441	DVA.5-38-19-SST-5/16-55
9413108	DVA.5-38-25-5/16-55	1.5	0.98	5/16-18	0.31	560	0.2	2857	0.11	9410443	DVA.5-38-25-SST-5/16-55
9413109	DVA.5-38-25-3/8-55	1.5	0.98	3/8-16	0.31	560	0.2	2857	0.11	9410442	DVA.5-38-25-SST-3/8-55
9413181	DVA.5-51-19-3/8-55	2.01	0.75	3/8-16	0.39	775	0.2	3954	0.15	9410451	DVA.5-51-19-SST-3/8-55
9413186	DVA.5-51-41-3/8-55	2.01	1.61	3/8-16	0.39	618	0.39	1577	0.26	9410455	DVA.5-51-41-SST-3/8-55