



STANDARD EXECUTIONS

- **DVA.3:** bushings with threaded blind holes and base plate in polished zinc-plated steel, vibration-damper body in natural rubber NR, black colour, hardness 40, 55, 70 Shore A ± 5 .
- **DVA.3-SST:** bushings with threaded blind holes and base plate in INOX AISI 304 stainless steel, vibration-damper body in natural rubber NR, black colour, hardness 55 Shore A ± 5 .

FEATURES AND APPLICATIONS


The rubber buffers have been designed to damp vibrations, shocks and noises produced by moving bodies or non-balanced vibrating masses of equipment and machines which can cause:

- malfunctioning and reduction of the machine lifespan and/or of the adjacent ones;
- damage to health;
- noise.

Load diagrams for each single code are available on request.
See Technical data and guidelines for the choice (on page 728).

SPECIAL EXECUTIONS ON REQUEST

Natural rubber NR, hardness 40, 70 tolerance ± 5 Shore A for executions with AISI 304 stainless steel base.



DVA.3	-16	-13	-8	-55
	D	L	d	Shore A

DVA.3

INCH

INCH

DVA.3										DVA.3-SST	
Code	Description	D	L	d	h	Max. load [lbf]	Max. deflection [inch]	Stiffness [lbf/inch]		Code	Description
9412326	DVA.3-16-13-8-55	0.63	0.51	8-32	0.16	63	0.15	429	0.02	9410215	DVA.3-16-13-SST-8-55
9412386	DVA.3-25-25-5/16-55	0.98	0.98	5/16-18	0.24	239	0.03	8708	0.06	9410233	DVA.3-25-25-SST-5/16-55
9412396	DVA.3-38-25-5/16-55	1.5	0.98	5/16-18	0.31	239	0.03	8708	0.14	9410251	DVA.3-38-25-SST-5/16-55
9412466	DVA.3-51-41-3/8-55	2.01	1.61	3/8-16	0.39	477	0.39	1217	0.32	9410265	DVA.3-51-41-SST-3/8-55