



STANDARD EXECUTIONS

- **DVA.6**: threaded stud and base plate in polished zinc-plated steel, vibration-damper body in natural rubber NR, black colour, hardness 40, 55, 70 Shore A ± 5 .
- **DVA.6-SST**: threaded stud and base plate in INOX AISI 304 stainless steel, vibration-damper body in natural rubber NR, black colour, hardness 55 Shore A ± 5 .

FEATURES AND APPLICATIONS


The rubber buffers have been designed to damp vibrations, shocks and noises produced by moving bodies or non-balanced vibrating masses of equipment and machines which can cause:

- malfunctioning and reduction of the machine lifespan and/or of the adjacent ones;
- damage to health;
- noise.

Load diagrams for each single code are available on request.
See Technical data and guidelines for the choice(on page 728).

SPECIAL EXECUTIONS ON REQUEST

Natural rubber NR, hardness 40, 70 tolerance ± 5 Shore A for executions with AISI 304 stainless steel base.



DVA.6

Code	Description	D	L	d	I	Max. load [lbf]	Max. deflection [inch]		DVA.6-SST	
									Code	Description
9413401	DVA.6-19-25-1/4-55	0.75	0.98	1/4-20	0.51	29	0.24	0.02	9410501	DVA.6-19-25-SST-1/4-55
9413411	DVA.6-25-32-1/4-55	0.98	1.26	1/4-20	0.51	29	0.24	0.04	9410503	DVA.6-25-32-SST-1/4-55
9413421	DVA.6-32-38-5/16-55	1.26	1.5	5/16-18	0.63	72	0.35	0.07	9410507	DVA.6-32-38-SST-5/16-55
9413431	DVA.6-38-45-5/16-55	1.5	1.77	5/16-18	0.63	67	0.39	0.11	9410515	DVA.6-38-45-SST-5/16-55
9413441	DVA.6-45-51-3/8-55	1.77	2.01	3/8-16	0.63	199	0.67	0.18	9410517	DVA.6-45-51-SST-3/8-55
9413451	DVA.6-51-57-3/8-55	2.01	2.24	3/8-16	1.1	199	0.67	0.26	9410521	DVA.6-51-57-SST-3/8-55