



STANDARD EXECUTIONS

- **DVA.7:** bushing with threaded blind hole and base plate in polished zinc-plated steel, vibration-damper body in natural rubber NR, black colour, hardness 40, 55, 70 Shore A ± 5 .
- **DVA.7-SST:** bushing with threaded blind hole and base plate in AISI 304 stainless steel, vibration-damper body in natural rubber NR, black colour, hardness 55 Shore A ± 5 .

FEATURES AND APPLICATIONS


The rubber buffers have been designed to damp vibrations, shocks and noises produced by moving bodies or non-balanced vibrating masses of equipment and machines which can cause:

- malfunctioning and reduction of the machine lifespan and/or of the adjacent ones;
- damage to health;
- noise.

Load diagrams for each single code are available on request. See Technical data and guidelines for the choice (on page 728).

SPECIAL EXECUTIONS ON REQUEST

Natural rubber NR, hardness 40, 70 tolerance ± 5 Shore A for executions with AISI 304 stainless steel base.



DVA.7

DVA.7-SST

Code	Description	D	L	d	h	Max. load [lbf]	Max. deflection [inch]		Code	Description
9413601	DVA.7-19-25-1/4-55	0.75	0.98	1/4-20	0.24	29	0.24	0.02	9410601	DVA.7-19-25-SST-1/4-55
9413611	DVA.7-25-32-1/4-55	0.98	1.26	1/4-20	0.24	29	0.24	0.03	9410605	DVA.7-25-32-SST-1/4-55
9413621	DVA.7-32-38-5/16-55	1.26	1.5	5/16-18	0.31	72	0.35	0.07	9410613	DVA.7-32-38-SST-5/16-55
9413631	DVA.7-38-45-5/16-55	1.5	1.77	5/16-18	0.31	67	0.39	0.1	9410625	DVA.7-38-45-SST-5/16-55
9413641	DVA.7-45-51-3/8-55	1.77	2.01	3/8-16	0.39	67	0.39	0.18	9410627	DVA.7-45-51-SST-3/8-55
9413651	DVA.7-51-57-3/8-55	2.01	2.24	3/8-16	0.39	199	0.67	0.23	9410631	DVA.7-51-57-SST-3/8-55