



MATERIAL

AISI 301 stainless steel.


FEATURES AND APPLICATIONS

GN 111.6 retaining rings can be mounted by rotating on the groove specially made at the end of a shaft or handle.


The different types of handwheels, for example, can be fixed in the place of use with an additional retaining cable (e.g. GN 111 - GN 111.2) avoiding the possibility of loss.



Assembly instructions



Conversion Table 1 mm = 0,039 inch			
d0			
mm	inch	mm	inch
12	0.47	20	0.79
14	0.55	21	0.83
15	0.59	22	0.87
16	0.63	23	0.91
17	0.67	24	0.94
18	0.71	26	1.02
19	0.75		



Code	Description	d0	d1 +0.5	d2	d3 ±0.1	l1	l2 ±0.5	l3 +0.3	b +0.2	⚖
GN.40971	GN 111.6-12-S	12	11.4	1.1	9.1	18.7	5	2.5	1.7	1
GN.40972	GN 111.6-14-S	14	13.2	1.1	10.9	19.8	5	3.2	1.8	1
GN.40973	GN 111.6-15-S	15	14.6	1.3	11.9	22.7	5.5	3.2	1.8	1
GN.40974	GN 111.6-16-S	16	15.6	1.3	12.9	23.3	5.5	3.2	1.8	1
GN.40975	GN 111.6-17-S	17	16.4	1.3	13.7	23.8	5.5	3.9	1.9	1
GN.40976	GN 111.6-18-S	18	17.6	1.4	14.7	26.5	6	3.9	1.9	1
GN.40977	GN 111.6-19-S	19	18.6	1.4	15.7	27.1	6	3.9	1.9	1
GN.40978	GN 111.6-20-S	20	19.6	1.4	16.7	27.7	6	3.9	1.9	1
GN.40979	GN 111.6-21-S	21	20.4	1.4	17.5	28.1	6	5.1	2	1
GN.40980	GN 111.6-22-S	22	21.8	1.6	18.5	31.1	7	5.1	2	1
GN.40981	GN 111.6-23-S	23	22.8	1.6	19.5	31.7	7	5.1	2	1
GN.40982	GN 111.6-24-S	24	23.8	1.6	20.5	32.2	7	5.1	2	1
GN.40983	GN 111.6-26-S	26	25.6	1.6	22.3	33.2	7	5.4	2.1	1