

MATERIAL

Glass-fibre reinforced polyamide based (PA) technopolymer, grey-black colour, matte finish.

Elastic fork in acetal based technopolymer (POM), black colour.

BOSS CAP

Polyamide based (PA) technopolymer, grey-black colour, matte finish, press-fit assembly, removable by a screwdriver.

STANDARD EXECUTIONS

- **EWN-B-RC**: brass boss, threaded through hole.
- **EWN-SST-RC**: AISI 303 stainless steel, threaded pass-through hole.
- **EWN-p-RC**: zinc-plated steel threaded stud, chamfered flat end according to UNI EN ISO 4753:2012 (see Technical data on page A-10).
- **EWN-SST-p-RC**: AISI 303 stainless steel threaded stud, chamfered flat end UNI EN ISO 4753:2012 (see Technical data on page A-10).

FEATURES AND APPLICATIONS

Suitable where it is necessary to prevent the loss of the wing nut. The elastic fork, housed in the groove of the knob can turn freely.


ACCESSORIES ON REQUEST

- CT-S (see page -) technopolymer and stainless steel ball chains.
- GN 111 (see page -) stainless steel and brass ball chains.
- CV-T (see page -) polyethylene and stainless steel retaining cables.
- GN 111.2 (see page -) stainless steel retaining cables.
- GN 111.4 (see page -) polyurethane and stainless steel spiral retaining cables.



ERGOSTYLE® ELESA Original design

**EWN-B-RC
EWN-SST-RC**



Conversion Table
1 mm = 0.039 inch

D	
mm	inch
47	1.83
55	2.15
63	2.46

EWN-B-RC


Code	Description	D	d6H	L	d1	l2	b	h	R	C# [Nm]	⚖
224921-C1	EWN.48-B-M5-RC-C1	47	M5	24	13.5	5.5	7	12	20.5	10	15
224922-C1	EWN.48-B-M6-RC-C1	47	M6	24	13.5	5.5	7	12	20.5	11	14
224952-C1	EWN.55-B-M6-RC-C1	55	M6	28	16	6.5	8	18	21.5	20	24
224953-C1	EWN.55-B-M8-RC-C1	55	M8	28	16	6.5	8	18	21.5	26	23
224983-C1	EWN.63-B-M8-RC-C1	63	M8	32	19	7.5	9	20	22.5	45	33
224984-C1	EWN.63-B-M10-RC-C1	63	M10	32	19	7.5	9	20	22.5	58	32

EWN-SST-RC

Code	Description	D	d6H	L	d1	l2	b	h	R	C# [Nm]	⚖
224956-C1	EWN.55-SST-M8-RC-C1	55	M8	28	16	6.5	8	18	21.5	26	23
224986-C1	EWN.63-SST-M10-RC-C1	63	M10	32	19	7.5	9	20	22.5	58	32

"Max limit Tightening torque" means the max torque value at which the metal insert, in normal conditions of use, is perfectly and strongly anchored to the plastic material.

Conversion Table	
1 mm = 0.039 inch	
D	
mm	inch
47	1.83
55	2.15
63	2.46



EWN-p-RC

METRIC

Code	Description	D	d6g	L	d1	l	l2	b	R	C# [Nm]	⚖
224931-C1	EWN.48-p-M5x16-RC-C1	47	M5	24	13.5	16	5.5	7	20.5	9	15
224932-C1	EWN.48-p-M5x20-RC-C1	47	M5	24	13.5	20	5.5	7	20.5	9	16
224933-C1	EWN.48-p-M5x30-RC-C1	47	M5	24	13.5	30	5.5	7	20.5	9	18
224936-C1	EWN.48-p-M6x16-RC-C1	47	M6	24	13.5	16	5.5	7	20.5	12	16
224937-C1	EWN.48-p-M6x20-RC-C1	47	M6	24	13.5	20	5.5	7	20.5	12	18
224938-C1	EWN.48-p-M6x25-RC-C1	47	M6	24	13.5	25	5.5	7	20.5	12	19
224939-C1	EWN.48-p-M6x30-RC-C1	47	M6	24	13.5	30	5.5	7	20.5	12	21
224961-C1	EWN.55-p-M8x20-RC-C1	55	M8	28	16	20	6.5	8	21.5	22	27
224963-C1	EWN.55-p-M8x30-RC-C1	55	M8	28	16	30	6.5	8	21.5	22	30
224964-C1	EWN.55-p-M8x40-RC-C1	55	M8	28	16	40	6.5	8	21.5	22	33
224966-C1	EWN.55-p-M10x20-RC-C1	55	M10	28	16	20	6.5	8	21.5	25	30
224968-C1	EWN.55-p-M10x30-RC-C1	55	M10	28	16	30	6.5	8	21.5	25	33
224969-C1	EWN.55-p-M10x40-RC-C1	55	M10	28	16	40	6.5	8	21.5	25	36
224991-C1	EWN.63-p-M8x20-RC-C1	63	M8	32	19	20	7.5	9	22.5	32	34
224993-C1	EWN.63-p-M8x30-RC-C1	63	M8	32	19	30	7.5	9	22.5	32	37
224994-C1	EWN.63-p-M8x40-RC-C1	63	M8	32	19	40	7.5	9	22.5	32	39
224997-C1	EWN.63-p-M10x20-RC-C1	63	M10	32	19	20	7.5	9	22.5	48	40
224998-C1	EWN.63-p-M10x30-RC-C1	63	M10	32	19	30	7.5	9	22.5	48	43
224999-C1	EWN.63-p-M10x40-RC-C1	63	M10	32	19	40	7.5	9	22.5	48	52

EWN-SST-p-RC

INOX STAINLESS STEEL

METRIC

Code	Description	D	d6g	L	d1	l	l2	b	R	C# [Nm]	⚖
224942-C1	EWN.48-SST-p-M6x20-RC-C1	47	M6	24	13.5	20	5.5	7	20.5	11	17
224944-C1	EWN.48-SST-p-M6x30-RC-C1	47	M6	24	13.5	30	5.5	7	20.5	11	19
224948-C1	EWN.48-SST-p-M8x20-RC-C1	47	M8	24	13.5	20	5.5	7	20.5	11	20
224949-C1	EWN.48-SST-p-M8x30-RC-C1	47	M8	24	13.5	30	5.5	7	20.5	11	23
224950-C1	EWN.48-SST-p-M8x40-RC-C1	47	M8	24	13.5	40	5.5	7	20.5	11	26
224971-C1	EWN.55-SST-p-M8x20-RC-C1	55	M8	28	16	20	6.5	8	21.5	22	27
224973-C1	EWN.55-SST-p-M8x30-RC-C1	55	M8	28	16	30	6.5	8	21.5	22	30
224974-C1	EWN.55-SST-p-M8x40-RC-C1	55	M8	28	16	40	6.5	8	21.5	22	34
225007-C1	EWN.63-SST-p-M10x20-RC-C1	63	M10	32	19	20	7.5	9	22.5	48	40
225008-C1	EWN.63-SST-p-M10x30-RC-C1	63	M10	32	19	30	7.5	9	22.5	48	44
225009-C1	EWN.63-SST-p-M10x40-RC-C1	63	M10	32	19	40	7.5	9	22.5	48	52

"Max limit Tightening torque" means the max torque value at which the metal insert, in normal conditions of use, is perfectly and strongly anchored to the plastic material.