

TYPES
- Type **P**: with mushroom grip
- Type **L**: with L-grip
- Type **T**: with T-grip

PIN
- AISI 303 stainless steel **A**
- INOX AISI 630 stainless steel **C**
  Precipitation hardening

BALLS
AISI 420C stainless steel

GRIP
Aluminium
Epoxy resin coating
Black, RAL 9005, opaque finish

PRESSURE SPRING
AISI 631 stainless steel
Working temperature between -30°C and +150°C


INFORMATION
GN 113.20 quick release pins are used for the quick fastening of components or workpieces. They are generally used as support pins when frequent disassembly and reassembly is required.
The two balls are released by pressing the spring-loaded button; releasing it locks them again.
The hardened pin of the C version is highly resistant to wear and tensile stress; these characteristics make it suitable for applications involving heavy components.
The technical annex lists the load capacities for double-shear resistance (ultimate strength).

ACCESSORIES
- GN 111.8: retaining cables
- DIN 172: guide bushings (with collar)
- DIN 179: guide bushings (without collar)
- GN 1140: fastening bushings

elesa 9/2026

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.

Ganter Norm




GN 113.20-P

INOX STAINLESS STEEL

Code	Description	$d_{1\ -0.04\ -0.08}$	$l_{1\ +0.6}$	$l_{2\ \pm1}$	Mounting hole H11	d_2	d_3	d_4	l_3	Max. load carrying capacity [kN]	⚖
GN.23603	GN 113.20-5-10-P-A	5	10	6	5	5.5	11.3	20	17.6	14	47
GN.23609	GN 113.20-5-15-P-A	5	15	6	5	5.5	11.3	20	17.6	14	62
GN.23615	GN 113.20-5-20-P-A	5	20	6	5	5.5	11.3	20	17.6	14	102
GN.23621	GN 113.20-5-25-P-A	5	25	6	5	5.5	11.3	20	17.6	14	111
GN.23627	GN 113.20-5-30-P-A	5	30	6	5	5.5	11.3	20	17.6	14	53
GN.23653	GN 113.20-6-10-P-A	6	10	7	6	7	11.3	20	17.6	21	44
GN.23659	GN 113.20-6-15-P-A	6	15	7	6	7	11.3	20	17.6	21	59
GN.23665	GN 113.20-6-20-P-A	6	20	7	6	7	11.3	20	17.6	21	58
GN.23671	GN 113.20-6-25-P-A	6	25	7	6	7	11.3	20	17.6	21	77
GN.23677	GN 113.20-6-30-P-A	6	30	7	6	7	11.3	20	17.6	21	81
GN.23683	GN 113.20-6-35-P-A	6	35	7	6	7	11.3	20	17.6	21	117
GN.23689	GN 113.20-6-40-P-A	6	40	7	6	7	11.3	20	17.6	21	44
GN.23695	GN 113.20-6-45-P-A	6	45	7	6	7	11.3	20	17.6	21	50
GN.23701	GN 113.20-6-50-P-A	6	50	7	6	7	11.3	20	17.6	21	33
GN.23753	GN 113.20-8-20-P-A	8	20	8.2	8	9.5	14.1	25	22.6	38	40
GN.23759	GN 113.20-8-25-P-A	8	25	8.2	8	9.5	14.1	25	22.6	38	38
GN.23765	GN 113.20-8-30-P-A	8	30	8.2	8	9.5	14.1	25	22.6	38	43
GN.23771	GN 113.20-8-35-P-A	8	35	8.2	8	9.5	14.1	25	22.6	38	46
GN.23777	GN 113.20-8-40-P-A	8	40	8.2	8	9.5	14.1	25	22.6	38	22
GN.23783	GN 113.20-8-45-P-A	8	45	8.2	8	9.5	14.1	25	22.6	38	88
GN.23789	GN 113.20-8-50-P-A	8	50	8.2	8	9.5	14.1	25	22.6	38	102
GN.23803	GN 113.20-10-20-P-A	10	20	9.6	10	12	14.1	25	22.6	60	21
GN.23809	GN 113.20-10-25-P-A	10	25	9.6	10	12	14.1	25	22.6	60	22
GN.23815	GN 113.20-10-30-P-A	10	30	9.6	10	12	14.1	25	22.6	60	13
GN.23821	GN 113.20-10-35-P-A	10	35	9.6	10	12	14.1	25	22.6	60	14
GN.23827	GN 113.20-10-40-P-A	10	40	9.6	10	12	14.1	25	22.6	60	90
GN.23833	GN 113.20-10-45-P-A	10	45	9.6	10	12	14.1	25	22.6	60	94
GN.23839	GN 113.20-10-50-P-A	10	50	9.6	10	12	14.1	25	22.6	60	72
GN.23845	GN 113.20-10-60-P-A	10	60	9.6	10	12	14.1	25	22.6	60	20
GN.23853	GN 113.20-12-25-P-A	12	25	10.6	12	14.5	17.7	35	27.3	87	21
GN.23859	GN 113.20-12-30-P-A	12	30	10.6	12	14.5	17.7	35	27.3	87	21
GN.23865	GN 113.20-12-35-P-A	12	35	10.6	12	14.5	17.7	35	27.3	87	16
GN.23871	GN 113.20-12-40-P-A	12	40	10.6	12	14.5	17.7	35	27.3	87	17
GN.23877	GN 113.20-12-45-P-A	12	45	10.6	12	14.5	17.7	35	27.3	87	29
GN.23883	GN 113.20-12-50-P-A	12	50	10.6	12	14.5	17.7	35	27.3	87	24
GN.23889	GN 113.20-12-60-P-A	12	60	10.6	12	14.5	17.7	35	27.3	87	27
GN.23895	GN 113.20-12-70-P-A	12	70	10.6	12	14.5	17.7	35	27.3	87	28

Ganter Norm®

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.




GN 113.20-P

INOX STAINLESS STEEL

Code	Description	$d_{1\ -0.04\ -0.08}$	$l_{1\ +0.6}$	$l_{2\ \pm1}$	Mounting hole H11	d_2	d_3	d_4	l_3	Max. load carrying capacity [kN]	⚖
GN.23901	GN 113.20-12-80-P-A	12	80	10.6	12	14.5	17.7	35	27.3	87	26
GN.23604	GN 113.20-5-10-P-C	5	10	6	5	5.5	11.3	20	17.6	24	47
GN.23610	GN 113.20-5-15-P-C	5	15	6	5	5.5	11.3	20	17.6	24	62
GN.23616	GN 113.20-5-20-P-C	5	20	6	5	5.5	11.3	20	17.6	24	112
GN.23622	GN 113.20-5-25-P-C	5	25	6	5	5.5	11.3	20	17.6	24	53
GN.23628	GN 113.20-5-30-P-C	5	30	6	5	5.5	11.3	20	17.6	24	49
GN.23654	GN 113.20-6-10-P-C	6	10	7	6	7	11.3	20	17.6	35	59
GN.23660	GN 113.20-6-15-P-C	6	15	7	6	7	11.3	20	17.6	35	59
GN.23666	GN 113.20-6-20-P-C	6	20	7	6	7	11.3	20	17.6	35	78
GN.23672	GN 113.20-6-25-P-C	6	25	7	6	7	11.3	20	17.6	35	82
GN.23678	GN 113.20-6-30-P-C	6	30	7	6	7	11.3	20	17.6	35	86
GN.23684	GN 113.20-6-35-P-C	6	35	7	6	7	11.3	20	17.6	35	119
GN.23690	GN 113.20-6-40-P-C	6	40	7	6	7	11.3	20	17.6	35	36
GN.23696	GN 113.20-6-45-P-C	6	45	7	6	7	11.3	20	17.6	35	42
GN.23702	GN 113.20-6-50-P-C	6	50	7	6	7	11.3	20	17.6	35	33
GN.23754	GN 113.20-8-20-P-C	8	20	8.2	8	9.5	14.1	25	22.6	63	39
GN.23760	GN 113.20-8-25-P-C	8	25	8.2	8	9.5	14.1	25	22.6	63	41
GN.23766	GN 113.20-8-30-P-C	8	30	8.2	8	9.5	14.1	25	22.6	63	43
GN.23772	GN 113.20-8-35-P-C	8	35	8.2	8	9.5	14.1	25	22.6	63	38
GN.23778	GN 113.20-8-40-P-C	8	40	8.2	8	9.5	14.1	25	22.6	63	21
GN.23784	GN 113.20-8-45-P-C	8	45	8.2	8	9.5	14.1	25	22.6	63	94
GN.23790	GN 113.20-8-50-P-C	8	50	8.2	8	9.5	14.1	25	22.6	63	20
GN.23804	GN 113.20-10-20-P-C	10	20	9.6	10	12	14.1	25	22.6	100	21
GN.23810	GN 113.20-10-25-P-C	10	25	9.6	10	12	14.1	25	22.6	100	23
GN.23816	GN 113.20-10-30-P-C	10	30	9.6	10	12	14.1	25	22.6	100	21
GN.23822	GN 113.20-10-35-P-C	10	35	9.6	10	12	14.1	25	22.6	100	15
GN.23828	GN 113.20-10-40-P-C	10	40	9.6	10	12	14.1	25	22.6	100	90
GN.23834	GN 113.20-10-45-P-C	10	45	9.6	10	12	14.1	25	22.6	100	92
GN.23840	GN 113.20-10-50-P-C	10	50	9.6	10	12	14.1	25	22.6	100	21
GN.23846	GN 113.20-10-60-P-C	10	60	9.6	10	12	14.1	25	22.6	100	20
GN.23854	GN 113.20-12-25-P-C	12	25	10.6	12	14.5	17.7	35	27.3	144	21
GN.23860	GN 113.20-12-30-P-C	12	30	10.6	12	14.5	17.7	35	27.3	144	23
GN.23866	GN 113.20-12-35-P-C	12	35	10.6	12	14.5	17.7	35	27.3	144	16
GN.23872	GN 113.20-12-40-P-C	12	40	10.6	12	14.5	17.7	35	27.3	144	31
GN.23878	GN 113.20-12-45-P-C	12	45	10.6	12	14.5	17.7	35	27.3	144	38
GN.23884	GN 113.20-12-50-P-C	12	50	10.6	12	14.5	17.7	35	27.3	144	24
GN.23890	GN 113.20-12-60-P-C	12	60	10.6	12	14.5	17.7	35	27.3	144	27
GN.23896	GN 113.20-12-70-P-C	12	70	10.6	12	14.5	17.7	35	27.3	144	19
GN.23902	GN 113.20-12-80-P-C	12	80	10.6	12	14.5	17.7	35	27.3	144	26

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.

Ganter Norm




GN 113.20-L

INOX STAINLESS STEEL

Code	Description	$d_{1\ -0.04\ -0.08}$	$l_{1\ +0.6}$	$l_{2\ \pm1}$	l_5	l_4	Mounting hole H11	d_2	d_3	l_3	Max. load carrying capacity [kN]	⚖
GN.23601	GN 113.20-5-10-L-A	5	10	6	12.6	43.8	5	5.5	11.8	31	14	44
GN.23607	GN 113.20-5-15-L-A	5	15	6	12.6	43.8	5	5.5	11.8	31	14	53
GN.23613	GN 113.20-5-20-L-A	5	20	6	12.6	43.8	5	5.5	11.8	31	14	47
GN.23619	GN 113.20-5-25-L-A	5	25	6	12.6	43.8	5	5.5	11.8	31	14	109
GN.23625	GN 113.20-5-30-L-A	5	30	6	12.6	43.8	5	5.5	11.8	31	14	58
GN.23651	GN 113.20-6-10-L-A	6	10	7	12.6	43.8	6	7	11.8	31	21	50
GN.23657	GN 113.20-6-15-L-A	6	15	7	12.6	43.8	6	7	11.8	31	21	53
GN.23663	GN 113.20-6-20-L-A	6	20	7	12.6	43.8	6	7	11.8	31	21	50
GN.23669	GN 113.20-6-25-L-A	6	25	7	12.6	43.8	6	7	11.8	31	21	75
GN.23675	GN 113.20-6-30-L-A	6	30	7	12.6	43.8	6	7	11.8	31	21	79
GN.23681	GN 113.20-6-35-L-A	6	35	7	12.6	43.8	6	7	11.8	31	21	120
GN.23687	GN 113.20-6-40-L-A	6	40	7	12.6	43.8	6	7	11.8	31	21	49
GN.23693	GN 113.20-6-45-L-A	6	45	7	12.6	43.8	6	7	11.8	31	21	47
GN.23699	GN 113.20-6-50-L-A	6	50	7	12.6	43.8	6	7	11.8	31	21	41
GN.23751	GN 113.20-8-20-L-A	8	20	8.2	15.8	49.7	8	9.5	14.7	35.1	38	48
GN.23757	GN 113.20-8-25-L-A	8	25	8.2	15.8	49.7	8	9.5	14.7	35.1	38	45
GN.23763	GN 113.20-8-30-L-A	8	30	8.2	15.8	49.7	8	9.5	14.7	35.1	38	43
GN.23769	GN 113.20-8-35-L-A	8	35	8.2	15.8	49.7	8	9.5	14.7	35.1	38	36
GN.23775	GN 113.20-8-40-L-A	8	40	8.2	15.8	49.7	8	9.5	14.7	35.1	38	15
GN.23781	GN 113.20-8-45-L-A	8	45	8.2	15.8	49.7	8	9.5	14.7	35.1	38	85
GN.23787	GN 113.20-8-50-L-A	8	50	8.2	15.8	49.7	8	9.5	14.7	35.1	38	100
GN.23801	GN 113.20-10-20-L-A	10	20	9.6	15.8	49.7	10	12	14.7	35.1	60	13
GN.23807	GN 113.20-10-25-L-A	10	25	9.6	15.8	49.7	10	12	14.7	35.1	60	14
GN.23813	GN 113.20-10-30-L-A	10	30	9.6	15.8	49.7	10	12	14.7	35.1	60	21
GN.23819	GN 113.20-10-35-L-A	10	35	9.6	15.8	49.7	10	12	14.7	35.1	60	22
GN.23825	GN 113.20-10-40-L-A	10	40	9.6	15.8	49.7	10	12	14.7	35.1	60	73
GN.23831	GN 113.20-10-45-L-A	10	45	9.6	15.8	49.7	10	12	14.7	35.1	60	89
GN.23837	GN 113.20-10-50-L-A	10	50	9.6	15.8	49.7	10	12	14.7	35.1	60	70
GN.23843	GN 113.20-10-60-L-A	10	60	9.6	15.8	49.7	10	12	14.7	35.1	60	12
GN.23851	GN 113.20-12-25-L-A	12	25	10.6	20.2	57.1	12	14.5	18.2	34.4	87	19
GN.23857	GN 113.20-12-30-L-A	12	30	10.6	20.2	57.1	12	14.5	18.2	34.4	87	15
GN.23863	GN 113.20-12-35-L-A	12	35	10.6	20.2	57.1	12	14.5	18.2	34.4	87	24
GN.23869	GN 113.20-12-40-L-A	12	40	10.6	20.2	57.1	12	14.5	18.2	34.4	87	25
GN.23875	GN 113.20-12-45-L-A	12	45	10.6	20.2	57.1	12	14.5	18.2	34.4	87	31
GN.23881	GN 113.20-12-50-L-A	12	50	10.6	20.2	57.1	12	14.5	18.2	34.4	87	37
GN.23887	GN 113.20-12-60-L-A	12	60	10.6	20.2	57.1	12	14.5	18.2	34.4	87	20
GN.23893	GN 113.20-12-70-L-A	12	70	10.6	20.2	57.1	12	14.5	18.2	34.4	87	26

Ganter Norm®

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.




GN 113.20-L

INOX STAINLESS STEEL

Code	Description	$d_{1\ -0.04\ -0.08}$	$l_{1\ +0.6}$	$l_{2\ \pm1}$	l_5	l_4	Mounting hole H11	d_2	d_3	l_3	Max. load carrying capacity [kN]	⚖
GN.23899	GN 113.20-12-80-L-A	12	80	10.6	20.2	57.1	12	14.5	18.2	34.4	87	27
GN.23602	GN 113.20-5-10-L-C	5	10	6	12.6	43.8	5	5.5	11.8	31	14	44
GN.23608	GN 113.20-5-15-L-C	5	15	6	12.6	43.8	5	5.5	11.8	31	14	53
GN.23614	GN 113.20-5-20-L-C	5	20	6	12.6	43.8	5	5.5	11.8	31	14	56
GN.23620	GN 113.20-5-25-L-C	5	25	6	12.6	43.8	5	5.5	11.8	31	14	111
GN.23626	GN 113.20-5-30-L-C	5	30	6	12.6	43.8	5	5.5	11.8	31	14	53
GN.23652	GN 113.20-6-10-L-C	6	10	7	12.6	43.8	6	7	11.8	31	21	44
GN.23658	GN 113.20-6-15-L-C	6	15	7	12.6	43.8	6	7	11.8	31	21	67
GN.23664	GN 113.20-6-20-L-C	6	20	7	12.6	43.8	6	7	11.8	31	21	50
GN.23670	GN 113.20-6-25-L-C	6	25	7	12.6	43.8	6	7	11.8	31	21	77
GN.23676	GN 113.20-6-30-L-C	6	30	7	12.6	43.8	6	7	11.8	31	21	81
GN.23682	GN 113.20-6-35-L-C	6	35	7	12.6	43.8	6	7	11.8	31	21	117
GN.23688	GN 113.20-6-40-L-C	6	40	7	12.6	43.8	6	7	11.8	31	21	44
GN.23694	GN 113.20-6-45-L-C	6	45	7	12.6	43.8	6	7	11.8	31	21	50
GN.23700	GN 113.20-6-50-L-C	6	50	7	12.6	43.8	6	7	11.8	31	21	41
GN.23752	GN 113.20-8-20-L-C	8	20	8.2	15.8	49.7	8	9.5	14.7	35.1	38	48
GN.23758	GN 113.20-8-25-L-C	8	25	8.2	15.8	49.7	8	9.5	14.7	35.1	38	46
GN.23764	GN 113.20-8-30-L-C	8	30	8.2	15.8	49.7	8	9.5	14.7	35.1	38	35
GN.23770	GN 113.20-8-35-L-C	8	35	8.2	15.8	49.7	8	9.5	14.7	35.1	38	45
GN.23776	GN 113.20-8-40-L-C	8	40	8.2	15.8	49.7	8	9.5	14.7	35.1	38	15
GN.23782	GN 113.20-8-45-L-C	8	45	8.2	15.8	49.7	8	9.5	14.7	35.1	38	85
GN.23788	GN 113.20-8-50-L-C	8	50	8.2	15.8	49.7	8	9.5	14.7	35.1	38	100
GN.23802	GN 113.20-10-20-L-C	10	20	9.6	15.8	49.7	10	12	14.7	35.1	60	13
GN.23808	GN 113.20-10-25-L-C	10	25	9.6	15.8	49.7	10	12	14.7	35.1	60	22
GN.23814	GN 113.20-10-30-L-C	10	30	9.6	15.8	49.7	10	12	14.7	35.1	60	13
GN.23820	GN 113.20-10-35-L-C	10	35	9.6	15.8	49.7	10	12	14.7	35.1	60	14
GN.23826	GN 113.20-10-40-L-C	10	40	9.6	15.8	49.7	10	12	14.7	35.1	60	70
GN.23832	GN 113.20-10-45-L-C	10	45	9.6	15.8	49.7	10	12	14.7	35.1	60	94
GN.23838	GN 113.20-10-50-L-C	10	50	9.6	15.8	49.7	10	12	14.7	35.1	60	72
GN.23844	GN 113.20-10-60-L-C	10	60	9.6	15.8	49.7	10	12	14.7	35.1	60	20
GN.23852	GN 113.20-12-25-L-C	12	25	10.6	20.2	57.1	12	14.5	18.2	34.4	87	19
GN.23858	GN 113.20-12-30-L-C	12	30	10.6	20.2	57.1	12	14.5	18.2	34.4	87	29
GN.23864	GN 113.20-12-35-L-C	12	35	10.6	20.2	57.1	12	14.5	18.2	34.4	87	24
GN.23870	GN 113.20-12-40-L-C	12	40	10.6	20.2	57.1	12	14.5	18.2	34.4	87	25
GN.23876	GN 113.20-12-45-L-C	12	45	10.6	20.2	57.1	12	14.5	18.2	34.4	87	29
GN.23882	GN 113.20-12-50-L-C	12	50	10.6	20.2	57.1	12	14.5	18.2	34.4	87	17
GN.23888	GN 113.20-12-60-L-C	12	60	10.6	20.2	57.1	12	14.5	18.2	34.4	87	20
GN.23894	GN 113.20-12-70-L-C	12	70	10.6	20.2	57.1	12	14.5	18.2	34.4	87	26
GN.23900	GN 113.20-12-80-L-C	12	80	10.6	20.2	57.1	12	14.5	18.2	34.4	87	26

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.

Ganter Norm




GN 113.20-T

INOX STAINLESS STEEL

Code	Description	$d_{1\ -0.04\ -0.08}$	$l_{1\ +0.6}$	$l_{2\ \pm1}$	l_5	l_4	Mounting hole H11	d_2	d_3	l_3	Max. load carrying capacity [kN]	⚖
GN.23605	GN 113.20-5-10-T-A	5	10	6	12.6	45.2	5	5.5	11.8	31.3	14	38
GN.23611	GN 113.20-5-15-T-A	5	15	6	12.6	45.2	5	5.5	11.8	31.3	14	67
GN.23617	GN 113.20-5-20-T-A	5	20	6	12.6	45.2	5	5.5	11.8	31.3	14	112
GN.23623	GN 113.20-5-25-T-A	5	25	6	12.6	45.2	5	5.5	11.8	31.3	14	56
GN.23629	GN 113.20-5-30-T-A	5	30	6	12.6	45.2	5	5.5	11.8	31.3	14	36
GN.23655	GN 113.20-6-10-T-A	6	10	7	12.6	45.2	6	7	11.8	31.3	21	59
GN.23661	GN 113.20-6-15-T-A	6	15	7	12.6	45.2	6	7	11.8	31.3	21	68
GN.23667	GN 113.20-6-20-T-A	6	20	7	12.6	45.2	6	7	11.8	31.3	21	78
GN.23673	GN 113.20-6-25-T-A	6	25	7	12.6	45.2	6	7	11.8	31.3	21	82
GN.23679	GN 113.20-6-30-T-A	6	30	7	12.6	45.2	6	7	11.8	31.3	21	86
GN.23685	GN 113.20-6-35-T-A	6	35	7	12.6	45.2	6	7	11.8	31.3	21	119
GN.23691	GN 113.20-6-40-T-A	6	40	7	12.6	45.2	6	7	11.8	31.3	21	38
GN.23697	GN 113.20-6-45-T-A	6	45	7	12.6	45.2	6	7	11.8	31.3	21	50
GN.23703	GN 113.20-6-50-T-A	6	50	7	12.6	45.2	6	7	11.8	31.3	21	40
GN.23755	GN 113.20-8-20-T-A	8	20	8.2	15.8	51.5	8	9.5	14.7	35.4	38	39
GN.23761	GN 113.20-8-25-T-A	8	25	8.2	15.8	51.5	8	9.5	14.7	35.4	38	41
GN.23767	GN 113.20-8-30-T-A	8	30	8.2	15.8	51.5	8	9.5	14.7	35.4	38	45
GN.23773	GN 113.20-8-35-T-A	8	35	8.2	15.8	51.5	8	9.5	14.7	35.4	38	47
GN.23779	GN 113.20-8-40-T-A	8	40	8.2	15.8	51.5	8	9.5	14.7	35.4	38	83
GN.23785	GN 113.20-8-45-T-A	8	45	8.2	15.8	51.5	8	9.5	14.7	35.4	38	103
GN.23791	GN 113.20-8-50-T-A	8	50	8.2	15.8	51.5	8	9.5	14.7	35.4	38	22
GN.23805	GN 113.20-10-20-T-A	10	20	9.6	15.8	51.5	10	12	14.7	35.4	60	22
GN.23811	GN 113.20-10-25-T-A	10	25	9.6	15.8	51.5	10	12	14.7	35.4	60	23
GN.23817	GN 113.20-10-30-T-A	10	30	9.6	15.8	51.5	10	12	14.7	35.4	60	21
GN.23823	GN 113.20-10-35-T-A	10	35	9.6	15.8	51.5	10	12	14.7	35.4	60	23
GN.23829	GN 113.20-10-40-T-A	10	40	9.6	15.8	51.5	10	12	14.7	35.4	60	88
GN.23835	GN 113.20-10-45-T-A	10	45	9.6	15.8	51.5	10	12	14.7	35.4	60	92
GN.23841	GN 113.20-10-50-T-A	10	50	9.6	15.8	51.5	10	12	14.7	35.4	60	21
GN.23847	GN 113.20-10-60-T-A	10	60	9.6	15.8	51.5	10	12	14.7	35.4	60	12
GN.23855	GN 113.20-12-25-T-A	12	25	10.6	20.2	59.1	12	14.5	18.2	34.7	87	22
GN.23861	GN 113.20-12-30-T-A	12	30	10.6	20.2	59.1	12	14.5	18.2	34.7	87	29
GN.23867	GN 113.20-12-35-T-A	12	35	10.6	20.2	59.1	12	14.5	18.2	34.7	87	23
GN.23873	GN 113.20-12-40-T-A	12	40	10.6	20.2	59.1	12	14.5	18.2	34.7	87	39
GN.23879	GN 113.20-12-45-T-A	12	45	10.6	20.2	59.1	12	14.5	18.2	34.7	87	38
GN.23885	GN 113.20-12-50-T-A	12	50	10.6	20.2	59.1	12	14.5	18.2	34.7	87	26
GN.23891	GN 113.20-12-60-T-A	12	60	10.6	20.2	59.1	12	14.5	18.2	34.7	87	29
GN.23897	GN 113.20-12-70-T-A	12	70	10.6	20.2	59.1	12	14.5	18.2	34.7	87	19

Ganter Norm®

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.



GN 113.20-T

INOX STAINLESS STEEL

Code	Description	d_1 -0.04 -0.08	l_1 +0.6	l_2 ±1	l_5	l_4	Mounting hole H11	d_2	d_3	l_3	Max. load carrying capacity [kN]	⚖
GN.23903	GN 113.20-12-80-T-A	12	80	10.6	20.2	59.1	12	14.5	18.2	34.7	87	18
GN.23606	GN 113.20-5-10-T-C	5	10	6	12.6	45.2	5	5.5	11.8	31.3	14	62
GN.23612	GN 113.20-5-15-T-C	5	15	6	12.6	45.2	5	5.5	11.8	31.3	14	47
GN.23618	GN 113.20-5-20-T-C	5	20	6	12.6	45.2	5	5.5	11.8	31.3	14	109
GN.23624	GN 113.20-5-25-T-C	5	25	6	12.6	45.2	5	5.5	11.8	31.3	14	56
GN.23630	GN 113.20-5-30-T-C	5	30	6	12.6	45.2	5	5.5	11.8	31.3	14	42
GN.23656	GN 113.20-6-10-T-C	6	10	7	12.6	45.2	6	7	11.8	31.3	21	62
GN.23662	GN 113.20-6-15-T-C	6	15	7	12.6	45.2	6	7	11.8	31.3	21	68
GN.23668	GN 113.20-6-20-T-C	6	20	7	12.6	45.2	6	7	11.8	31.3	21	75
GN.23674	GN 113.20-6-25-T-C	6	25	7	12.6	45.2	6	7	11.8	31.3	21	79
GN.23680	GN 113.20-6-30-T-C	6	30	7	12.6	45.2	6	7	11.8	31.3	21	120
GN.23686	GN 113.20-6-35-T-C	6	35	7	12.6	45.2	6	7	11.8	31.3	21	56
GN.23692	GN 113.20-6-40-T-C	6	40	7	12.6	45.2	6	7	11.8	31.3	21	47
GN.23698	GN 113.20-6-45-T-C	6	45	7	12.6	45.2	6	7	11.8	31.3	21	35
GN.23704	GN 113.20-6-50-T-C	6	50	7	12.6	45.2	6	7	11.8	31.3	21	47
GN.23756	GN 113.20-8-20-T-C	8	20	8.2	15.8	51.5	8	9.5	14.7	35.4	38	45
GN.23762	GN 113.20-8-25-T-C	8	25	8.2	15.8	51.5	8	9.5	14.7	35.4	38	43
GN.23768	GN 113.20-8-30-T-C	8	30	8.2	15.8	51.5	8	9.5	14.7	35.4	38	36
GN.23774	GN 113.20-8-35-T-C	8	35	8.2	15.8	51.5	8	9.5	14.7	35.4	38	22
GN.23780	GN 113.20-8-40-T-C	8	40	8.2	15.8	51.5	8	9.5	14.7	35.4	38	83
GN.23786	GN 113.20-8-45-T-C	8	45	8.2	15.8	51.5	8	9.5	14.7	35.4	38	103
GN.23792	GN 113.20-8-50-T-C	8	50	8.2	15.8	51.5	8	9.5	14.7	35.4	38	22
GN.23806	GN 113.20-10-20-T-C	10	20	9.6	15.8	51.5	10	12	14.7	35.4	60	14
GN.23812	GN 113.20-10-25-T-C	10	25	9.6	15.8	51.5	10	12	14.7	35.4	60	22
GN.23818	GN 113.20-10-30-T-C	10	30	9.6	15.8	51.5	10	12	14.7	35.4	60	22
GN.23824	GN 113.20-10-35-T-C	10	35	9.6	15.8	51.5	10	12	14.7	35.4	60	73
GN.23830	GN 113.20-10-40-T-C	10	40	9.6	15.8	51.5	10	12	14.7	35.4	60	89
GN.23836	GN 113.20-10-45-T-C	10	45	9.6	15.8	51.5	10	12	14.7	35.4	60	94
GN.23842	GN 113.20-10-50-T-C	10	50	9.6	15.8	51.5	10	12	14.7	35.4	60	12
GN.23848	GN 113.20-10-60-T-C	10	60	9.6	15.8	51.5	10	12	14.7	35.4	60	12
GN.23856	GN 113.20-12-25-T-C	12	25	10.6	20.2	59.1	12	14.5	18.2	34.7	87	22
GN.23862	GN 113.20-12-30-T-C	12	30	10.6	20.2	59.1	12	14.5	18.2	34.7	87	21
GN.23868	GN 113.20-12-35-T-C	12	35	10.6	20.2	59.1	12	14.5	18.2	34.7	87	23
GN.23874	GN 113.20-12-40-T-C	12	40	10.6	20.2	59.1	12	14.5	18.2	34.7	87	39
GN.23880	GN 113.20-12-45-T-C	12	45	10.6	20.2	59.1	12	14.5	18.2	34.7	87	37
GN.23886	GN 113.20-12-50-T-C	12	50	10.6	20.2	59.1	12	14.5	18.2	34.7	87	29
GN.23892	GN 113.20-12-60-T-C	12	60	10.6	20.2	59.1	12	14.5	18.2	34.7	87	28
GN.23898	GN 113.20-12-70-T-C	12	70	10.6	20.2	59.1	12	14.5	18.2	34.7	87	27
GN.23904	GN 113.20-12-80-T-C	12	80	10.6	20.2	59.1	12	14.5	18.2	34.7	87	18

Models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings and photos.

Ganter Norm