




MAIN SPECIFICATIONS

Aluminium
- Epoxy resin coating,
black, RAL 9005, textured finish **SW**
- Plain, matte shot-blasted **BL**
Grub screw DIN 913
Stainless Steel AISI 304

FEATURES AND APPLICATIONS

The clamping bore of base plate connector clamps GN 162.8 is not machined and designed for GN 990 (see page -).
At the screw location **z** a grub screw reduces the bore cross-section for clamping.



Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
10	0.39
12	0.47
14	0.55
15	0.59
16	0.62
18	0.70

METRIC

Code	Description	d1	d2	k	l	t	z	x1	x2	y1	y2	Δ
GN.48371	GN 162.8-B10-3-BL	B 10	5.5	32	25	6	M6-6	40	28	40	28	52
GN.48372	GN 162.8-B10-3-SW	B 10	5.5	32	25	6	M6-6	40	28	40	28	52
GN.48373	GN 162.8-B12-3-BL	B 12	5.5	32	25	6	M6-6	40	28	40	28	50
GN.48374	GN 162.8-B12-3-SW	B 12	5.5	32	25	6	M6-6	40	28	40	28	50
GN.48375	GN 162.8-B14-3-BL	B 14	5.5	32	25	6	M6-6	40	28	40	28	48
GN.48376	GN 162.8-B14-3-SW	B 14	5.5	32	25	6	M6-6	40	28	40	28	48
GN.48377	GN 162.8-B15-3-BL	B 15	5.5	32	25	6	M6-6	40	28	40	28	47
GN.48378	GN 162.8-B15-3-SW	B 15	5.5	32	25	6	M6-6	40	28	40	28	47
GN.48379	GN 162.8-B16-3-BL	B 16	5.5	32	25	6	M6-6	40	28	40	28	42
GN.48380	GN 162.8-B16-3-SW	B 16	5.5	32	25	6	M6-6	40	28	40	28	42
GN.48381	GN 162.8-B18-3-BL	B 18	5.5	32	25	6	M6-6	40	28	40	28	38
GN.48382	GN 162.8-B18-3-SW	B 18	5.5	32	25	6	M6-6	40	28	40	28	38