



MATERIAL


Stainless steel, matte finish.
AISI 304 stainless steel screws and nuts.
Polyamide based (PA) or polytetrafluoroethylene based (PTFE) techno-
polymer sliding bushing (d1).

FEATURES AND APPLICATIONS

GN 131.1-NI connecting clamps can normally be matched with the
linear actuators.
By clamping the guide hole d1 it is possible to adjust the actuator
positioning and to lock the slider after having set up the final position.
The clamping screws d3 may be replaced by clamping kits GN 911
(see page 1958).



Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
18	0.71



Code	Description	d1##	d2#	d3	d4	k	l	m	d3	⚖
									Clamping kit	
GN.42213	GN 131.1-G18-B18-2-NI	18	18	M6	M3	25	64	20	GN 911-M6-22	142

Hole without sliding bushing.
Hole with sliding bushing.