

# GN 227.7 | Spoked handwheels

for valves, pressed steel



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

## SPECIFICATION

Pressed steel  
 cathodic dip coated (KTL)  
 black, RAL 9005 **SWK**  
 red, RAL 3000, matte **RTK**  
 Hub  
 Steel, welded

## FEATURES AND APPLICATIONS


Pressed steel handwheels GN 227.7 feature high mechanical strength and a coating for increased corrosion resistance. They are also not affected by shock and knocks. The conical square hole allows easy installation and firm seating on a spindle. The cast shape prevents injuries from sharp edges during handling. The engraved labels "SHUT" and "OPEN" help with safe and correct operation of the valves.

## ON REQUEST

with bore B  
 with square V  
 neutral, no labeling



Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
125	4.92
150	5.91
200	7.87
250	9.84
300	11.81
400	15.75



**METRIC**

Code	Description	d1	d2	s1	s2	l1	l2±1	Spokes no.	Sheet metal thickness	⚖
GN.23501	GN 227.7-125-VK11-RTK	125	28	11	12.7	17	31	3	1.2	240
GN.23506	GN 227.7-125-VK11-SWK	125	28	11	12.7	17	31	3	1.2	240
GN.23511	GN 227.7-150-VK12-RTK	150	30	12	13.8	18	33.5	3	1.5	360
GN.23516	GN 227.7-150-VK12-SWK	150	30	12	13.8	18	33.5	3	1.5	360
GN.23521	GN 227.7-200-VK14-RTK	200	35	14	16	20	40.5	3	2	750
GN.23526	GN 227.7-200-VK14-SWK	200	35	14	16	20	40.5	3	2	750
GN.23531	GN 227.7-250-VK17-RTK	250	36	17	19.25	23	47	4	2	1100
GN.23536	GN 227.7-250-VK17-SWK	250	36	17	19.25	23	47	4	2	1100
GN.23541	GN 227.7-300-VK19-RTK	300	42	19	21.8	28	59	5	2	1600
GN.23546	GN 227.7-300-VK19-SWK	300	42	19	21.8	28	59	5	2	1600
GN.23551	GN 227.7-400-VK24-RTK	400	48	24	27	30	66	5	2.5	3100
GN.23556	GN 227.7-400-VK24-SWK	400	48	24	27	30	66	5	2.5	3100

Handwheels and crank handles