



SHAFT ADAPTER

Black-oxide steel.

Complete with key and shaft clamping screw.

LOCKING BASE

Anodised aluminium, black colour.



Complete with shaft locking dowel.

FEATURES AND APPLICATIONS



GN 295 installation kits allow the installation on position indicators DD52R (see page 764) and DD51 (see page 758) on linear actuators. An installation kit includes one shaft adapter and one locking base.



Execution for linear actuators ø18, 30, 40, 50



Execution for linear actuator ø60



Conversion Table 1 mm = 0.039 inch	
d1	
mm	inch
18	0.71
30	1.18
40	1.57
50	1.97
60	2.36

METRIC

Code	Description	d1	d2 H7/H7	d3	b	l1	l2	l3	r1	r2	s	Position indicator	△
GN.67301	GN 295-18-6-30	18	6	14	35	30	16	4.5	24.5	17.5	8	DD51	50
GN.67306	GN 295-30-8-35	30	8	14	35	35	15	-	24.5	17.5	10	DD51	60
GN.67311	GN 295-40-12-39	40	12	20	47	40	16	-	32	24.5	10	DD52R	120
GN.67316	GN 295-50-12-39	50	12	20	58	40	17	-	32	29	10	DD52R	118
GN.67321	GN 295-60-14-44	60	14	20	-	39	18	-	-	32	7	DD52R	150