



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

## MATERIAL

Hardened steel (60 ±2 HRC).

## FEATURES AND APPLICATIONS

GN 172.1 guide bushings feature a tapered hole to optimise the use with indexing plungers GN 817.5 (see page 881).



Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
6	0.24
8	0.31
10	0.39

## METRIC

Code	Description	d1	d2 n6	d3	d4*	l	⚖
GN.51001	GN 172.1-6-10	6	10	12.5	13.5	8	4
GN.51011	GN 172.1-8-12	8	12	15	16	10	7
GN.51021	GN 172.1-10-15	10	15	19	20.6	12	12