





MATERIAL
Die-cast zinc alloy.

STANDARD EXECUTIONS
Zinc-plated steel countersunk head screws for handle fastening.
- **GN 181-SR:** epoxy resin coating, RAL 9006 grey colour, matte finish.
- **GN 181-SW:** epoxy resin coating, RAL 9005 black colour, matte finish.

FEATURES AND APPLICATIONS
GN 181 handle fastening kit is composed of 2 plates and 2 countersunk head screws.
A suitable positioning of the fixing plates of the handle allows to realise compensation of different hole centre distances.
GN 181 fastening kit allows to turn a handle with a threaded blind hole for rear mounting into a handle for front mounting.



Conversion Table			
1 mm = 0.039 inch			
d1			
mm	inch	mm	inch
8	0.31	20	0.79
10	0.39	26	1.02
12	0.47	28	1.10
16	0.63		

METRIC

Code	Description	l	d1	d2	d3 +0.2 +0.5	b	s	t	m	Screws	For handle	⚖
GN.31201	GN 181-ZD-8-M4-SR	20	8	M4	4	10	3	7	10	M4x10	GN 425-8	4
GN.31202	GN 181-ZD-8-M4-SW	20	8	M4	4	10	3	7	10	M4x10	GN 425-8	4
GN.31203	GN 181-ZD-10-M5-SR	24	10	M5	5	12	4	8	12	M5x12	GN 425-10 / GN 425.1-10	8
GN.31204	GN 181-ZD-10-M5-SW	24	10	M5	5	12	4	8	12	M5x12	GN 425-10 / GN 425.1-10	8
GN.31205	GN 181-ZD-12-M6-SR	30	12	M6	6	15	4.5	9.5	15	M6x14	GN 425-12 / GN 425.1-12	14
GN.31206	GN 181-ZD-12-M6-SW	30	12	M6	6	15	4.5	9.5	15	M6x14	GN 425-12 / GN 425.1-12	14
GN.31207	GN 181-ZD-16-M6-SR	34	16	M6	6	18	4.5	9.5	16	M6x14	GN 425-16	22
GN.31208	GN 181-ZD-16-M6-SW	34	16	M6	6	18	4.5	9.5	16	M6x14	GN 425-16	22
GN.31209	GN 181-ZD-20-M6-SR	40	20	M6	6	22	4.5	9.5	18	M6x14	GN 565-20 / GN 565.5-20	35
GN.31210	GN 181-ZD-20-M6-SW	40	20	M6	6	22	4.5	9.5	18	M6x14	GN 565-20 / GN 565.5-20	35
GN.31211	GN 181-ZD-20-M8-SR	42	20	M8	8	22	6	12	20	M8x18	GN 426-20 / GN 426.1-20	42
GN.31212	GN 181-ZD-20-M8-SW	42	20	M8	8	22	6	12	20	M8x18	GN 426-20 / GN 426.1-20	42
GN.31213	GN 181-ZD-26-M8-SR	52	26	M8	8	28	6	12	24	M8x18	GN 565-26	78
GN.31214	GN 181-ZD-26-M8-SW	52	26	M8	8	28	6	12	24	M8x18	GN 565-26	78
GN.31215	GN 181-ZD-28-M10-SR	56	28	M10	10	30	6.5	13.5	26	M10x20	GN 426-28 / GN 426.1-28	88
GN.31216	GN 181-ZD-28-M10-SW	56	28	M10	10	30	6.5	13.5	26	M10x20	GN 426-28 / GN 426.1-28	88