



MATERIAL

Die-cast zinc alloy, epoxy resin coating, black colour, matte finish.

FEATURES AND APPLICATIONS

GN 416.1 positioning flanges are very useful accessories for optimal positioning of indexing plungers GN 416 (see page 914).



Conversion Table	
1 mm = 0.039 inch	
b1	
mm	inch
38	1.50
46	1.81

METRIC

Code	Description	d+0.15-0.05	b1	b2	b3	b4	h1	h2	k1	k2	k3	⚖️
GN.27861	GN 416.1-6-38	6.2	38	28	16	5.4	8.5	6	27	5.5	17	51
GN.27863	GN 416.1-8-38	8.2	38	28	16	5.4	8.5	6	27	5.5	17	47
GN.27864	GN 416.1-8-46	8.2	46	38	20	6.4	11	6	33	6.5	25	94
GN.27866	GN 416.1-10-38	10.2	38	28	16	5.4	8.5	6	27	5.5	17	96
GN.27867	GN 416.1-10-46	10.2	46	38	20	6.4	11	6	33	6.5	25	87
GN.27869	GN 416.1-12-46	12.2	46	38	20	6.4	11	6	33	6.5	25	79

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8**
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

Indexing and positioning elements