



SPECIFICATION

Stainless steel **NI**
AISI 304
matte shot-blasted



FEATURES AND APPLICATIONS

Stainless Steel-Cabinet U-handles GN 435.3, tall design, are made from bent round profiles and are fastened by welding. They are designed for applications requiring more height for gripping. For example, this makes it possible to grab or hold the handle while wearing safety gloves.

The holes d2 serve, if necessary, for inserting dowel pins or guide pins that provide a simple method for positioning and fixing the cabinet U-handle in place via the alignment holes in the opposing part for the welding process.

ON REQUEST

- other dimensions
- other materials



Conversion Table	
1 mm = 0.039 inch	
mm	inch
125	4.88
160	6.24
200	7.80
300	11.7

Code	Description	d1	l±0.5	d2 H12	h	r	t	⚖
GN.63607	GN 435.3-12-125-75-NI	12	125	4	75	14	6	214
GN.63608	GN 435.3-12-125-110-NI	12	125	4	110	14	6	230
GN.63617	GN 435.3-12-160-75-NI	12	160	4	75	14	6	245
GN.63618	GN 435.3-12-160-110-NI	12	160	4	110	14	6	260
GN.63627	GN 435.3-12-200-75-NI	12	200	4	75	14	6	281
GN.63628	GN 435.3-12-200-110-NI	12	200	4	110	14	6	297
GN.63637	GN 435.3-16-160-85-NI	16	160	4	85	18	6	277
GN.63638	GN 435.3-16-160-125-NI	16	160	4	125	18	6	290
GN.63647	GN 435.3-16-200-85-NI	16	200	4	85	18	6	308
GN.63648	GN 435.3-16-200-125-NI	16	200	4	125	18	6	325
GN.63657	GN 435.3-16-300-85-NI	16	300	4	85	18	6	344
GN.63658	GN 435.3-16-300-125-NI	16	300	4	125	18	6	369