

BASE WITH HOLES FOR GROUND MOUNTING

AISI 316L stainless steel, turned finish.

THREADED STEM

AISI 316L stainless steel

STANDARD EXECUTIONS

- **GN 24-D0-SK**: without no-slip disk, with adjusting hexagon
- **GN 24-D0-TK**: without no-slip disk, with milled flat faces at the base
- **GN 24-D1-SK**: with no-slip disk, with adjusting hexagon
- **GN 24-D1-TK**: with no-slip disk, with milled flat faces at the base

HEX NUT ISO 4032

Stainless steel

MOUNTING SCREW

Stainless steel

NO-SLIP DISK

Acrylonitrile butadiene rubber (NBR)

- Black colour
- Hardness 70 Shore A
- Mounted


FEATURES

GN 24 levelling feet are particularly suitable for use in aggressive environments.

They are supplied assembled and cannot be disassembled.



GN 24-D0-SK




Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
100	3.90
120	4.68

GN 24-D0-SK

Code	Description	d1	d2	h1	h3	l1	k	sw1	Static load [KN]	⚖
GN.80861	GN 24-100-M8-40-D0-SK	100	M 8	9	20.5	40	70.5	17	6	446
GN.80863	GN 24-100-M8-50-D0-SK	100	M 8	9	20.5	50	70.5	17	6	450
GN.80865	GN 24-100-M8-63-D0-SK	100	M 8	9	20.5	63	70.5	17	6	455
GN.80871	GN 24-100-M10-50-D0-SK	100	M 10	9	20.5	50	70.5	17	11	466
GN.80873	GN 24-100-M10-60-D0-SK	100	M 10	9	20.5	60	70.5	17	11	472
GN.80875	GN 24-100-M10-80-D0-SK	100	M 10	9	20.5	80	70.5	17	11	484
GN.80877	GN 24-100-M10-100-D0-SK	100	M 10	9	20.5	100	70.5	17	11	496
GN.80881	GN 24-100-M12-60-D0-SK	100	M 12	9	20.5	60	70.5	17	16	494
GN.80883	GN 24-100-M12-80-D0-SK	100	M 12	9	20.5	80	70.5	17	16	511
GN.80885	GN 24-100-M12-100-D0-SK	100	M 12	9	20.5	100	70.5	17	16	529
GN.80887	GN 24-100-M12-125-D0-SK	100	M 12	9	20.5	125	70.5	17	16	551




Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
100	3.90
120	4.68




GN 24-D1-SK

INOX STAINLESS STEEL METRIC

Code	Description	d1	d2	h1	h2	h3	l1	k	sw1	Static load [kN]	⚖️
GN.80862	GN 24-100-M8-40-D1-SK	100	M 8	9	3	20.5	40	70.5	17	6	484
GN.80864	GN 24-100-M8-50-D1-SK	100	M 8	9	3	20.5	50	70.5	17	6	488
GN.80866	GN 24-100-M8-63-D1-SK	100	M 8	9	3	20.5	63	70.5	17	6	493
GN.80872	GN 24-100-M10-50-D1-SK	100	M 10	9	3	20.5	50	70.5	17	11	504
GN.80874	GN 24-100-M10-60-D1-SK	100	M 10	9	3	20.5	60	70.5	17	11	511
GN.80876	GN 24-100-M10-80-D1-SK	100	M 10	9	3	20.5	80	70.5	17	11	523
GN.80878	GN 24-100-M10-100-D1-SK	100	M 10	9	3	20.5	100	70.5	17	11	535
GN.80882	GN 24-100-M12-60-D1-SK	100	M 12	9	3	20.5	60	70.5	17	16	532
GN.80884	GN 24-100-M12-80-D1-SK	100	M 12	9	3	20.5	80	70.5	17	16	550
GN.80886	GN 24-100-M12-100-D1-SK	100	M 12	9	3	20.5	100	70.5	17	16	568
GN.80888	GN 24-100-M12-125-D1-SK	100	M 12	9	3	20.5	125	70.5	17	16	590



Conversion Table 1 mm = 0.039 inch	
d1	
mm	inch
100	3.90
120	4.68




GN 24-D0-TK

INOX STAINLESS STEEL METRIC

Code	Description	d1	d2	h1	h4	l1	k	sw2	Static load [kN]	⚖
GN.80891	GN 24-100-M16-75-D0-TK	100	M 16	9	26.5	75	70.5	12	17	587
GN.80893	GN 24-100-M16-100-D0-TK	100	M 16	9	26.5	100	70.5	12	17	626
GN.80895	GN 24-100-M16-125-D0-TK	100	M 16	9	26.5	125	70.5	12	17	666
GN.80897	GN 24-100-M16-150-D0-TK	100	M 16	9	26.5	150	70.5	12	17	705
GN.80899	GN 24-100-M16-200-D0-TK	100	M 16	9	26.5	200	70.5	12	17	783
GN.80901	GN 24-100-M16-250-D0-TK	100	M 16	9	26.5	250	70.5	12	17	862
GN.80911	GN 24-100-M20-75-D0-TK	100	M 20	9	28	75	70.5	15	28	698
GN.80913	GN 24-100-M20-100-D0-TK	100	M 20	9	28	100	70.5	15	28	760
GN.80915	GN 24-100-M20-125-D0-TK	100	M 20	9	28	125	70.5	15	28	821
GN.80917	GN 24-100-M20-150-D0-TK	100	M 20	9	28	150	70.5	15	28	882
GN.80919	GN 24-100-M20-200-D0-TK	100	M 20	9	28	200	70.5	15	28	1005
GN.80921	GN 24-100-M20-250-D0-TK	100	M 20	9	28	250	70.5	15	28	1125
GN.80931	GN 24-100-M24-100-D0-TK	100	M 24	9	31.5	100	70.5	19	46	945
GN.80933	GN 24-100-M24-125-D0-TK	100	M 24	9	31.5	125	70.5	19	46	1035
GN.80935	GN 24-100-M24-150-D0-TK	100	M 24	9	31.5	150	70.5	19	46	1120
GN.80937	GN 24-100-M24-200-D0-TK	100	M 24	9	31.5	200	70.5	19	46	1300
GN.80939	GN 24-100-M24-300-D0-TK	100	M 24	9	31.5	300	70.5	19	46	1650
GN.80951	GN 24-120-M20-75-D0-TK	120	M 20	12	32	75	95.5	15	28	1075
GN.80953	GN 24-120-M20-100-D0-TK	120	M 20	12	32	100	95.5	15	28	1135
GN.80955	GN 24-120-M20-125-D0-TK	120	M 20	12	32	125	95.5	15	28	1195
GN.80957	GN 24-120-M20-150-D0-TK	120	M 20	12	32	150	95.5	15	28	1255
GN.80959	GN 24-120-M20-200-D0-TK	120	M 20	12	32	200	95.5	15	28	1380
GN.80961	GN 24-120-M20-250-D0-TK	120	M 20	12	32	250	95.5	15	28	1500
GN.80971	GN 24-120-M24-100-D0-TK	120	M 24	12	35.5	100	95.5	19	46	1310
GN.80973	GN 24-120-M24-125-D0-TK	120	M 24	12	35.5	125	95.5	19	46	1400
GN.80975	GN 24-120-M24-150-D0-TK	120	M 24	12	35.5	150	95.5	19	46	1490
GN.80977	GN 24-120-M24-200-D0-TK	120	M 24	12	35.5	200	95.5	19	46	1665
GN.80979	GN 24-120-M24-300-D0-TK	120	M 24	12	35.5	300	95.5	19	46	2015

Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
100	3.90
120	4.68



GN 24-D1-TK

INOX STAINLESS STEEL METRIC

Code	Description	d1	d2	h1	h2	h4	l1	k	sw2	Static load [KN]	⚖
GN.80892	GN 24-100-M16-75-D1-TK	100	M 16	9	3	26.5	75	70.5	12	17	626
GN.80894	GN 24-100-M16-100-D1-TK	100	M 16	9	3	26.5	100	70.5	12	17	665
GN.80896	GN 24-100-M16-125-D1-TK	100	M 16	9	3	26.5	125	70.5	12	17	704
GN.80898	GN 24-100-M16-150-D1-TK	100	M 16	9	3	26.5	150	70.5	12	17	743
GN.80900	GN 24-100-M16-200-D1-TK	100	M 16	9	3	26.5	200	70.5	12	17	822
GN.80902	GN 24-100-M16-250-D1-TK	100	M 16	9	3	26.5	250	70.5	12	17	900
GN.80912	GN 24-100-M20-75-D1-TK	100	M 20	9	3	28	75	70.5	15	28	737
GN.80914	GN 24-100-M20-100-D1-TK	100	M 20	9	3	28	100	70.5	15	28	798
GN.80916	GN 24-100-M20-125-D1-TK	100	M 20	9	3	28	125	70.5	15	28	860
GN.80918	GN 24-100-M20-150-D1-TK	100	M 20	9	3	28	150	70.5	15	28	921
GN.80920	GN 24-100-M20-200-D1-TK	100	M 20	9	3	28	200	70.5	15	28	1045
GN.80922	GN 24-100-M20-250-D1-TK	100	M 20	9	3	28	250	70.5	15	28	1165
GN.80932	GN 24-100-M24-100-D1-TK	100	M 24	9	3	31.5	100	70.5	19	46	984
GN.80934	GN 24-100-M24-125-D1-TK	100	M 24	9	3	31.5	125	70.5	19	46	1070
GN.80936	GN 24-100-M24-150-D1-TK	100	M 24	9	3	31.5	150	70.5	19	46	1160
GN.80938	GN 24-100-M24-200-D1-TK	100	M 24	9	3	31.5	200	70.5	19	46	1335
GN.80940	GN 24-100-M24-300-D1-TK	100	M 24	9	3	31.5	300	70.5	19	46	1690
GN.80952	GN 24-120-M20-75-D1-TK	120	M 20	12	3.5	32	75	95.5	15	28	1145
GN.80954	GN 24-120-M20-100-D1-TK	120	M 20	12	3.5	32	100	95.5	15	28	1210
GN.80956	GN 24-120-M20-125-D1-TK	120	M 20	12	3.5	32	125	95.5	15	28	1270
GN.80958	GN 24-120-M20-150-D1-TK	120	M 20	12	3.5	32	150	95.5	15	28	1330
GN.80960	GN 24-120-M20-200-D1-TK	120	M 20	12	3.5	32	200	95.5	15	28	1455
GN.80962	GN 24-120-M20-250-D1-TK	120	M 20	12	3.5	32	250	95.5	15	28	1575
GN.80972	GN 24-120-M24-100-D1-TK	120	M 24	12	3.5	35.5	100	95.5	19	46	1385
GN.80974	GN 24-120-M24-125-D1-TK	120	M 24	12	3.5	35.5	125	95.5	19	46	1475
GN.80976	GN 24-120-M24-150-D1-TK	120	M 24	12	3.5	35.5	150	95.5	19	46	1560
GN.80978	GN 24-120-M24-200-D1-TK	120	M 24	12	3.5	35.5	200	95.5	19	46	1740
GN.80980	GN 24-120-M24-300-D1-TK	120	M 24	12	3.5	35.5	300	95.5	19	46	2090