

VERSIONS

- Version **C**: open eye
- Version **E**: closed eye (only available in stainless steel)

Steel **ST**

Zinc plated **ZB**

Stainless steel **A4**

Plain finish **BL**

FEATURES AND APPLICATIONS

Carabiners GN 5299 are used, for example, to connect tools or other components quickly and without tools or to secure them against loss. The carabiner is opened by hand and closes automatically by a concealed spring when released.

The eye of type E, which is fitted with a pressed-in, closed round thimble, enables captive mounting of the carabiners, e.g. by means of an appropriately pressed retaining cable.

Carabiners GN 5299 must not be used for lifting loads or lashing. The data on load capacity are approximate values to the exclusion of any liability.




GN 5299-C-ST
GN 5299-C-A4

GN 5299-E-A4

Conversion Table
1 mm = 0.039 inch

d1	
mm	inch
6	0.23
7	0.27
8	0.31
9	0.35



GN 5299-C-ST

Code	Description	d1	d2 min	d3	f min	Length l	m min	Static load [N]	⚖
GN.47662	GN 5299-C-40-ST-ZB	6	11	4	4.5	40	5	500	11
GN.47664	GN 5299-C-50-ST-ZB	8	15	5	5.5	50	7	1200	16
GN.47666	GN 5299-C-60-ST-ZB	9	17	6	6.5	60	8	1200	27

GN 5299-C-A4

Code	Description	d1	d2 min	d3	f min	Length l	m min	Static load [N]	⚖
GN.47661	GN 5299-C-40-A4-BL	6	11	4	4.5	40	5	500	11
GN.47663	GN 5299-C-50-A4-BL	8	15	5	5.5	50	7	1200	16
GN.47665	GN 5299-C-60-A4-BL	9	17	6	6.5	60	8	1200	27

GN 5299-E-A4

Code	Description	b	d1	d2 min	d3	f min	Length l	m min	Static load [N]	⚖
GN.47671	GN 5299-E-50-A4-BL	5.3	6	15	5	5.5	50	7	1200	16
GN.47672	GN 5299-E-60-A4-BL	6.4	7	17	6	6.5	60	8	1200	27