

VERSIONS

- Version **A**: without accessories
- Version **C**: with fastening set and cover cap

Angle bracket

Die-cast zinc alloy

Painted, white aluminum **ZW**

Screws and T-Nuts (only for Type C)

Zinc-plated steel, blue passivated **SZ**

Cover cap (only for Type C)

Polyamide based (PA) technopolymer

Black **S**

FEATURES AND APPLICATIONS

Angle brackets GN 30I fasten aluminum profiles to objects such as tables and panels or at right angles to each other. Machining of the profile is not necessary.


The connection can be freely positioned and slid along the slot. To fasten the angle brackets to a panel or transversely to an aluminum profile, the guide steps must be broken off.

ACCESSORIES ON REQUEST


- GN 50I: T-Nuts




Assembly of cover cap
(only for GN 30I-C-ZWSZS)



Application examples






GN 30I-A-ZW

METRIC

Code	Description	h1	l*	l#	d For screws	k	n	s*	s#	⚖
GN.67801	GN 30I-30306-A-ZW	30	30	M6	2.5	-	6	30	30	47
GN.67806	GN 30I-30606-A-ZW	60	60	M6	3.5	-	6	30	30	130
GN.67811	GN 30I-40408-A-ZW	40	40	M8	5	-	8	40	40	85
GN.67816	GN 30I-40808-A-ZW	80	80	M8	5	-	8	40	40	271
GN.67821	GN 30I-80808-A-ZW	80	76	M8	8	40	8	80	74	407



Conversion Table	
1 mm = 0.039 inch	
mm	inch
30	1.17
40	1.56
60	2.34
76	2.96
80	3.12

GN 30I-C-ZWSZS

METRIC

Code	Description	h1	l*	l#	d	h2	k	n	s*	s#	⚖
GN.67851	GN 30I-30306-C-ZWSZS	30	30	M6	2.5	2	-	6	30	30	52
GN.67856	GN 30I-30606-C-ZWSZS	60	60	M6	3.5	2	-	6	30	30	166
GN.67861	GN 30I-40408-C-ZWSZS	40	40	M8	5	2	-	8	40	40	158
GN.67866	GN 30I-40808-C-ZWSZS	80	80	M8	5	2	-	8	40	40	355
GN.67871	GN 30I-80808-C-ZWSZS	80	76	M8	8	7	40	8	80	74	575

* Nominal dimension
Real dimension