



1

MATERIAL

AISI 316L stainless steel, sandblasted matte finish.



2

STANDARD EXECUTIONS

- **GN 5335.4-C:** H7 reamed blind hole.
- **GN 5335.4-E:** threaded blind hole.



3

FEATURES AND APPLICATIONS

The finish quality, angular seal and absence of recesses, prevents dirt adherence and facilitates cleaning.

Particularly suitable for applications on machines and equipment whose parts must be frequently cleaned by using water jets or steam.



4



5



6



7



8



9



10



11



12



13



14



15




16



17



18

**Conversion Table**

1 mm = 0.039 inch

| d1 | |
|----|------|
| mm | inch |
| 40 | 1.57 |
| 50 | 1.97 |
| 60 | 2.34 |

GN 5335.4-C

INOX STAINLESS STEEL

METRIC

| Code | Description | d1 | d3 H7 | d4 | h1 | h2 | t1 min | ⚖ |
|----------|--------------------|----|-------|----|------|----|--------|-----|
| GN.28457 | GN 5335.4-40-B8-C | 40 | 8 | 18 | 30.5 | 15 | 15 | 125 |
| GN.28467 | GN 5335.4-50-B10-C | 50 | 10 | 21 | 34 | 17 | 18 | 205 |
| GN.28477 | GN 5335.4-60-B12-C | 60 | 12 | 25 | 39 | 18 | 22 | 366 |

GN 5335.4-E

INOX STAINLESS STEEL

METRIC

| Code | Description | d1 | d2 | d4 | h1 | h2 | t1 min | ⚖ |
|----------|--------------------|----|-----|----|------|----|--------|-----|
| GN.28451 | GN 5335.4-40-M6-E | 40 | M6 | 18 | 30.5 | 15 | 12 | 128 |
| GN.28453 | GN 5335.4-40-M8-E | 40 | M8 | 18 | 30.5 | 15 | 15 | 125 |
| GN.28461 | GN 5335.4-50-M8-E | 50 | M8 | 21 | 34 | 17 | 15 | 214 |
| GN.28463 | GN 5335.4-50-M10-E | 50 | M10 | 21 | 34 | 17 | 18 | 208 |
| GN.28471 | GN 5335.4-60-M10-E | 60 | M10 | 25 | 39 | 18 | 18 | 367 |
| GN.28473 | GN 5335.4-60-M12-E | 60 | M12 | 25 | 39 | 18 | 22 | 365 |