


SPECIFICATION

- Tube Ø 28 x 2
Stainless steel
- AISI 304
 - sand-blasted matte finish.
- End supports
- Stainless Steel-precision casting
- AISI CF-8
 - Sand-blasted matte finish.

FEATURES AND APPLICATIONS

With the Stainless Steel-Tubular handles GN 333.6, the handle legs and the handle tube are pressed together.

A typical application for tubular handles is on double-winged doors for machines or devices.



Conversion Table	
1 mm = 0.039 inch	
mm	inch
200	7.87
250	9.84
300	11.81
400	15.75
500	19.69
600	23.62

Code	Description	d1	l±0.5	b1	b2	b3	b4	d2	h1	h2	tmin	⚖
GN.33361	GN 333.6-28-200	28	200	25	14	50	66	M8	50	66	15	605
GN.33362	GN 333.6-28-250	28	250	25	14	50	66	M8	50	66	15	670
GN.33363	GN 333.6-28-300	28	300	25	14	50	66	M8	50	66	15	730
GN.33364	GN 333.6-28-400	28	400	25	14	50	66	M8	50	66	15	845
GN.33365	GN 333.6-28-500	28	500	25	14	50	66	M8	50	66	15	980
GN.33366	GN 333.6-28-600	28	600	25	14	50	66	M8	50	66	15	1060