


MATERIAL

AISI 304 stainless steel, sandblasted matte finish.


STANDARD EXECUTIONS

H8 reamed hole. Assembly by means of a supplied stainless steel transversal grub screw with hexagon socket.

- **GN 436-N:** plain execution.
- **GN 436-M:** with laser-engraved black position point, in a position opposite to the set screw.



Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
24	0.94
28	1.10



GN 436-N

INOX STAINLESS STEEL **METRIC**

Code	Description	d1	d2 H8	d3	l	h	tmin	⚖️
GN.22152	GN 436-24-B5-N-MT	24	5	M4	4	16	10	53
GN.22154	GN 436-24-B6-N-MT	24	6	M4	4	16	10	52
GN.22156	GN 436-28-B6-N-MT	28	6	M4	4	18	11	80
GN.22158	GN 436-28-B8-N-MT	28	8	M4	4	18	11	78

GN 436-M

INOX STAINLESS STEEL **METRIC**

Code	Description	d1	d2 H8	d3	l	h	tmin	⚖️
GN.22151	GN 436-24-B5-M-MT	24	5	M4	4	16	10	53
GN.22153	GN 436-24-B6-M-MT	24	6	M4	4	16	10	52
GN.22155	GN 436-28-B6-M-MT	28	6	M4	4	18	11	80
GN.22157	GN 436-28-B8-M-MT	28	8	M4	4	18	11	78