

MATERIAL

Reinforced polyamide based (PA) technopolymer, black colour, matte finish.

STANDARD EXECUTIONS


- **GN 6336.3:** zinc-plated steel hub with pass-through and oblique hole, partially threaded.
- **GN 6336.3-NI:** AISI 303 stainless steel hub with pass-through and oblique hole, partially threaded.

APPLICATIONS


GN 6336.3 lobe knobs are used when quick tightening is required with only a slight clamping force.

ASSEMBLY INSTRUCTIONS

The knob is placed in the axial position so that it fits onto the pin threads. At this point it can be locked with just a slight rotation.



Application examples
The threaded pin must exceed length h



Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
40	1.57
50	1.97
63	2.48

GN 6336.3

METRIC

Code	Description	d1	d2	d3	d4	h1	h2	h3 min	⚖
GN.29211	GN 6336.3-40-M8	40	M8	16	8.4	26	13	24	32
GN.29221	GN 6336.3-50-M10	50	M10	20	10.5	34	17	30	60
GN.29231	GN 6336.3-63-M12	63	M12	26	13	42	21	37	129

GN 6336.3-NI

INOX
STAINLESS
STEEL

METRIC

Code	Description	d1	d2	d3	d4	h1	h2	h3 min	⚖
GN.29213	GN 6336.3-40-M8-NI	40	M8	16	8.4	26	13	24	32
GN.29223	GN 6336.3-50-M10-NI	50	M10	20	10.5	34	17	30	60
GN.29233	GN 6336.3-63-M12-NI	63	M12	26	13	42	21	37	129

