

MATERIAL


Hardened steel.

FEATURES AND APPLICATIONS


GN 6322 elements are generally used for positioning and fixing of workpieces.

The spherical shape of the head (GN 6322-B) allows an optimal positioning in the holes facilitating their insertion.


The flat design (GN 6322-C) helps to compensate for tolerances in the spacing of two holes.



GN 6322-B



GN 6322-C



Conversion Table
1 mm = 0.039 inch

d1

mm	inch
10	0.39
12	0.47
16	0.63
20	0.79
22	0.87
25	0.98

GN 6322-B

Code	Description	d1 g6	d2 n6	d3 -0.01 -0.05	d4	h1	h2	l	t	r	⚖
GN.28631	GN 6322-10-7-B	10	7	10	M3	10	2.5	7	6	2.5	7
GN.28633	GN 6322-12-8-B	12	8	12	M4	12	3	8	8	3	11
GN.28635	GN 6322-16-12-B	16	12	16	M5	16	4	12	10	4	30
GN.28637	GN 6322-20-14-B	20	14	20	M5	20	5	14	10	5	57
GN.28639	GN 6322-22-16-B	22	16	22	M5	22	5.5	16	10	5.5	79
GN.28641	GN 6322-25-18-B	25	18	25	M5	25	6	18	10	6	116

GN 6322-C

Code	Description	d1 g6	d2 n6	d3 -0.01 -0.05	d4	h1	h2	l	s	t	r	⚖
GN.28632	GN 6322-10-7-C	10	7	10	M3	10	2.5	7	2.5	6	2.5	5
GN.28634	GN 6322-12-8-C	12	8	12	M4	12	3	8	2.5	8	3	8
GN.28636	GN 6322-16-12-C	16	12	16	M5	16	4	12	4.3	10	4	24
GN.28638	GN 6322-20-14-C	20	14	20	M5	20	5	14	5	10	5	45
GN.28640	GN 6322-22-16-C	22	16	22	M5	22	5.5	16	5	10	5.5	62
GN.28642	GN 6322-25-18-C	25	18	25	M5	25	6	18	5.6	10	6	90

METRIC