

GN 798.1

Revolving handles

Stainless steel

GN 798.4

Revolving handles

Mounting on the operator's side, stainless steel



MATERIAL

Fine turned AISI 303 stainless steel.

STANDARD EXECUTION

AISI 303 stainless steel pin, hexagonal socket at threaded end.

SPECIAL EXECUTIONS ON REQUEST

Shank with different threadings.



MATERIAL

Fine turned AISI 303 stainless steel.

STANDARD EXECUTION



AISI 303 stainless steel pin.

FEATURES

Using a wrench for the flat faces (s) at the base of the pin, the front locking allows to exert a greater torque than the one applied with a wrench to the hexagonal socket into the threaded pin (back mounting).



Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
18	0.71
22	0.87
24	0.94



Code	Description	d1	d2	d3	d4	l1	l2	l3	l4	⚖️
GN.11221	GN 798.1-NI-18-M6	18	M6	10	14.5	56	13	2.5	19	95
GN.11222	GN 798.1-NI-18-M8	18	M8	10	14.5	56	13	2.5	19	97
GN.11225	GN 798.1-NI-22-M8	22	M8	14	18.5	59	14	2.5	21	163
GN.11226	GN 798.1-NI-22-M10	22	M10	14	18.5	59	14	2.5	21	165
GN.11227	GN 798.1-NI-24-M8	24	M8	14	18.5	74	16	2.5	27	210
GN.11228	GN 798.1-NI-24-M10	24	M10	14	18.5	74	16	2.5	27	212



Code	Description	d1	d2	d3	d4	l1	l2	l3	l4	s	⚖️
GN.11212	GN 798.4-NI-18-M6	18	M6	10	14.5	56	13	4	19	8	89
GN.11215	GN 798.4-NI-22-M8	22	M8	14	18.5	59	14	5.2	21	11	157
GN.11217	GN 798.4-NI-24-M10	24	M10	14	18.5	74	16	5.2	27	11	209