



MOUNTING BASE

Chrome-plated steel, matte finish.



FASTENING NUT

Zinc-plated steel.



KNOB

Knurled aluminium profile, anodised, black colour.



SLIDING BUSHING

Natural steel.



CAP

Acetal resin based (POM) technopolymer, light-grey colour.



NUMBERING ON THE BASE

- 10 marks (D=27) which correspond to 10 knob rotations.

- 15 marks (D=34) which correspond to 15 knob rotations.

Each mark corresponds to 1 mm linear movement.

Black colour laser-engraving in contrast with the chrome-plated surface of the base.



NUMBERING ON THE KNOB

- 50 marks numbered from 0.1 ... to 0.9.

Each mark corresponds to 0.02 mm axial movement.

Laser-engraving in contrast with the black surface of the knob.



STANDARD EXECUTIONS

- **GN 727-A**: base with holes for assembly screws coaxial to the spindle.

- **GN 727-B**: base with holes for assembly screws perpendicular to the spindle axis.

- **GN 727-S1**: fastening by nut

Index for graduation type:

- **SR**: values increasing by clockwise rotation.

- **SL**: values increasing by anticlockwise rotation.



FEATURES



GN 727 control knobs allow axial adjustments, for example, of a limit stop device.

GN 727-S1 execution is suitable for assembly on plates of limited thickness (from 2 to 8 mm).




SPECIAL EXECUTIONS ON REQUEST

On the surface of the cap words, marks, graphic symbols, etc...can be tampoprinted in colours.



Conversion Table	
1 mm = 0.039 inch	
d1 f7	
mm	inch
27	1.06
34	1.34



GN 727-A

Code	Description	d1 f7	d2	d3	d4	d5	d6	d7	b1	b2	k1	l1+0.2	l2	l3	l4	h	w	⚖
GN.30561	GN 727-27-A-SR	27	M6	M12x1	6.4	18	4.3	38	10	20	28	54	19.5	37.5	0.5	4.3	10	110
GN.30565	GN 727-27-A-SL	27	M6	M12x1	6.4	18	4.3	38	10	20	28	54	19.5	37.5	0.5	4.3	10	110
GN.30571	GN 727-34-A-SR	34	M8	M16x1	8.5	23	5.3	40	11	25	36	67	23.5	45.5	0.5	4.2	15	210
GN.30575	GN 727-34-A-SL	34	M8	M16x1	8.5	23	5.3	40	11	25	36	67	23.5	45.5	0.5	4.2	15	210

GN 727-B

Code	Description	d1 f7	d2	d3	d4	d5	d6	d7	b1	b2	k2	l1+0.2	l2	l3	l4	h	w	⚖
GN.30562	GN 727-27-B-SR	27	M6	M12x1	6.4	18	4.3	38	10	20	22	54	19.5	37.5	0.5	4.3	10	105
GN.30566	GN 727-27-B-SL	27	M6	M12x1	6.4	18	4.3	38	10	20	22	54	19.5	37.5	0.5	4.3	10	105
GN.30572	GN 727-34-B-SR	34	M8	M16x1	8.5	23	5.3	40	11	25	30	67	23.5	45.5	0.5	4.2	15	200
GN.30576	GN 727-34-B-SL	34	M8	M16x1	8.5	23	5.3	40	11	25	30	67	23.5	45.5	0.5	4.2	15	200

GN 727-S1

Code	Description	d1 f7	d2	d3	d4	d5	d8-0.05	d9	l1+0.2	l2	l3	l5	h	s	w	⚖
GN.30564	GN 727-27-S1-SR	27	M6	M12x1	6.4	18	19	12.5	54	19.5	37.5	1	4.3	22	10	101
GN.30563	GN 727-27-S1-SL	27	M6	M12x1	6.4	18	19	12.5	54	19.5	37.5	1	4.3	22	10	101
GN.30574	GN 727-34-S1-SR	34	M8	M16x1	8.5	23	24	18.3	67	23.5	45.5	1	4.2	27	15	206
GN.30573	GN 727-34-S1-SL	34	M8	M16x1	8.5	23	24	18.3	67	23.5	45.5	1	4.2	27	15	206