

MATERIAL

Die cast zinc alloy, epoxy resin coating, black colour RAL 9005 (SW) or grey colour RAL 9006 (SR), matte finish.

PACKING RING

NBR synthetic rubber, black colour, glued to the handle body.

SCREWS (ONLY FOR GN 7330-A)

AISI 304 stainless steel with countersunk flat head, with polyamide coating in the underhead.

IP PROTECTION

Degree of protection IP 66 in accordance with EN 60529 table (on page A-19).
(only for executions with packing ring).

STANDARD EXECUTIONS

Front mounting by means of pass-through holes for M5 countersunk flat head screws, included in the supply:

- GN 7330-A-1: without gasket.
- GN 7330-A-2: with packing ring.

Rear mounting by means of 4 M5 screws welded to the handle body:


- GN 7330-C-1: without gasket.
- GN 7330-C-2: with packing ring.

ASSEMBLY INSTRUCTIONS


Drill the handle housing according to the template dimensions.



Drilling template





	l7	m1
GN 7330-127	88 ⁺¹	100
GN 7330-155	115 ⁺¹	128



GN 7330-A-1

GN 7330-A-2



Conversion Table 1 mm = 0.039 inch	
mm	inch
127	5
155	6.10

SW RAL9005 SR RAL9006



METRIC

GN 7330-A-1

Code	Description	l1	l2	l3	l4	l5	h1	h2	m1	m2	⚖
GN.30352	GN 7330-127-A-1-SW	127	72	25	3.5	22.5	80	43	100	53	247
GN.30372	GN 7330-155-A-1-SW	155	99	25	3.5	22.5	80	43	128	53	290
GN.30351	GN 7330-127-A-1-SR	127	72	25	3.5	22.5	80	43	100	53	234
GN.30371	GN 7330-155-A-1-SR	155	99	25	3.5	22.5	80	43	128	53	288

GN 7330-A-2

Code	Description	l1	l2	l3	l4	l5	h1	h2	m1	m2	⚖
GN.30354	GN 7330-127-A-2-SW	127	72	25	3.5	22.5	80	43	100	53	252
GN.30374	GN 7330-155-A-2-SW	155	99	25	3.5	22.5	80	43	128	53	300
GN.30353	GN 7330-127-A-2-SR	127	72	25	3.5	22.5	80	43	100	53	250
GN.30373	GN 7330-155-A-2-SR	155	99	25	3.5	22.5	80	43	128	53	325



Conversion Table	
1 mm = 0.039 inch	
l1	
mm	inch
127	5
155	6.10

GN 7330-C-1

Code	Description	l1	l2	l3	l4	l5	h1	h2	m1	m2	⚖
GN.30356	GN 7330-127-C-1-SW	127	72	25	3.5	22.5	80	43	100	53	249
GN.30376	GN 7330-155-C-1-SW	155	99	25	3.5	22.5	80	43	128	53	312
GN.30355	GN 7330-127-C-1-SR	127	72	25	3.5	22.5	80	43	100	53	246
GN.30375	GN 7330-155-C-1-SR	155	99	25	3.5	22.5	80	43	128	53	311

GN 7330-C-2

Code	Description	l1	l2	l3	l4	l5	h1	h2	m1	m2	⚖
GN.30358	GN 7330-127-C-2-SW	127	72	25	3.5	22.5	80	43	100	53	249
GN.30378	GN 7330-155-C-2-SW	155	99	25	3.5	22.5	80	43	128	53	317
GN.30357	GN 7330-127-C-2-SR	127	72	25	3.5	22.5	80	43	100	53	260
GN.30377	GN 7330-155-C-2-SR	155	99	25	3.5	22.5	80	43	128	53	316