

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

MATERIAL

Black-oxide steel, class 5.8 (tensile strength 500 N/mm 2), hexagon socket head.

STANDARD EXECUTIONS

- **GN 913.3-KU** acetal resin based (POM) technopolymer bolt, natural colour.
- **GN 913.3-MS** brass bolt.

FEATURES AND APPLICATIONS


GN 913.3 grub screws, thanks to the brass or technopolymer bolt, prevent the contact surface from being damaged.

SPECIAL EXECUTIONS ON REQUEST

Different threadings and lengths.



Conversion Table			
1 mm = 0.039 inch			
l1			
mm	inch	mm	inch
3	0.12	20	0.78
4	0.16	25	0.98
5	0.20	32	1.25
6	0.23	40	1.56
8	0.31	50	1.95
10	0.39	63	2.46
12	0.47	80	3.12
16	0.62	100	3.90



METRIC

GN 913.3-KU


Code	Description	d1	d3	l1	l3±0.3	sw	
GN.13586	GN 913.3-M3-3-KU	M 3	1.5	3	0.8	1.5	1
GN.13588	GN 913.3-M3-4-KU	M3	1.5	4	0.8	1.5	1
GN.13590	GN 913.3-M3-5-KU	M3	1.5	5	0.8	1.5	1
GN.13592	GN 913.3-M3-6-KU	M3	1.5	6	0.8	1.5	1
GN.13594	GN 913.3-M3-8-KU	M3	1.5	8	0.8	1.5	1
GN.13596	GN 913.3-M3-10-KU	M3	1.5	10	0.8	1.5	1
GN.13701	GN 913.3-M4-6-KU	M 4	2	6	1	1.5	1
GN.13702	GN 913.3-M4-8-KU	M 4	2	8	1	1.5	1
GN.13703	GN 913.3-M4-10-KU	M 4	2	10	1	1.5	1
GN.13704	GN 913.3-M4-12-KU	M 4	2	12	1	1.5	1
GN.13705	GN 913.3-M4-16-KU	M 4	2	16	1	1.5	1
GN.13706	GN 913.3-M4-20-KU	M 4	2	20	1	1.5	1
GN.13711	GN 913.3-M5-8-KU	M 5	3	8	1	2.5	1
GN.13712	GN 913.3-M5-10-KU	M 5	3	10	1	2.5	1
GN.13713	GN 913.3-M5-12-KU	M 5	3	12	1	2.5	1
GN.13714	GN 913.3-M5-16-KU	M 5	3	16	1	2.5	2
GN.13715	GN 913.3-M5-20-KU	M 5	3	20	1	2.5	2
GN.13716	GN 913.3-M5-25-KU	M 5	3	25	1	2.5	3
GN.13607	GN 913.3-M6-6-KU	M 6	3.5	6	1.3	3	1
GN.13609	GN 913.3-M6-8-KU	M 6	3.5	8	1.3	3	1
GN.13720	GN 913.3-M6-10-KU	M 6	3.5	10	1.3	3	1
GN.13721	GN 913.3-M6-12-KU	M 6	3.5	12	1.3	3	2
GN.13722	GN 913.3-M6-16-KU	M 6	3.5	16	1.3	3	2
GN.13723	GN 913.3-M6-20-KU	M 6	3.5	20	1.3	3	3
GN.13724	GN 913.3-M6-25-KU	M 6	3.5	25	1.3	3	4
GN.13725	GN 913.3-M6-32-KU	M 6	3.5	32	1.3	3	9
GN.13726	GN 913.3-M6-40-KU	M 6	3.5	40	1.3	3	6
GN.13728	GN 913.3-M6-50-KU	M 6	3.5	50	1.3	3	8

GN 913.3-KU

Code	Description	d1	d3	l1	l3±0.3	sw	
GN.13615	GN 913.3-M8-8-KU	M 8	5	8	1.6	4	2
GN.13729	GN 913.3-M8-12-KU	M 8	5	12	1.6	4	3
GN.13730	GN 913.3-M8-16-KU	M 8	5	16	1.6	4	5
GN.13731	GN 913.3-M8-20-KU	M 8	5	20	1.6	4	5
GN.13732	GN 913.3-M8-25-KU	M 8	5	25	1.6	4	6
GN.13733	GN 913.3-M8-32-KU	M 8	5	32	1.6	4	9
GN.13734	GN 913.3-M8-40-KU	M 8	5	40	1.6	4	12
GN.13736	GN 913.3-M8-50-KU	M 8	5	50	1.6	4	15
GN.13738	GN 913.3-M8-63-KU	M 8	5	63	1.6	4	19
GN.13739	GN 913.3-M10-16-KU	M 10	6.5	16	1.9	5	7
GN.13740	GN 913.3-M10-20-KU	M 10	6.5	20	1.9	5	9
GN.13741	GN 913.3-M10-25-KU	M 10	6.5	25	1.9	5	11
GN.13742	GN 913.3-M10-32-KU	M 10	6.5	32	1.9	5	15
GN.13743	GN 913.3-M10-40-KU	M 10	6.5	40	1.9	5	18
GN.13744	GN 913.3-M10-50-KU	M 10	6.5	50	1.9	5	23
GN.13746	GN 913.3-M10-63-KU	M 10	6.5	63	1.9	5	30
GN.13748	GN 913.3-M10-80-KU	M 10	6.5	80	1.9	5	38
GN.13749	GN 913.3-M12-20-KU	M 12	8	20	2.1	6	12
GN.13750	GN 913.3-M12-25-KU	M 12	8	25	2.1	6	16
GN.13751	GN 913.3-M12-32-KU	M 12	8	32	2.1	6	21
GN.13752	GN 913.3-M12-40-KU	M 12	8	40	2.1	6	27
GN.13753	GN 913.3-M12-50-KU	M 12	8	50	2.1	6	34
GN.13754	GN 913.3-M12-63-KU	M 12	8	63	2.1	6	43
GN.13756	GN 913.3-M12-80-KU	M 12	8	80	2.1	6	55
GN.13758	GN 913.3-M12-100-KU	M 12	8	100	2.1	6	70

METRIC

Conversion Table 1 mm = 0.039 inch			
l1			
mm	inch	mm	inch
3	0.12	20	0.78
4	0.16	25	0.98
5	0.20	32	1.25
6	0.23	40	1.56
8	0.31	50	1.95
10	0.39	63	2.46
12	0.47	80	3.12
16	0.62	100	3.90



GN 913.3-MS

METRIC

Code	Description	d1	d2	l1	l2	sw	△
GN.13587	GN 913.3-M3-3-MS	M 3	1.9	3	0.5	1.5	1
GN.13589	GN 913.3-M3-4-MS	M 3	1.9	4	0.5	1.5	1
GN.13591	GN 913.3-M3-5-MS	M 3	1.9	5	0.5	1.5	1
GN.13593	GN 913.3-M3-6-MS	M 3	1.9	6	0.5	1.5	1
GN.13595	GN 913.3-M3-8-MS	M 3	1.9	8	0.5	1.5	1
GN.13597	GN 913.3-M3-10-MS	M 3	1.9	10	0.5	1.5	1
GN.13601	GN 913.3-M4-4-MS	M 4	2.5	4	0.5	1.5	1
GN.13602	GN 913.3-M4-5-MS	M 4	2.5	5	0.5	1.5	1
GN.13801	GN 913.3-M4-6-MS	M 4	2.5	6	0.5	1.5	1
GN.13802	GN 913.3-M4-8-MS	M 4	2.5	8	0.5	1.5	1
GN.13803	GN 913.3-M4-10-MS	M 4	2.5	10	0.5	1.5	1
GN.13804	GN 913.3-M4-12-MS	M 4	2.5	12	0.5	2	1
GN.13805	GN 913.3-M4-16-MS	M 4	2.5	16	0.5	2	1
GN.13806	GN 913.3-M4-20-MS	M 4	2.5	20	0.5	2	1
GN.13604	GN 913.3-M5-5-MS	M 5	3	5	0.5	2.5	1
GN.13605	GN 913.3-M5-6-MS	M 5	3	6	0.5	2.5	1
GN.13811	GN 913.3-M5-8-MS	M 5	3	8	0.5	2.5	1
GN.13812	GN 913.3-M5-10-MS	M 5	3	10	0.5	2.5	1
GN.13813	GN 913.3-M5-12-MS	M 5	3	12	0.5	2.5	1
GN.13814	GN 913.3-M5-16-MS	M 5	3	16	0.5	2.5	2
GN.13815	GN 913.3-M5-20-MS	M 5	3	20	0.5	2.5	2
GN.13816	GN 913.3-M5-25-MS	M 5	3	25	0.5	2.5	3

GN 913.3-MS

METRIC

Code	Description	d1	d2	l1	l2	sw	△
GN.13608	GN 913.3-M6-6-MS	M 6	4	6	1	3	1
GN.13610	GN 913.3-M6-8-MS	M 6	4	8	1	3	1
GN.13821	GN 913.3-M6-10-MS	M 6	4	10	1	3	1
GN.13822	GN 913.3-M6-12-MS	M 6	4	12	1	3	2
GN.13823	GN 913.3-M6-16-MS	M 6	4	16	1	3	2
GN.13824	GN 913.3-M6-20-MS	M 6	4	20	1	3	3
GN.13825	GN 913.3-M6-25-MS	M 6	4	25	1	3	4
GN.13826	GN 913.3-M6-32-MS	M 6	4	32	1	3	9
GN.13827	GN 913.3-M6-40-MS	M 6	4	40	1	3	6
GN.13828	GN 913.3-M6-50-MS	M 6	4	50	1	3	8
GN.13616	GN 913.3-M8-8-MS	M 8	6	8	1.5	4	2
GN.13619	GN 913.3-M8-10-MS	M 8	6	10	1.5	4	2
GN.13831	GN 913.3-M8-12-MS	M 8	6	12	1.5	4	3
GN.13832	GN 913.3-M8-16-MS	M 8	6	16	1.5	4	5
GN.13833	GN 913.3-M8-20-MS	M 8	6	20	1.5	4	5
GN.13834	GN 913.3-M8-25-MS	M 8	6	25	1.5	4	6
GN.13835	GN 913.3-M8-32-MS	M 8	6	32	1.5	4	9
GN.13836	GN 913.3-M8-40-MS	M 8	6	40	1.5	4	12
GN.13837	GN 913.3-M8-50-MS	M 8	6	50	1.5	4	15
GN.13838	GN 913.3-M8-63-MS	M 8	6	63	1.5	4	19
GN.13841	GN 913.3-M10-16-MS	M 10	8	16	2	5	7
GN.13842	GN 913.3-M10-20-MS	M 10	8	20	2	5	9
GN.13843	GN 913.3-M10-25-MS	M 10	8	25	2	5	11
GN.13844	GN 913.3-M10-32-MS	M 10	8	32	2	5	15
GN.13845	GN 913.3-M10-40-MS	M 10	8	40	2	5	18
GN.13846	GN 913.3-M10-50-MS	M 10	8	50	2	5	23
GN.13847	GN 913.3-M10-63-MS	M 10	8	63	2	5	30
GN.13848	GN 913.3-M10-80-MS	M 10	8	80	2	5	38
GN.13851	GN 913.3-M12-20-MS	M 12	10	20	2	6	12
GN.13852	GN 913.3-M12-25-MS	M 12	10	25	2	6	16
GN.13853	GN 913.3-M12-32-MS	M 12	10	32	2	6	21
GN.13854	GN 913.3-M12-40-MS	M 12	10	40	2	6	27
GN.13855	GN 913.3-M12-50-MS	M 12	10	50	2	6	34
GN.13856	GN 913.3-M12-63-MS	M 12	10	63	2	6	43
GN.13857	GN 913.3-M12-80-MS	M 12	10	80	2	6	55
GN.13858	GN 913.3-M12-100-MS	M 12	10	100	2	6	70



Standard machine parts